

此为证书 CN16/21298 译本

下述组织

## 维谛技术(绵阳)有限公司

注册地址:中国四川省绵阳市飞云大道东段 299号 经营地址:中国四川省绵阳市飞云大道东段 299号



的管理体系已经过审核,并被证明符合下述要求

ISO 14001:2015

所涉及的活动范围覆盖

不间断电源和风能变流器的制造

该证书的有效期自 2020年 01月 23日至 2023年 01月 22日 并须经过符合要求的监督审核保持有效 持续认证至少在证书失效前60天执行 版本号 4. 初始注册日期 2017 年 01 月 23 日






SGS United Kingdom Ltd 

HC SGS 14001 2015 0118

第1页 共1页



0005



本文件由本公司根据公布在其网站 www.sgs.com/terms\_and\_conditions.htm 中的认证服务通用条款颁发。提请注意其中已确定的责任范围,赔偿 和司法管辖事项。本文件的真实性可在网站 https://www.sgs.com/en/certified-clients-and-products/certified-client-directory 中核 实。任何未经授权的对此文件的内容或外观的变更、伪造或篡改皆属

非法, 违反者将会被依法追诉。



Certificate CN16/21298

The management system of

## Vertiv Tech (Mianyang) Co., Ltd.

Business Registration Address: No. 299, East Feiyun Avenue, Mianyang, Sichuan, P.R. China Business Operation Address: No. 299, East Feiyun Avenue, Mianyang, Sichuan, P.R. China

has been assessed and certified as meeting the requirements of

ISO 14001:2015

For the following activities

Manufacture of Uninterrupted Power Supply and Wind Power Converter

This certificate is valid from 23 January 2020 until 22 January 2023 and remains valid subject to satisfactory surveillance audits.

Recertification audit due a minimum of 60 days before the expiration date Issue 4. Certified since 23 January 2017



Authorised by

HE

SGS United Kingdom Ltd
Rossmore Business Park Ellesmere Port Cheshire CH65 3EN UK
t +44 (0)151 350-6666 f +44 (0)151 350-6600 www.sqs.com

HC SGS 14001 2015 0118

Page 1 of 1







This document is issued by the Company subject to its General Conditions of Certification Services accessible at www.sgs.com/terms\_and\_conditions.htm.

Attention is drawn to the limitations of liability, indemnification and jurisdictional issues established therein. The authenticity of this document may be verified at http://www.sgs.com/en/certified-clients-after-products/certified-client-directory. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent certified and the fullest extent certified at the full extent certified at