



FRONT VIEW



REAR VIEW



SIDE VIEW

- | | |
|---|--|
| ① ESC/MUTE BUTTON | ⑥ AC INPUT. C14 |
| ② NAVIGATION BUTTONS | ⑦ EPO SWITCH |
| ③ ENTER/POWER BUTTON | ⑧ USB COMMUNICATION PORT |
| ④ SNMP INTELLIGENT SLOT. NETWORK COMMUNICATIONS CARD OPTIONAL | ⑨ PROGRAMMABLE OUTPUT RECEPTACLES. C13 |
| ⑤ INPUT CIRCUIT BREAKER. 8A | ⑩ NON-PROGRAMMABLE OUTPUT RECEPTACLES. C13 |

NOTES:

- UNIT DIMENSIONS (WxDxH): 17.2" x 20.1" x 1.7" (1U)
(438mm) x (510mm) x (44mm)
- UNIT WEIGHT: 35.5lbs (16.1kg)
- SHIPPING DIMENSIONS (WxDxH): 22.4" x 27.6" x 7.9"
(570mm) x (700mm) x (200mm)
- SHIPPING WEIGHT: 51.6lbs (23.4kg)
- MINIMUM AIRFLOW CLEARANCE IS 4.0" (100mm)
FRONT AND REAR.

DRAWN BY B. LAY	SHEET NO. 1 OF 1
CHK BY L. JOHNSON	ECN NO.
REF. DWG.	ORDER NO.

OUTLINE DRAWING
LIEBERT EDGE 1000VA 1U
230VAC RACK UPS

DWG. NO. EDGE_1000IRT1U_OD	DATE 4/27/20	REV. # 0	1050 DEARBORN DRIVE P.O. BOX 29186 COLUMBUS, OHIO 43229
-------------------------------	-----------------	-------------	---

FILE NAME: I:\dpgeng\EDGE\Submittals\EDGE_1000IRT1U_OD

