






FRONT VIEW



REAR VIEW



SIDE VIEW

- | | |
|---|---|
| ① ESC/MUTE BUTTON | ⑦ EXTERNAL BATTERY COMMUNICATION CONNECTOR |
| ② NAVIGATION BUTTONS | ⑧ USB COMMUNICATION PORT |
| ③ ENTER/POWER BUTTON | ⑨ EPO SWITCH |
| ④ INPUT CIRCUIT BREAKER. 10A | ⑩ SNMP INTELLIGENT SLOT. NETWORK COMMUNICATIONS CARD OPTIONAL |
| ⑤ AC INPUT. C14 | ⑪ PROGRAMMABLE OUTPUT RECEPTACLES. C13 |
| ⑥ EXTERNAL BATTERY POWER CONNECTOR. USES GXT5-EBC48VRT2U. | ⑫ NON-PROGRAMMABLE OUTPUT RECEPTACLES. C13 |

NOTES:

- UNIT DIMENSIONS (WxDxH): 17.2" x 20.1" x 3.4" (2U)
(438mm) x (510mm) x (86mm)
- UNIT WEIGHT: 47.4lbs (21.5kg)
- SHIPPING DIMENSIONS (WxDxH): 22.2" x 27.6" x 9.4"
(565mm) x (700mm) x (240mm)
- SHIPPING WEIGHT: 65.3lbs (29.6kg)
- MINIMUM AIRFLOW CLEARANCE IS 4.0" (100mm)
FRONT AND REAR.

DRAWN BY B. LAY	SHEET NO. 1 OF 1
CHK BY L. JOHNSON	ECN NO.
REF. DWG.	ORDER NO.

OUTLINE DRAWING
LIEBERT EDGE 1500VA 2U
230VAC RACK UPS

DWG. NO. EDGE_1500IRT2U_OD	DATE 4/28/20	REV. # 0	1050 DEARBORN DRIVE P.O. BOX 29186 COLUMBUS, OHIO 43229
-------------------------------	-----------------	-------------	---

FILE NAME: I:\dpgeng\EDGE\Submittals\EDGE_1500IRT2U_OD

