






FRONT VIEW



REAR VIEW



SIDE VIEW

- | | |
|---|---|
| ① ESC/MUTE BUTTON | ⑦ SNMP INTELLIGENT SLOT. NETWORK COMMUNICATIONS CARD OPTIONAL |
| ② NAVIGATION BUTTONS | ⑧ USB COMMUNICATION PORT |
| ③ ENTER/POWER BUTTON | ⑨ EPO SWITCH |
| ④ INPUT CIRCUIT BREAKER. 16A | ⑩ EXTERNAL BATTERY COMMUNICATION CONNECTOR |
| ⑤ AC INPUT. C20 | ⑪ NON-PROGRAMMABLE OUTPUT RECEPTACLES. C13 |
| ⑥ EXTERNAL BATTERY POWER CONNECTOR. USES GXT5-EBC72VRT2U. | ⑫ PROGRAMMABLE OUTPUT RECEPTACLES. C13 |
| | ⑬ NON-PROGRAMMABLE OUTPUT RECEPTACLE. C19 |

NOTES:

- UNIT DIMENSIONS (WxDxH): 17.2" x 24.8" x 3.4" (2U)
(438mm) x (630mm) x (86mm)
- UNIT WEIGHT: 74.5lbs (33.8kg)
- SHIPPING DIMENSIONS (WxDxH): 23.6" x 31.5" x 9.4"
(600mm) x (800mm) x (240mm)
- SHIPPING WEIGHT: 91.7lbs (41.6kg)
- MINIMUM AIRFLOW CLEARANCE IS 4.0" (100mm)
FRONT AND REAR.

DRAWN BY B. LAY	SHEET NO. 1 OF 1
CHK BY L. JOHNSON	ECN NO.
REF. DWG.	ORDER NO.

OUTLINE DRAWING
LIEBERT EDGE 3000VA 2U
230VAC RACK UPS

DWG. NO. EDGE 3000IRT2U_OD	DATE 4/28/20	REV. # 0	1050 DEARBORN DRIVE P.O. BOX 29186 COLUMBUS, OHIO 43229
-------------------------------	-----------------	-------------	---

FILE NAME: I:\dpgeng\EDGE\Submittals\EDGE_3000IRT2U_OD

