






FRONT VIEW



REAR VIEW



SIDE VIEW

- | | |
|---|---|
| ① ESC/MUTE BUTTON | ⑦ SNMP INTELLIGENT SLOT. NETWORK COMMUNICATIONS CARD OPTIONAL |
| ② NAVIGATION BUTTONS | ⑧ USB COMMUNICATION PORT |
| ③ ENTER/POWER BUTTON | ⑨ EPO SWITCH |
| ④ INPUT CIRCUIT BREAKER. 16A | ⑩ EXTERNAL BATTERY COMMUNICATION CONNECTOR |
| ⑤ AC INPUT. C20 | ⑪ NON-PROGRAMMABLE OUTPUT RECEPTACLES. C13 |
| ⑥ EXTERNAL BATTERY POWER CONNECTOR. USES GXT5-EBC72VRT2U. | ⑫ PROGRAMMABLE OUTPUT RECEPTACLES. C13 |
| | ⑬ NON-PROGRAMMABLE OUTPUT RECEPTACLE. C19 |

NOTES:

- UNIT DIMENSIONS (WxDxH): 17.2" x 19.3" x 5.1" (3U)
(438mm) x (490mm) x (131mm)
- UNIT WEIGHT: 74.1lbs (33.6kg)
- SHIPPING DIMENSIONS (WxDxH): 22.4" x 26.4" x 11.1"
(570mm) x (670mm) x (282mm)
- SHIPPING WEIGHT: 92.8bs (42.1kg)
- MINIMUM AIRFLOW CLEARANCE IS 4.0" (100mm)
FRONT AND REAR.

DRAWN BY B. LAY	SHEET NO. 1 OF 1
CHK BY L. JOHNSON	ECN NO.
REF. DWG.	ORDER NO.

OUTLINE DRAWING
LIEBERT EDGE 3000VA 3U
230VAC RACK UPS

DWG. NO. EDGE_3000IRT3U_OD	DATE 4/28/20	REV. # 0	1050 DEARBORN DRIVE P.O. BOX 29186 COLUMBUS, OHIO 43229
-------------------------------	-----------------	-------------	---

FILE NAME: I:\dpgeng\EDGE\Submittals\EDGE_3000IRT3U_OD

