PowerIT

Product Approval

Part Number:	VP7UA005 -- JMUU5MIZ1-36CF13-8HW56A9DXX-S
	Switched, Outlet Level Monitoring
Power Configuration:	80A, 240/415V WYE, 57.6kW
Physical Configuration:	66in / 1683mm Vertical
Product Summary:	rPDU, Switched Outlet Level Monitoring, 80A, 200-240/346-415V WYE, 57.6kW, Vertical, (36) Combination C13/C19, Hardwired, Black Powder Coat.

Specifications and Options

Monitoring	Input and Outlet power monitoring with Outlet switching. Circuit/Breaker current monitoring. Environmental monitoring via optional remote sensors. Daisy chain Ethernet connectivity. Local high visibility display.
Input Monitoring	Total Unit Monitoring (kWh, W, VA, PF) Phase (A, B, C) Monitoring (kWh, W, VA, PF, V, A) Power Measurements Compliant with ANSI C12.1 and IEC 62053-21 at 1% Accuracy Class Requirements
Circuit Monitoring	Circuit / Breaker Monitoring (A) Circuit/Breaker Current Measurements Independently Tested and Verified at 1% Accuracy
Outlet Monitoring	Outlet Monitoring (kWh, W, VA, PF, V, A) Power Measurements Compliant with ANSI C12.1 and IEC 62053-21 at 1% Accuracy Class Requirements.
Remote Power Management	Individual Outlet Switching with Optional User Defined Time Delays and Sequential Power-up
Quantity Of Inputs	1
Voltage	200-240/346-415V WYE
Current	80A x 3 Phase WYE
VA per Input (Load Capacity)	57.6kVA (240V)
Frequency	50/60Hz
Over Current Protection	(18) 20A Single Pole Magnetic Breakers (10kAIC Rated)
Switch	Breaker/Switch Combination
LCD Touchscreen Display / Auto Oriented	Yes
Indicators - LED(s)	36
Power Entry Location	Top End
Hardwired	Removable Panel - Conduit Connection Access for Input & Output
Receptacle/Socket Type #1	Combination C13/C19 (Outlet 1 Opposite Input)
- Quantity on Face	36

Confidential. Property of Vertiv.

Specifications and Options Cont.

- Quantity per Breaker	2
- Quantity per Phase	12
- Circuit Color ID	18 Circuit = Orange, Green, Blue, Light Orange, Light Green, Light Blue, Orange, Green, Blue, Light Orange, Light Green, Light Blue, Orange, Green, Blue, Light Orange, Light Green, Light Blue
- Style	Banks of 6
- Voltage per Receptacle/Socket	240V (L-N)
Network Connection	Dual 10/100/1000Mbps Ethernet
Protocols Supported	DHCP, HTTP, HTTPS, IPv4, IPv6, LDAP, NTP, RADIUS, RSTP, SSH, SMTP, SNMP (v1/v2c/v3), Syslog, TACACS+, Modbus TCP
Data Access Formats	CSV datalog, JSON API, JSON datalog
USB Support	Yes
IP Reset Button	Yes
Hard Reboot Button	Yes
Serial Connection	RS232 via RJ45
Remote Sensor RJ Connection Jacks	1 (Supports up to 16 Sensors)
Maximum Operating Temperature	60C / 140F
Heavy Steel - Powder Coat Finish	Black
Configuration	Zero U
7938 Vertical Mounting Bracket Kit	Yes
Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in / 1556mm and 1645mm
Product Warranty	5-year limited warranty
Certification/Agency Approvals	CE Marked
Certification/Agency Approvals	UL & c-UL Listed 62368-1
Certification/Agency Approvals	UKCA Marked
Certification/Agency Approvals	Complies with IEC 62368-1 (DOC Available)
Certification/Agency Approvals	Complies with EN 55032 and EN 55035
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	RCM Mark (EMC Only)
Certification/Agency Approvals	China RoHS
Certification/Agency Approvals	FCC Part 15 Class B Conformance
Chassis Dimensions (LxWxD)	66.25in x 3.8in x 3.0in / 1683mm x 97mm x 76mm
Shipping Weight	24 lbs (9.98 kg)

Confidential. Property of Vertiv.

Revised: 1/28/2026

To ensure customer satisfaction with this unit, prior to acceptance of an order, Vertiv requires a signature of approval for the specification above and the terms below.

PLEASE NOTE: THESE UNITS ARE …NON-RETURNABLE…NON REFUNDABLE…NON-CANCELLABLE

Company: _____

Printed Name: _____ Title: _____

Authorized Customer Signature: _____ Date: _____

Technical claims listed depend on a series of technical assumptions. Your experience with these products may differ if you operate the products in an environment which is different from the technical assumptions. Vertiv reserves the right to modify these specifications without prior notice. Vertiv makes no warranties, express or implied, on the information contained in this document.

Confidential. Property of Vertiv.