

OVERVIEW

Upgradeable Metered rPDUs provide reliable power distribution to critical IT equipment within a rack or cabinet while delivering a view of real-time view of power usage from a local LED display.

Benefits

- With the Geist Upgradeable hot-swap technology, users may easily transform metered rPDUs to monitored rPDUs with the addition of the appropriate Interchangeable Monitoring Device (IMD).
- Avoid accidental overloads when deploying or moving critical server equipment with instant access to power consumption metrics on the local digital display.
- Gather comprehensive power data at the palm of your hand with the use of the Vertiv VLC mobile app.
- Every unit is 100% tested for reliability and functionality.
- Simple and convenient configuration options for cord lengths and chassis colors.



Part #: G110098

Model Number: MG01D4W1-36CF13-3PS56B2A10-S-A

Category: Metered

Sub Category: Upgradeable

Power Configuration: 32A, 230/400V WYE, 22.0kW

Physical Configuration: 70in / 1778mm, Vertical

Product Summary:

rPDU, Metered Upgradeable, 32A, 230/400V WYE, 22.0kW, Vertical, (36) Combination C13/C19, 10ft power cord with 3P+N+E (IP44), Black Powder Coat.

Monitoring:

Input Phase and Circuit/Breaker current monitoring. Local high visibility LED display. Input and per Phase power monitoring available via VLC using the Vertiv rPDU Scanner app.

Plug Form:



3P+N+E (IP44)

Receptacle:



Combination C13/C19
(Quantity: 36)

Chassis Color Options:



To discuss color options, contact your local sales representative.

Product Specification and Options

System Features

Monitoring

Input Phase and Circuit/Breaker current monitoring. Local high visibility LED display. Input and per Phase power monitoring available via VLC using the Vertiv rPDU Scanner app.

Monitoring Level 1	Aggregate - Total Unit Monitoring (kWh, W, VA, PF)
	Power Measurements Compliant with ANSI C12.1 and IEC 62053-21 at 1% Accuracy Class Requirements
Monitoring Level 2	Phase (A, B, C) Monitoring (kWh, W, VA, PF, V, A)
	Power Measurements Compliant with ANSI C12.1 and IEC 62053-21 at 1% Accuracy Class Requirements
Monitoring Level 3	Circuit / Breaker Monitoring (A)
	Circuit/Breaker Current Measurements Independently Tested and Verified at 2% Accuracy
VLC Support	Yes
Quantity Of Inputs	1
Voltage	200-240/346-415V WYE
Current	32A x 3 Phase WYE
VA per Input (Load Capacity)	22.0kW (230V)
Frequency	50/60Hz
Over Current Protection	(6) 16A Single Pole Magnetic Breakers (10kAIC Rated)
Switch	Breaker/Switch Combination
Scrolling / Rotatable Digital Display	Yes
Power Cable Wire Gauge	6mm² H07RN-F
Power Cable Length	10ft / 3m
Power Entry Location	Bottom Front
Plug Type	IEC60309 3P + N + E, 32A, 230/400V, Splashproof IP44
Alternating Phase/Circuits	Yes
Receptacle/Socket Type #1	Combination C13/C19
- Quantity on Face	36
- Quantity per Breaker	6
- Quantity per Phase	12
- Circuit Color ID	6 Circuit = Orange, Green, Blue, Light Orange, Light Green, Light Blue
- Style	Banks of 6
- Voltage per Receptacle/Socket	230V
Internal RMS Voltage Sensor	Yes
Internal RMS Current Sensor	Yes
Maximum Operating Temperature	60C / 140F
Heavy Steel - Powder Coat Finish	Black
Configuration	Zero U
7938 Vertical Mounting Bracket Kit	Yes
Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in / 1556mm and 1645mm
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	CE Marked
Certification/Agency Approvals	Complies with EN 55032 and EN 55024
Certification/Agency Approvals	RoHS Compliant

Certification/Agency Approvals	RCM Mark (EMC Only)
Certification/Agency Approvals	Complies with IEC 62368-1 (DOC Available)
Certification/Agency Approvals	China RoHS
Chassis Dimensions (LxWxD)	70in x 2in x 2.25in / 1778mm x 51mm x 58mm
Shipped Weight	17lbs (7.71kg)