AVOCENT® SV300 SERIES DESKTOP KVM SWITCHES

Connect and control your entire desktop



OVERVIEW

KEY FEATURES

- Support for DVI-I, HDMI 1.4 and DP1.2 in single and dual head models supporting high resolutions up to UHD 4K
- Mobile High-Definition Link

 (available on 4-port HDMI models)
 enables viewing of media from mobile devices on connected
 HDMI monitors

BENEFITS

- Access from two to four computers using a single keyboard, monitor and mouse
- Managed copy and paste of files and text between sources
- Mouse and keyboard switching via emulation assures zero delay in switching time between connected sources
- Easily switch audio and USB 3.0 (select models) peripherals independently of KVM
- Three USB 3.0 ports on the front of the 240 KVMs enable easy connectivity to external USB devices, quick data transfer and high speed charging of mobile devices





SPECIFICATIONS			
MODEL NUMBER	SV340	SV340H	SV340D
System Connections	4	4	4
Console Connections	2	2	2
Display Support	DVI-I	HDMI 1.4	DP1.2
Max Resolution	UHD 4K - 3840X2160 @ 30 Hz (via DVI to HDMI cable)	Supporting UHD 4K resolutions up to 3840x2160 @ 30Hz	Supporting UHD 4K resolutions up to 3840x2160 @ 30Hz
	DVI dual-link - 2560X1600 @ 60 Hz (via DVI cable)		

SUPPORTED HARDWARE	
Console Peripherals	USB Type-A
Computer Peripherals	USB Type-B
Dedicated Peripheral Port	3 x USB Super Speed
Audio Input/Output	2 x 3.5mm stereo female
MECHANICAL	
Enclosure	Steel with Plastic Front Panel
Dimensions WxDxH	342x125x56mm
	13.7x5x2.2 inches
Weight	1.85 kg (3.7 lbs)
POWER	
Power Requirements	35W Max Internal
AC Input Voltage	100 to 240V AC
ENVIRONMENTAL	
Operating Temperature	32° to 104° F; 0° to 40° C
Storage Temperature	-4° to 140° F; -20° to 60° C
Humidity	0-80% RH, non-condensing
Certifications	CE, RCM, FCC class B, VCCI, TUV US, TUV Canada



3 Years Advance Replacement

SV340D

Ordering Details

Warranty

MODEL NUMBER	CABLE OPTIONS-LENGTH	CABLE DESCRIPTION
SV340	CBL0120 - 6 ft., CBL0121 - 10 ft.	CABLE ASSY, 2-DVI-I/1-USB/2-AUDIO
SV340D	CBL0124 - 6 ft.	2-DISPLAYPORT/1-USB/2-AUDIO
SV340H	CBL0128 - 6 ft., CBL0129 - 10 ft.	CABLE ASSY, 2-HDMI/1-USB/2-AUDIO

VertivCo.com | Vertiv Headquarters, 1050 Dearborn Drive, Columbus, OH, 43085, USA

© 2018 Vertiv Co. All rights reserved. Vertiv and the Vertiv logo are trademarks or registered trademarks of Vertiv Co. All other names and logos referred to are trade names, trademarks or registered trademarks of their respective owners. While every precaution has been taken to ensure accuracy and completeness herein, Vertiv Co. assumes no responsibility, and disclaims all liability, for damages resulting from use of this information or for any errors or omissions. Specifications are subject to change without notice.

AV-11413 (R01/18)