

Vertiv™ Wall Mount Outdoor

NEMA 4-rated wall mount for outdoor use



Highlights

Ideal for outdoor spaces, The Vertiv™ Wallmount Outdoor provides secure, organized housing for critical 19" equipment. The double-swing design offers front and rear access while protecting internal components with a locking center section and weather-sealed construction. With optional HVAC or fan/filter configurations, cable-friendly mounting rails, and lift-off hinges for easy setup, it's a rugged, space-saving solution built to meet NEMA 4 standards.



Vertiv™ Wall Mount Outdoor

Typical applications

Built for outdoor or exposed installations where access, serviceability and protection meet.

Ideal for:

- Outdoor telecom or wireless equipment
- Utility pole or wall-mounted network nodes
- Fiber distribution and remote site enclosures
- Edge or IoT deployments in exposed or semi-protected environments



Dual swing access

Front and rear sections swing open for full service access



Weather-tight enclosure

NEMA Type 4 rated with welded steel frame and rain-shrouded knockouts




Pole or wall mountable

Designed for versatile mounting options (wall or pole) in outdoor settings



Popular configurations



Specifications

Using the attribute chart below, select a Base Unit and Airflow unit to designate a standard Vertiv™ Wall Mount Outdoor

Base Unit	Airflow	Example
BXWM04-xxUxx-GY-SH-	xxxxx	Configured Wall Mount Outdoor
BXWM04-11U26-GY-SH- (11U, 26"D)	00000 (none)	BXWM04-11U32-GY-SH-AC010
BXWM04-11U32-GY-SH- (11U, 32"D)	FFKN4 (Fan/Filter Kit: 28 CFM, 115V fan w/ 6', 5-15P cord; includes exhaust filter and two rain shrouds (RAL 7035 Gray) ¹	Wall Mount Outdoor, (11U, 32"D, Gray, Swing Handle, 1000 BTU AC)
BXWM04-18U32-GY-SH- (18U, 32"D)	AC010 (1000 BTU AC; 115V; 300W; SNMP Level 3; 6', 5-15P cord; Model 1830801) ²	
BXWM04-25U32-GY-SH- (25U, 32"D)	AC020 (2000 BTU AC; 115V; 600W; SNMP Level 3; 6', 5-15P cord; Model 1830803) ²	
	AC041 (4100 BTU AC; 115V; 1200W; SNMP Level 3; 6', 5-15P cord; Model 1830806) ³	

¹One fan/filter kit included; 36" and 48" wall mounts can accept an additional kit (purchased separately); ²1000 and 2000 BTU AC for use with 24" and 36"H; ³4100 BTU AC for use with 48"H

Vertiv.com | Vertiv Headquarters, 505 N Cleveland Ave, Westerville, OH 43082, USA

© 2025 Vertiv Group Corp. All rights reserved. Vertiv™ and the Vertiv logo are trademarks or registered trademarks of Vertiv Group Corp. All other names and logos referred to are trade names, trademarks or registered trademarks of their respective owners. While every precaution has been taken to ensure accuracy and completeness here, Vertiv Group Corp. assumes no responsibility, and disclaims all liability, for damages resulting from use of this information or for any errors or omissions. Specifications, rebates and other promotional offers are subject to change at Vertiv's sole discretion upon notice.