

SmartCloset[™]

Complete Solution Designed to Protect IT & Network Closets



Systemic Challenges at the Edge

IT teams with limited resources face new challenges when supporting distributed IT environments such as IT and Network Closets.



Remote Visibility Across Multiple Sites



Reliability and Unplanned Downtime



Facilities not Designed for IT Infrastructure



The Vertiv[™] SmartCloset[™] is Designed to Reduce Complexity and Simplify Deployment.



Vertiv[™] SmartCloset[™]

Purpose-built rack solution for Network Closets and Distributed IT

Fast

The SmartCloset[™] is stocked to enable rapid deployment.

Seamless

Pre-validated by Vertiv to ensure easy deployment.

Scalable

Standardized components provide a scalable solution.



Secure IT Rack

Vertiv[™] VR Racks provide a secure, organized, and efficient place to manage critical IT infrastructure and enable edge locations to meet power and space requirements.



Emergency backup power

Vertiv[™] Liebert[®] PSI5 and Vertiv[™] Liebert[®] GXT5 UPS provide market-leading efficiency in line-interactive and online double-conversion topologies for power protection and voltage regulation. Also available with Lithium-ion UPS technology.



Networking cards enable integration of the UPS into monitoring systems, allowing users to manage system status and alarms 24/7 anywhere in the world.

Environmental Monitoring

Help protect your critical IT infrastructure by strategically monitoring the temperature, humidity, and dew point within the network closet environment. Sensors are available only for some models.



Integrated power distribution

Vertiv[™] Geist[™] rPDUs give unmatched reliability, ultimate versatility, and peace of mind that the last link in your power chain is secure. Rack PDU's are available only for select models.

Your investment protected with a system level warranty from Vertiv

We are here to support you with service solutions for your critical infrastructure and to ensure that your vital applications always work. The Vertiv SmartCloset has a full suite of service offerings to help protect your investment and your business.



Assembly and Installation Required

Why piece together products by yourself when you can find a readily available solution that has already been curated by industry experts?

Vertiv[™] SmartCloset[™]

Options for Any Budget





Vertiv[™] VR Rack

Each Vertiv[™] SmartCloset[™] includes a Vertiv VR Rack. The rack is designed to work with a wide variety of equipment including servers, storage, switches, routers, and other devices.

Each Rack Includes:

- Single 77% perforated locking front door.
- Split 77% perforated locking rear doors.
- 2 pair split locking side panels.
- High density cable entry top cover (2000 Cat 6 cables).
- 2 sets of 19" EIA Rails.
- 2 full height rack PDU Mounting / cable management brackets (one per side).
- Low profile casters and leveling feet.
- Baying brackets.
- Bolt down brackets.
- Hardware includes (50 each M6 cage nuts and screws), Cage nut installation tool, edge protection for top panel cable entry, T30 / Phillips L key, T30 extension driver.
- Keys.



Scan to Learn More



High Density Cable Entry Top Panel

Removable openings for cable entry — ready for front / rear cabling. Can accommodate over 2000 Cat 6 cables.

Frame

More usable depth compared to similar sized rack.



Doors

Single and split 77% perforated doors providing maximum airflow. Lift off hinges for easy removal, and field reversibility.



Tool-less Cable Management

Requires just inserting and twisting the toolless accessories on 19" vertical mounting rail, or the PDU / cable management brackets.

H			-	
Γ	Γ	Γ	П	

Integrated 19" Rail Alignment

Ensures 19" rails are positioned correctly without measuring.



Split Locking Side Panels

For quick and easy installation and maintenance. Locks provide security.

Leveling Feet

Accessible from the top of the frame for easy adjustment.

Cable Management Accessories

Each SmartCloset™ includes cable management accessories to aid in optimal organization for efficient operation and increased reliability.

Velcro Straps



Part Number: VRA1005 Quantity: (10)

Vertical Cable Managers

Part Number: VRA1014 Quantity: (2)



Optional Rack Accessories

Blanking Panels

A frequently overlooked component in air flow management, blanking panels allow you to close unused U space within the rack while promoting proper airflow to IT equipment.

Part Number	Description
VRA2000	1U 19" Black Plastic Tool Less Airflow Blanking Panel (Qty. 10)
VRA2001	1U 19" Black Plastic Tool Less Airflow Blanking Panel (Qty. 200)
VRA2002	19" Sheet Metal Airflow Blanking Panel Kit (1U, 2U, 4U, 8U) Black (Qty. 1 ea. Size)
VRA2003	1U 19" Sheet Metal Airflow Blanking Panel Kit Black (Qty. 2) Black

Door Locks

Locking rack handle for increased security.

A6023 Combination Lock Handle (Qty. 2)

Cable Pass Through Brush Kit

Part Number	Description
VRA2006	Cable Pass Through Brush Kit for Top Panel (Qty. 8)





VRA2002







Scan to Find Other Accessories Vertiv offers a comprehensive portfolio of rack accessories for cable management, airflow management, blanking panels, mounting, and physical security.



UPS Battery Backup

Each Vertiv[™] SmartCloset[™] includes a network and server grade UPS and network card for power protection and remote management. Choose one from the following options:

Line-Interactive UPS

- Surge protection
- Battery backup
- Automatic voltage regulation
- Network Card (IS-UNITY-SNMP)
- 4-6ms transfer-time to battery

Vertiv™ Liebert® PSI5

3kVA 120VAC



Network Card Included (IS-UNITY-SNMP) Scalable Runtime Supported

Vertiv™ Liebert® PSI5 Lithium-Ion

3kVA 120VAC



Network Card Included (IS-UNITY-SNMP) Scalable Runtime Not Supported

Online Double-Conversion UPS

- Surge protection
- Battery backup
- Automatic voltage regulation
- Network Card (RDU101)
- + Zero transfer-time to battery
- + Frequency Regulation

Vertiv™ Liebert® GXT5

5kVA 208VAC or 3kVA 120VAC



Network Card Included (RDU101) Scalable Runtime Supported

Vertiv[™] Liebert[®] GXT5 Lithium-Ion 3kVA 120VAC



Network Card Included (RDU101) Scalable Runtime Supported

Lithium-ion Outperforms VRLA



Last up to 3x Longer



Resilient To Heat



Higher Power Density



Lower TCO

Scan here to learn more about lithium-ion UPS



Power Distribution

Select SmartCloset[™] models include a rack PDU to provide reliable power distribution and enable remote monitoring with automated alerts. Choose one from the following options:



- Monitored
- Switched

8



Environmental Monitoring

SmartCloset models with a Switched PDU also include an Environmental Sensor that monitors temperature, humidity, and dew point. Scan here to use

our PDU Finder

Part Number: GTHD



Free Power Management Software

Vertiv[™] Power Insight





Scan for details

Vertiv Power Insight is a web-based solution for managing and monitoring up to 100 Vertiv[™] UPSs and Vertiv[™] rPDUs that provides a quick way to safely shutdown IT devices based on user-configured parameters.

Easy to Connect and Control

- Free download from Vertiv.com.
- On-premise and remote UPS and rPDU monitoring for 100 devices with notification and control for Network based devices.
- Auto-discovery of Vertiv[™] Liebert[®] devices for ease of installation and configuration.

Intelligently Controlled Shutdown

- Automatic Shutdown protection for physical and virtual servers.
- VMWare vCenter / vSphere Integration out of the box for virtual compute management.
- Sequential server shutdown function to extend runtime for the most critical loads.

Single Pane of Glass View

- Dashboard views of key data points such as capacity load percentage, output current, battery percentage charge and battery time remaining.
- Alarm views with data that can be sorted or filtered.
- Alarm notifications via email, SMS and on-screen icons.
- Summarized data of individual devices.

Optional Remote Monitoring Software

Vertiv[™] Environet[™] Alert





Vendor-neutral data center infrastructure monitoring software helps prevent downtime and reduces operational costs.

Vendor Neutral

• Supports your entire fleet of devices for comprehensive visibility in one platform.

Scalable Platform

Plans based on number of devices to support any size deployment and budget.

Customizable Dashboard

• Choose your own views to focus on the data you need the most.

Connect Operations

• Connect your DCIM and BMS to get one complete picture of your operations.

Scan for details

Vertiv[™] LIFE[™] Remote Diagnostic Services for Rapid Response



Uptime assurance

- Continuous monitoring for early detection of trends and operating anomalies.
- Analysis and interpretation of alarm and status messages.

Rapid incident response

- Automatic transmission of data for analysis.
- Concurrent diagnosis and dispatch of engineer to site.
- Shipment of parts for corrective maintenance.

Increased insight and ease of management

- Notification of operating conditions that may impact system health.
- Periodic trend and analysis reports.
- Integration of remote and on-site services to ensure business continuity.

Power Assurance Package



Power Continuity Services



Comprehensive Protection

Vertiv's exclusive Power Assurance Package offers lifecycle power management for critical single-phase UPS systems, eliminating the concerns surrounding all aspects of UPS support.

- Available with Vertiv[™] Liebert[®] APS, Vertiv[™] Liebert[®] PSI and Vertiv[™] Liebert[®] GXT UPS products, from 500VA 10kVA.
- Installation and startup services.
- Five-year, hassle-free protection plan.
- Safe disposal of UPS/battery.
- 24x7 on-site emergency response.
- Parts and labor coverage.

Vertiv[™] Power Continuity Services is a complete line of battery and UPS replacement services for the Vertiv[™] Liebert[®] GXT and Vertiv[™] Liebert[®] PSI systems, commonly used at the edge of an IT network in small or remote sites. Three levels of services that help ensure continuous power for your vital applications:

- UPS restoration services provides a replacement UPS battery pack, shipped from Vertiv, ready for your IT resources to install.
- UPS refresh includes a replacement battery pack, installation and startup by our factory-authorized technicians, a wellness check, spent battery removal and disposal, optional two-year service contract, and optional remote services.
- UPS replacement gives you a new UPS with installation, startup, legacy equipment removal and disposal, an optional five-year protection plan, and optional remote services.



Other Accessories

Optional Accessories below are not included but may be purchased separately.

Vertiv[™] Geist[™] Rack Transfer Switch

Delivers redundant power to single-corded devices by automatically detecting loss of primary power and switching to the alternative power source in 4-8ms. Multiple configurations are available.





SCAN FOR DETAILS

Model number VA4N3100 is compatible with 5000VA 208VAC Vertiv™ SmartCloset™ models



Vertiv[™] Liebert[®] MicroPOD

Maintenance bypass and power distribution accessory allows manual transfer of connected equipment to utility power to enable scheduled maintenance without power disruption.

Zero-U Design

Mounts to rear of Vertiv™ Liebert® PSI5 or Vertiv™ Liebert® GXT5 UPS (3000VA and below) ٠







SCAN FOR DETAILS

Technical Specifications - Entry Models

Network Closet Bundle SKUs	VSC42NX30PLANN	VSC42NX30PLAMV	VSC42NX30PLASV	VSC42NX30PLINN	VSC42NX30PLIMV	VSC42NX30PLISV
System Specifications						
W x D x H, mm (in)	600 x 1100 x 2000 (23.6 x 43.3 x 78.6)	600 x 1100 x 2000 (23.6 x 43.3 x 78.6)	600 x 1100 x 2000 (23.6 x 43.3 x 78.6)	600 x 1100 x 2000 (23.6 x 43.3 x 78.6)	600 x 1100 x 2000 (23.6 x 43.3 x 78.6)	600 x 1100 x 2000 (23.6 x 43.3 x 78.6)
Weight, kg (lbs)	159 (350)	166.5 (367)	168 (371)	151 (334)	159 (350)	160 (354)
Static load / Dynamic load, kg (lbs)	1360 (3000) / 1022 (2250)					
U-Space (Usable)	40U	40U	40U	40U	40U	40U
rPDU Type	N/A	Monitored	Switched	N/A	Monitored	Switched
Usable Outlets, (rPDU)	N/A	(24) NEMA 5-20	(24) NEMA 5-20	N/A	(24) NEMA 5-20	(24) NEMA 5-20
UPS Topology	Line Interactive					
UPS Battery Chemistry	VRLA	VRLA	VRLA	Lithium-ion	Lithium-ion	Lithium-ion
Usable Outlets, (UPS)	(6) NEMA 5-20 (1) NEMA L5-30	(6) NEMA 5-20	(6) NEMA 5-20	(6) NEMA 5-20 (1) NEMA L5-30	(6) NEMA 5-20	(6) NEMA 5-20
Environmental Monitoring	N/A	N/A	Temperature Humidity Dew Point	N/A	N/A	Temperature Humidity Dew Point
Power Rating, VA	3000	3000	3000	3000	3000	3000
Max IT Load, Watts	2700	2700	2700	2700	2700	2700
Warranty and Service						
Standard Warranty	3-Year, System Level	3-Year, System Level	3-Year, System Level	5-Year, System Level	5-Year, System Level	5-Year, System Level
Bill of Material						
Rack	VR3100	VR3100	VR3100	VR3100	VR3100	VR3100
UPS	PSI5-3000RT120	PSI5-3000RT120	PSI5-3000RT120	PSI5-3000RT120LI	PSI5-3000RT120LI	PSI5-3000RT120LI
rPDU	N/A	VP8832	VP8932	N/A	VP8832	VP8932
Monitoring	IS-UNITY-SNMP	IS-UNITY-SNMP	IS-UNITY-SNMP	IS-UNITY-SNMP	IS-UNITY-SNMP	IS-UNITY-SNMP
Sensors	N/A	N/A	GTHD	N/A	N/A	GTHD
Rack Accessories	VRA1014 VRA1005	VRA1014 VRA1005	VRA1014 VRA1005	VRA1014 VRA1005	VRA1014 VRA1005	VRA1014 VRA1005



Technical Specifications - Value Models

Network Closet Bundle SKUs	VSC42NX30GLANN	VSC42NX30GLAMV	VSC42NX30GLASV	VSC42NX30GLINN	VSC42NX30GLIMV	VSC42NX30GLISV
System Specifications						
W x D x H, mm (in)	600 x 1100 x 2000 (23.6 x 43.3 x 78.6)	600 x 1100 x 2000 (23.6 x 43.3 x 78.6)	600 x 1100 x 2000 (23.6 x 43.3 x 78.6)	600 x 1100 x 2000 (23.6 x 43.3 x 78.6)	600 x 1100 x 2000 (23.6 x 43.3 x 78.6)	600 x 1100 x 2000 (23.6 x 43.3 x 78.6)
Weight, kg (lbs)	157 (346)	164 (362)	166 (366)	149 (329)	156 (345)	158 (349)
Static load / Dynamic load, kg (lbs)	1360 (3000) / 1022 (2250)					
U-Space (Usable)	40U	40U	40U	40U	40U	40U
rPDU Type	N/A	Monitored	Switched	N/A	Monitored	Switched
Usable Outlets, (rPDU)	N/A	(24) NEMA 5-20	(24) NEMA 5-20	N/A	(24) NEMA 5-20	(24) NEMA 5-20
UPS Topology	Online Double- Conversion					
UPS Battery Chemistry	VRLA	VRLA	VRLA	Lithium-ion	Lithium-ion	Lithium-ion
Usable Outlets, (UPS)	(6) NEMA 5-20 (1) NEMA L5-30	(6) NEMA 5-20	(6) NEMA 5-20	(6) NEMA 5-20 (1) NEMA L5-30	(6) NEMA 5-20	(6) NEMA 5-20
Environmental Monitoring	N/A	N/A	Temperature Humidity Dew Point	N/A	N/A	Temperature Humidity Dew Point
Power Rating, VA	3000	3000	3000	3000	3000	3000
Max IT Load, Watts	2700	2700	2700	2700	2700	2700
Warranty and Service						
Standard Warranty	3-Year, System Level	3-Year, System Level	3-Year, System Level	5-Year, System Level	5-Year, System Level	5-Year, System Level
Bill of Material						
Rack	VR3100	VR3100	VR3100	VR3100	VR3100	VR3100
UPS	GXT5-3000LVRT2UXL	GXT5-3000LVRT2UXL	GXT5-3000LVRT2UXL	GXT5LI- 3000LVRT2UXL	GXT5LI- 3000LVRT2UXL	GXT5LI- 3000LVRT2UXL
rPDU	N/A	VP8832	VP8932	N/A	VP8832	VP8932
Monitoring	RDU101	RDU101	RDU101	RDU101	RDU101	RDU101
Sensors	N/A	N/A	GTHD	N/A	N/A	GTHD
Rack Accessories	VRA1014 VRA1005	VRA1014 VRA1005	VRA1014 VRA1005	VRA1014 VRA1005	VRA1014 VRA1005	VRA1014 VRA1005

Technical Specifications - Premium Models

Network Closet Bundle SKUs	VSC42NX50GLANN	VSC42NX50GLAMV	VSC42NX50GLASV
System Specifications			
W x D x H, mm (in)	600 x 1100 x 2000 (23.6 x 43.3 x 78.6)	600 x 1100 x 2000 (23.6 x 43.3 x 78.6)	600 x 1100 x 2000 (23.6 x 43.3 x 78.6)
Weight, kg (lbs)	195 (429)	202 (446)	204 (449)
Static load / Dynamic load, kg (lbs)	37U	37U	37U
U-Space (Usable)	37U	37U	37U
rPDU Type	N/A	Monitored	Switched
Usable Outlets, (rPDU)	N/A	(36) C13, (6) C19	(24) C13, (4) C19
UPS Topology	Online Double-Conversion	Online Double-Conversion	Online Double-Conversion
UPS Battery Chemistry	VLRA	VLRA	VLRA
Usable Outlets, (UPS)	(2) NEMA L6-30 (2) NEMA L6-20	(1) NEMA L6-30 (2) NEMA L6-20	(1) NEMA L6-30 (2) NEMA L6-20
Environmental Monitoring	N/A	N/A	Temperature Humidity Dew Point
Power Rating, VA	5000	5000	5000
Max IT Load, Watts	4600	4600	4600
Warranty and Service			
Standard Warranty	3-Year, System Level	3-Year, System Level	3-Year, System Level
Bill of Material			
Rack	VR3100	VR3100	VR3100
UPS	GXT5-6KL630RT5UXLN	GXT5-6KL630RT5UXLN	GXT5-6KL630RT5UXLN
rPDU	N/A	VP8841	VP8941
Monitoring	RDU101 (factory installed in UPS)	RDU101 (factory installed in UPS)	RDU101 (factory installed in UPS)
Sensors	N/A	N/A	GTHD
Rack Accessories	VRA1014 VRA1005	VRA1014 VRA1005	VRA1014 VRA1005



Edge Infrastructure One-Stop Shop

Vertiv offers an unmatched portfolio of reliable infrastructure from trusted brands to simplify edge deployments.

Liebert[®] | Geist[™] | Avocent[®]



Want to Learn More?



Contact us: AskTheExpert@Vertiv.com

Scan to see our Edge portfolio





Vertiv.com | Vertiv Headquarters, 505 N Cleveland Ave, Westerville, OH 43082, USA

© 2023 Vertiv Group Corp. All rights reserved. Vertiv³⁴ and the Vertiv logo are trademarks or registered trademarks of Vertiv Group Corp. All other names and logos referred to are trade names, trademarks or registered trademarks of their respective owners. While every precaution has been taken to ensure accuracy and completeness here, Vertiv Group Corp. assumes no responsibility, and disclaims all liability, for damages resulting from use of this information or for any errors or omissions. Specifications, rebates and other promotional offers are subject to change at Vertiv's sole discretion upon notice.