



- ① 16 AMP OUTPUT CIRCUIT BREAKER SWITCH FOR IEC320-C19
- ② IEC320-C19 OUTPUT RECEPTACLE
- ③ 16 AMP OUTPUT CIRCUIT BREAKER SWITCH FOR IEC320-C19
- ④ IEC320-C19 OUTPUT RECEPTACLE
- ⑤ 16 AMP OUTPUT CIRCUIT BREAKER SWITCH FOR IEC320-C19

- ⑥ IEC320-C19 OUTPUT RECEPTACLE
- ⑦ 16 AMP OUTPUT CIRCUIT BREAKER SWITCH FOR IEC320-C19
- ⑧ IEC320-C19 OUTPUT RECEPTACLE
- ⑨ 10 AMP OUTPUT CIRCUIT BREAKER SWITCH FOR IEC320-C19
- ⑩ (4) IEC320-C13 OUTPUT RECEPTACLES

NOTES:

1. UNIT DIMENSIONS: 7.4" W x 5.7" H
(188mm) x (145mm)
2. UNIT WEIGHT: 4.4lbs (2.0kg)
3. SHIPPING DIMENSIONS: 11.9" H x 20.6" W x 8.7" D
(302mm) x (522mm) x (220mm)
4. SHIPPING WEIGHT: 6.6lbs (3.0kg)
5. ALL WIRING IS TO BE IN COMPLIANCE WITH NATIONAL AND LOCAL ELECTRICAL CODES.

DRAWN BY K. STACY	SHEET NO. 1 OF 1	POD PD2-200 WITH (4) IEC320-C19 AND (4) IEC320-C13 OUTPUT SOCKETS FOR GXT4-8000RT208 OR GXT4-10000RT208 UPS						
CHK BY G. FUNK	ECN NO.					DWG. NO. PD2-200	DATE 1/14/15	REV. # 1
REF. DWG.	ORDER NO.					1050 DEARBORN DRIVE P.O. BOX 29186 COLUMBUS, OHIO 43229		