



FRONT VIEW



REAR VIEW



SIDE VIEW

- ① LIEBERT INTELLISLOT PORT
- ② TERMINAL BLOCK COMMUNICATION
- ③ USB PORT
- ④ RS-485 PORT
- ⑤ RS-232 PORT
- ⑥ REPO CONNECTOR
- ⑦ EXTERNAL BATTERY CONNECTOR
- ⑧ L6-30R OUTPUT RECEPTACLES

- ⑨ PROGRAMMABLE L6-20R OUTPUT RECEPTACLES
- ⑩ OUTPUT CIRCUIT BREAKERS
- ⑪ OUTPUT CIRCUIT BREAKER FOR HARD WIRE AND NON-PROGRAMMABLE OUTLETS
- ⑫ MAINTENANCE BYPASS BREAKER FOR PROGRAMMABLE OUTLETS
- ⑬ MAINTENANCE BYPASS BREAKER FOR HARD WIRE AND NON-PROGRAMMABLE OUTLETS
- ⑭ HARDWIRED POWER INPUT AND OUTPUT CONNECTIONS
- ⑮ INPUT CIRCUIT BREAKER

NOTES:

1. UNIT DIMENSIONS (WxDxH): 430mm x 631mm x 217mm (5U)
(16.9") x (24.9") x (8.5")
2. UNIT WEIGHT: 68kg (149.9lbs)
3. SHIPPING DIMENSIONS (WxDxH): 646mm x 816mm x 520mm
(25.4") x (32.1") x (20.5")
4. SHIPPING WEIGHT: 92kg (202.8lbs)
5. MINIMUM AIRFLOW CLEARANCE IS 100mm (4.0") FRONT AND REAR.

DRAWN BY B. LAY	SHEET NO. 1 OF 1
CHK BY L. JOHNSON	ECN NO.
REF. DWG.	ORDER NO.

OUTLINE DRAWING
LIEBERT GXT5 5kVA
208VAC RACK/TOWER UPS

DWG. NO. GXT5-5KHV_OD	DATE 11/5/19	REV. # 1	1050 DEARBORN DRIVE P.O. BOX 29186 COLUMBUS, OHIO 43229
--------------------------	-----------------	-------------	---

FILE NAME: I:\dpgeng\GXT5\Submittals\A)Outline Dwg\GXT5-5KHV_OD

