



FOR DETAIL
SEE DRAWING
GXT5-DISPLAY

FRONT VIEW



SIDE VIEW



REAR VIEW

- | | |
|--|---|
| ① TERMINAL BLOCK COMMUNICATION | ⑩ L6-30R OUTPUT BREAKER |
| ② REPO (REMOTE EMERGENCY POWER OFF) | ⑪ (2) PROGRAMMABLE L6-20R OUTPUT RECEPTACLE |
| ③ RS232 | ⑫ PROGRAMMABLE L6-20R OUTPUT BREAKER |
| ④ LIEBERT INTELLISLOT PORT | ⑬ OUTPUT CIRCUIT BREAKER FOR HARDWIRED CONNECTIONS AND NON-PROGRAMMABLE OUTLETS |
| ⑤ RS485 | ⑭ MAINTENANCE BYPASS BREAKER FOR PROGRAMMABLE OUTLETS |
| ⑥ USB PORT | ⑮ MAINTENANCE BYPASS BREAKER FOR HARDWIRED CONNECTIONS AND NON-PROGRAMMABLE OUTLETS |
| ⑦ (2) DB9 PORTS (PARALLEL COMMUNICATION) | ⑯ HARDWIRED POWER INPUT AND OUTPUT CONNECTIONS |
| ⑧ EXTERNAL BATTERY CONNECTOR | ⑰ INPUT CIRCUIT BREAKER |
| ⑨ (2) L6-30R OUTPUT RECEPTACLE | |

NOTES:

- UNIT DIMENSIONS (WxDxH): 430mm x 631mm x 217mm (5U)
(16.9") x (24.9") x (8.5")
- UNIT WEIGHT: 72.9kg (160.7lbs)
- SHIPPING DIMENSIONS (WxDxH): 640mm x 890mm x 800mm
(25.2") x (35.0") x (31.5")
- SHIPPING WEIGHT: 108.6kg (239.4lbs)
- MINIMUM AIRFLOW CLEARANCE IS 4.0" (100mm) FRONT AND REAR.

DRAWN BY B. LAY	SHEET NO. 1 OF 1
CHK BY L. JOHNSON	ECN NO.
REF. DWG.	ORDER NO.

OUTLINE DRAWING
GXT5 8/10kVA
208VAC RACK/TOWER UPS

DWG. NO. GXT5-8K 10KHV_OD	DATE 5/13/20	REV. # 2	1050 DEARBORN DRIVE P.O. BOX 29186 COLUMBUS, OHIO 43229
------------------------------	-----------------	-------------	---

FILE NAME: T:\dpgeng\GXT5\Submittals\A)Outline Dwg\GXT5-8K_10KHV_OD

