



FRONT VIEW



REAR VIEW




SIDE VIEW

- ① TERMINAL BLOCK COMMUNICATION
- ② REPO (REMOTE EMERGENCY POWER OFF)
- ③ RS232
- ④ LIEBERT INTELLISLOT PORT
- ⑤ RS485
- ⑥ USB PORT
- ⑦ (2) DB9 PORTS (PARALLEL COMMUNICATION)
- ⑧ EXTERNAL BATTERY CONNECTOR
- ⑨ (3) C19 OUTPUT RECEPTACLES

- ⑩ (3) OUTPUT CIRCUIT BREAKERS FOR NON-PROGRAMMABLE C19 RECEPTACLES
- ⑪ PROGRAMMABLE C19 OUTPUT RECEPTACLE
- ⑫ (4) PROGRAMMABLE C13 OUTPUT RECEPTACLES
- ⑬ (2) OUTPUT CIRCUIT BREAKERS FOR PROGRAMMABLE RECEPTACLES
- ⑭ OUTPUT CIRCUIT BREAKER FOR HARDWIRED AND NON-PROGRAMMABLE OUTLETS
- ⑮ MAINTENANCE BYPASS BREAKER
- ⑯ HARDWIRED POWER INPUT AND OUTPUT CONNECTIONS
- ⑰ BYPASS CIRCUIT BREAKER
- ⑱ INPUT CIRCUIT BREAKER

NOTES:

1. UNIT DIMENSIONS (WxDxH): 430mm x 631mm x 217mm (5U)
(16.9") x (24.9") x (8.5")
2. UNIT WEIGHT: 71.9kg (158.5lbs)
3. SHIPPING DIMENSIONS (WxDxH): 600mm x 800mm x 520mm
(23.6") x (31.5") x (20.5")
4. SHIPPING WEIGHT: 94.0kg (207.2lbs)
5. MINIMUM AIRFLOW CLEARANCE IS 4.0" (100mm) FRONT AND REAR.

DRAWN BY B. LAY	SHEET NO. 1 OF 1	OUTLINE DRAWING GXT5 8/10kVA 230VAC RACK/TOWER UPS					
CHK BY L. JOHNSON	ECN NO.						
REF. DWG.	ORDER NO.						
			DWG. NO. GXT5-8K_10KI_OD	DATE 5/13/20	REV. # 2	1050 DEARBORN DRIVE P.O. BOX 29186 COLUMBUS, OHIO 43229	
FILE NAME: I:\dpeng\GXT5\Submittals\A\Outline Dwg\GXT5-8K_10KI_OD							

FILE NAME: I:\dpgeng\GXT5\Submittals\A\Outline Dwg\GXT5-8K_10KI_OD