



FRONT VIEW



REAR VIEW



SIDE VIEW

- ① INPUT POWER CORD: NEMA L5-20P WITH 10 FOOT ATTACHED CORD
- ② EXTERNAL BATTERY CABINET CONNECTOR
- ③ 20A INPUT BREAKER
- ④ RJ-45 DATA LINE CONNECTORS
- ⑤ INTELLISLOT PORT. NETWORK COMMUNICATIONS CARD OPTIONAL
- ⑥ EPO CONNECTOR
- ⑦ USB PORT
- ⑧ OUTPUT RECEPTACLES: 3 NEMA 5-15R ALWAYS ON
- ⑨ OUTPUT RECEPTACLES: 3 NEMA 5-15R PROGRAMMABLE GROUP
- ⑩ OUTPUT RECEPTACLE: NEMA L5-20R
- ⑪ ON/MUTE BUTTON
- ⑫ SELECT BUTTON
- ⑬ OFF/ENTER BUTTON

NOTES:

1. UNIT DIMENSIONS: 17.2" x 3.4" x 24.8" (438mm) x (86mm) x (630mm)
2. UNIT WEIGHT: 59.1lbs (26.8kg)
3. SHIPPING DIMENSIONS: 21.7" x 10.2" x 30.8" (550mm) x (258mm) x (782mm)
4. SHIPPING WEIGHT: 68.3lbs (31.0kg)
5. MINIMUM AIRFLOW CLEARANCE IS 4.0" (100.0mm) FRONT/REAR
6. FIXED RAIL KIT: INCLUDED
7. ALL SITE WIRING IS TO BE IN COMPLIANCE WITH NATIONAL AND LOCAL ELECTRIC CODES.
8. USES PSI5-72VBATT
9. INCLUDES L5-20R TO NEMA 5-20P ADAPTER.
10. UNIT INPUT: 100~125 VAC, 60/50HZ, 16A
11. UNIT OUTPUT: 100/110/115/120/125VAC, 60/50HZ, 1920VA/1920W, 15.4A, @125VAC INPUT OR 1920VA/1920W, 16A, @120VAC INPUT OR 1840VA/1840W, 16A, @115VAC INPUT OR 1632VA/1632W, 14.8A, @110VAC INPUT OR 1600VA/1600W, 16A, @100VAC INPUT

DRAWN BY B. LAY	SHEET NO. 1 OF 1
CHK BY B. HOCKENSMITH	ECN NO.
REF. DWG.	ORDER NO.

PSI5 2200RT120

DWG. NO.
PSI5 2200RT120

DATE
8/13/18

REV. #
1

1050 DEARBORN DRIVE
P.O. BOX 29186
COLUMBUS, OHIO 43229

