

3.39"
(86mm)

17.24"
(438mm)



FRONT VIEW

12 13 14

- ① INPUT POWER CORD: NEMA L5-30P WITH 10 FOOT ATTACHED CORD
- ② EXTERNAL BATTERY CABINET CONNECTOR
- ③ 30A INPUT BREAKER
- ④ RJ-45 DATA LINE CONNECTORS
- ⑤ INTELLISLOT PORT. NETWORK COMMUNICATIONS CARD OPTIONAL
- ⑥ EPO CONNECTOR
- ⑦ USB PORT
- ⑧ 20A OUPUT BREAKER
- ⑨ OUTPUT RECEPTACLES: 3 NEMA 5-15R ALWAYS ON
- ⑩ OUTPUT RECEPTACLES: 3 NEMA 5-15R PROGRAMMABLE GROUP
- ⑪ OUTPUT RECEPTACLE: NEMA L5-30R
- ⑫ ON/MUTE BUTTON
- ⑬ SELECT BUTTON
- ⑭ OFF/ENTER BUTTON

REAR VIEW

NOTES:

1. UNIT DIMENSIONS: 17.2" x 3.4" x 24.8" (438mm) x (86mm") x (630mm)
2. UNIT WEIGHT: 70.8lbs (32.1kg)
3. SHIPPING DIMENSIONS: 21.7" x 10.2" x 30.8" (550mm) x (258mm) x (782mm)
4. SHIPPING WEIGHT: 80.0lbs (36.3kg)
5. MINIMUM AIRFLOW CLEARANCE IS 4.0" (100.0mm) - FRONT/REAR
6. FIXED RAIL KIT: INCLUDED
7. ALL SITE WIRING IS TO BE IN COMPLIANCE WITH NATIONAL AND LOCAL ELECTRIC CODES.
8. USES PSI5-72VBATT
9. UNIT INPUT: 100~125 VAC, 60/50HZ, 24A
10. UNIT OUTPUT: 100/110/115/120/125VAC, 60/50HZ, 3000VA/2700W, 24A, @125VAC INPUT OR 2880VA/2700W, 24A, @120VAC INPUT OR 2760VA/2760W, 24A, @115VAC INPUT OR 2550VA/2295W, 23.2A, @110VAC INPUT OR 2400VA/2295W, 24A, @100VAC INPUT

24.80"
(630mm)

SIDE VIEW

DRAWN BY
B. LAY
CHK BY
B. HOCKENSMITH
REF. DWG.

SHEET NO.
1 OF 1
ECN NO.
ORDER NO.

PSI5 3000RT120

DWG. NO.
PSI5 3000RT120

DATE
8/13/18

REV. #
1

1050 DEARBORN DRIVE
P.O. BOX 29186
COLUMBUS, OHIO 43229



FILE NAME: I:\dpg\DRAWINGS\PSI5\PSI5 3000RT120.dft