

OVERVIEW

The Vertiv Geist FSC, Facility Side Cable, features a universal connector designed to mate with the Universal Input on the Vertiv Geist UPDU, Universal Power Distribution Unit. The FSC is available in common worldwide AC power specs ranging from 16A to 60A, 120V to 415V with single and three phase power configurations. Select the detachable Vertiv Geist FSC specific to the local power configuration to power the UPDU. (UPDU sold separately)

Benefits

- The flexibility offered by the UPDU and FSC enable any rack architecture to be installed in any data center around the world, regardless of the power infrastructure already in place.
- The FSC enables users to utilize a single UPDU model with various input power configurations to simplify global IT infrastructure deployments, inventory management and enable rapid deployments worldwide.
- Increase or decrease UPDU power capacity by changing the FSC to adapt to fluctuating equipment power needs.
- Every unit is 100% tested for reliability and functionality to ensure units function as designed.



Part #: FSC3N003

Model Number: CSN-S02A8-03000-3TL21A-S

Category: Facility Side Cable

Sub Category: Standard

Power Configuration: 30A, 120/208V WYE, 8.6kW

Product Summary: FSC3N003 - Facility Side Cable, 30A, 120/208V WYE, 8.6kW, 10ft power cord with L21-30P with Universal Connector.

Plug Form:



L21-30P

Receptacle:



Universal Connector
(Quantity: 1)

Chassis Color Options:



To discuss color options, contact your local sales representative.

Product Specification and Options

System Features

Compatibility	For use with Vertiv Geist Universal Rack PDU (UPDU)
Voltage	120/208V WYE
Current	30A
Frequency	50/60Hz
Power Cable Wire Gauge	10/5
Power Cable Length	10ft / 3m
Plug Type	NEMA L21-30P Twistlock
Max Plug kW	8.6kW (208V)
Output Connector	Universal Connector
UPDU Voltage per Receptacle/Socket	208-240V
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Shipped Weight	5lbs (2.27kg)