

Input values		Input plug	Outputs			Length (mm)	Order No.
Voltage	Current		C13	C19	Schuko		
100-240 V	16 A	C20 inlet	18	3		826,5	MPE-3141
100-240 V	16 A	C20 inlet	24			826,5	MPE-3241
230 V	16 A	IEC 60309 16A 1P+N+G	18	3		826,5	MPE-3142
230 V	16 A	IEC 60309 16A 1P+N+G	24			826,5	MPE-3242
230 V	32 A	IEC 60309 32A 1P+N+G	36	6		1736,5	MPE-1243
230 V	32 A	IEC 60309 32A 1P+N+G	24	6		1736,5	MPE-1543
230 V	32 A	IEC 60309 32A 1P+N+G				1736,5	MPE-1643
230 V	32 A	Hardwired	36	6		1736,5	MPE-1260
230 V	32 A	Hardwired	24	6	3	1736,5	MPE-1560
230 V	32 A	Hardwired			18	1736,5	MPE-1660
230/400 V	16 A	IEC 60309 16A 3P+N+G	36	12		1736,5	MPE-1144
230/400 V	16 A	IEC 60309 16A 3P+N+G	36	6	3	1736,5	MPE-1444
230/400 V	16 A	IEC 60309 16A 3P+N+G			18	1736,5	MPE-1644
230/400 V	16 A	Hardwired	36	12		1736,5	MPE-1161
230/400 V	16 A	Hardwired	36	6	3	1736,5	MPE-1461
230/400 V	16 A	Hardwired			18	1736,5	MPE-1661
230/400 V	32 A	IEC 60309 32A 3P+N+G		6		826,5	MPE-3345-002
230/400 V	32 A	IEC 60309 32A 3P+N+G	36	6		1736,5	MPE-1245
230/400 V	32 A	IEC 60309 32A 3P+N+G	24	12		1736,5	MPE-1345
230/400 V	32 A	IEC 60309 32A 3P+N+G	24	6	3	1736,5	MPE-1545
230/400 V	32 A	IEC 60309 32A 3P+N+G			18	1736,5	MPE-1645
230/400 V	32 A	IEC 60309 32A 3P+N+G	48			1736,5	MPE-1745
230/400 V	32 A	Hardwired	36	6		1736,5	MPE-1262
230/400 V	32 A	Hardwired	24	12		1736,5	MPE-1362
230/400 V	32 A	Hardwired	24	6	3	1736,5	MPE-1562
230/400 V	32 A	Hardwired			18	1736,5	MPE-1662
230/400 V	32 A	Hardwired	48			1736,5	MPE-1762

