

OVERVIEW

The Vertiv Geist FSC, Facility Side Cable, features a universal connector designed to mate with the Universal Input on the Vertiv Geist UPDU, Universal Power Distribution Unit. The FSC is available in common worldwide AC power specs ranging from 16A to 60A, 120V to 415V with single and three phase power configurations. Select the detachable Vertiv Geist FSC specific to the local power configuration to power the UPDU. (UPDU sold separately)

Benefits

- The flexibility offered by the UPDU and FSC enable any rack architecture to be installed in any data center around the world, regardless of the power infrastructure already in place.
- The FSC enables users to utilize a single UPDU model with various input power configurations to simplify global IT infrastructure deployments, inventory management and enable rapid deployments worldwide.
- Increase or decrease UPDU power capacity by changing the FSC to adapt to fluctuating equipment power needs.
- Every unit is 100% tested for reliability and functionality to ensure units function as designed.



Part #: FSC3U001

Model Number: CSU-S02A3-43000-2PS56B-S

Category: Facility Side Cable

Sub Category: Standard

Power Configuration: 16A OR 20A, 230/400V WYE, 11.0kW

Product Summary:

FSC3U001 - Facility Side Cable, 16A/20A, 230/400V WYE, 11.0kW, 10ft / 3m with IEC 3P+N+E (IP44) and Universal Connector.

Plug Form:

3P+N+E (IP44)

Receptacle:Universal Connector
(Quantity: 1)**Chassis Color Options:**

To discuss color options, contact your local sales representative.

Product Specification and Options**System Features**

Compatibility	For use with Vertiv Geist Universal Rack PDU (UPDU)
Voltage	208-240/360-415V WYE
Current	16/20A x 3 Phase WYE
Frequency	50/60Hz
Power Cable Wire Gauge	9/5 (6mm ²)
Power Cable Length	10ft / 3m
Plug Type	IEC60309 3P + N + E, 16A/20A, 230/400V, Splashproof IP44
Max Plug kW	11.0kW (230V)
Output Connector	Universal Connector
UPDU Voltage per Receptacle/Socket	208-240V
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	CE Marked
Certification/Agency Approvals	Complies with EN 55032 and EN 55024
Certification/Agency Approvals	Complies with IEC 60950-1 (CB Certificate Available)
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Shipped Weight	6lbs (2.72kg)