

## OVERVIEW

Basic rPDUs deliver reliable power to critical IT equipment within a rack or cabinet.

### Benefits

- Reliable rack power distribution.
- Every unit is 100% tested for reliability and functionality.
- Simple and convenient configuration options for cord lengths and chassis colors.
- Standard three-year warranty, upgraded to a five-year warranty with product registration.



## Part #: VP9562

**Model Number:** BRN100-10

**Category:** Basic

**Sub Category:** Standard

**Power Configuration:** 15A, 120V, 1.4kW

**Physical Configuration:** 19 in / 483 mm, Horizontal

### Product Summary:

VP9562 - rPDU, Basic Standard, 15A, 120V, 1.4kW, Horizontal, (10) NEMA 5-15R, 10 ft power cord with 5-15P, Black Powder Coat.

### Plug Form:



5-15P

### Receptacle:



NEMA 5-15R  
(Quantity: 10)

### Chassis Color Options:



To discuss color options, contact your local sales representative.

## Product Specification and Options

### System Features

Quantity Of Inputs	1
Voltage	100-120V
Current	15A
VA per Input (Load Capacity)	1.4kW (120V)
Frequency	50/60Hz

<b>Over Current Protection</b>	15A Thermal Breaker
<b>Switch</b>	No
<b>Indicators - LED(s)</b>	1 - Power ON Green LED
<b>Power Cable Wire Gauge</b>	14/3
<b>Power Cable Length</b>	10ft
<b>Plug Type</b>	NEMA 5-15P
<b>Receptacle/Socket Type #1</b>	NEMA 5-15R
<b>- Quantity on Rear</b>	10
<b>- Quantity per Breaker</b>	10
<b>- Style</b>	Duplex
<b>- Maximum Output per Receptacle/Socket</b>	15A
<b>- Voltage per Receptacle/Socket</b>	120V
<b>Continuous Operating Temperature Range</b>	10-45C / 50-113F
<b>Heavy Steel - Powder Coat Finish</b>	Black
<b>Configuration</b>	19in / 483mm Horizontal Rackmount
<b>Flush Mount</b>	Yes
<b>Made in the USA</b>	Yes, TAA Compliant
<b>Product Warranty</b>	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
<b>Certification/Agency Approvals</b>	RoHS Compliant
<b>Certification/Agency Approvals</b>	UL & c-UL Listed 60950
<b>Chassis Dimensions (HxWxD)</b>	1.72in x 17in x 3.75in
<b>Shipped Weight</b>	6lbs (2.72kg)