




- 1 INTELLISLOT PORT. NETWORK COMMUNICATIONS CARD OPTIONAL
- 2 EPO CONNECTOR
- 3 USB PORT
- 4 INPUT RECEPTACLES: 1 IEC C14 15A 250V SINGLE
- 5 13A INPUT CIRCUIT BREAKER
- 6 OUTPUT RECEPTACLES: 2 NEMA 5-15R PROGRAMMABLE GROUP 1
- 7 OUTPUT RECEPTACLES: 2 NEMA 5-15R PROGRAMMABLE GROUP 2
- 8 OUTPUT RECEPTACLES: 2 NEMA 5-15R ALWAYS ON
- 9 ESC/MUTE BUTTON
- 10 ENTER ON/OFF BUTTON
- 11 GROUNDING SCREW

SIDE VIEW

NOTES

1. UNIT DIMENSIONS (WxDxH) 438mm x 300mm x 86.2mm(2U)
(17.2") x (11.8") x (3.4")
2. UNIT WEIGHT : 8.9kg (19.4lbs)
3. SHIPPING DIMENSIONS (WxDxH) 570mm x 470mm x 240mm
(22.4") x (18.5") x (9.5")
4. SHIPPING WEIGHT : 12.9kg (28.4lbs)
5. MINIMUM AIRFLOW CLEARANCE IS 100mm (4.0") FRONT AND REAR.

SHEET NO. 1 OF 1	DRAWN BY: BAPIN N	TITLE OUTLINE DRAWING PSIS-1100SRT2ULI	DWG. NO. PSIS-1100SRT2ULI	
CO. NO. -	DESIGNED BY: PETE BENNER		DATE (LATEST REV.) 2025/06/12	
REF DWG. -	APPROVED BY: SAM AINEHVAND		REVISION 0	