



FRONT VIEW



REAR VIEW



SIDE VIEW

- 1 INTELLISLOT PORT. NETWORK COMMUNICATIONS CARD OPTIONAL
- 2 USB PORT
- 3 EPO CONNECTOR
- 4 8A INPUT CIRCUIT BREAKER
- 5 INPUT RECEPTACLES: 1 IEC C14 15A 250V SINGLE
- 6 OUTPUT RECEPTACLES: 2 NEMA 5-15R PROGRAMMABLE GROUP
- 7 OUTPUT RECEPTACLES: 2 NEMA 5-15R ALWAYS ON
- 8 ON/OFF BUTTON
- 9 GROUNDING SCREW

NOTES

1. UNIT DIMENSIONS (WxDxH) 438mm x 225mm x 42.5mm(1U)
(17.2") x (8.9") x (1.7")
2. UNIT WEIGHT : 4.2kg (9.2lbs)
3. SHIPPING DIMENSIONS (WxDxH) 570mm x 370mm x 185mm
(22.4") x (14.6") x (7.3")
4. SHIPPING WEIGHT : 7.16kg (15.8lbs)
5. MINIMUM AIRFLOW CLEARANCE IS 100mm (4.0") FRONT AND REAR.

SHEET NO. 1 OF 1	DRAWN BY: BAPIN N	TITLE OUTLINE DRAWING PSI5-500SRT1ULI	DWG. NO. PSI5-500SRT1ULI	
CO. NO. -	DESIGNED BY: PETE BENNER		DATE (LATEST REV.) 2025/06/12	
REF DWG. -	APPROVED BY: SAM AINEHVAND		REVISION 0	