

Vertiv™ MPH2™ Types for Europe

Vertical models

Model/functions	Vertiv MPHR	Vertiv MPHM	Vertiv MPH C	Vertiv MPH B
Input / Group measurement	■	■	■	■
Output measurement	■	■		
Output switching	■		■	

Type	Input Values		Input Connector	Outputs		Length (mm)	Order Number
	Voltage	Current		C13	C19		
B	230V	16A	C20 inlet	17	2	916.5	MPHB3241
B	230V	16A	C20 inlet	21		916.5	MPHB3141
B	230V	16A	C20 inlet	30	6	1736.5	MPHB1241
B	230V	16A	IEC 60309 16A 1P+N+G	17	2	916.5	MPHB3242
B	230V	16A	IEC 60309 16A 1P+N+G	21		916.5	MPHB3142
B	230V	16A	IEC 60309 16A 1P+N+G	30	6	1736.5	MPHB1242
B	230V	32A	IEC 60309 32A 1P+N+G	30	6	1736.5	MPHB1243
B	230V	32A	Connection unit	30	6	1736.5	MPHB1260
B	230/400V	3 x 16A	IEC 60309 16A 3P+N+G	30	6	1736.5	MPHB1244
B	230/400V	3 x 32A	IEC 60309 32A 3P+N+G	42		1826.5	MPHB1545
B	230/400V	3 x 32A	IEC 60309 32A 3P+N+G	18	12	1826.5	MPHB1345
B	230/400V	3 x 32A	IEC 60309 32A 3P+N+G	30	6	1826.5	MPHB1245
B	230/400V	3 x 32A	Connection unit	42		1826.5	MPHB1562
B	230/400V	3 x 32A	Connection unit	18	12	1826.5	MPHB1362
B	230/400V	3 x 32A	Connection unit	30	6	1826.5	MPHB1262
C	230V	16A	C20 inlet	8		916.5	MPHC3341
C	230V	16A	C20 inlet	16		1004	MPHC3141
C	230V	16A	C20 inlet	18	6	1736.5	MPHC1141
C	230V	16A	C20 inlet	24		1736.5	MPHC1241
C	230V	16A	IEC 60309 16A 1P+N+G	18	6	1736.5	MPHC1142
C	230V	16A	IEC 60309 16A 1P+N+G	24		1736.5	MPHC1242
C	230V	16A	IEC 60309 16A 1P+N+G	16		1004	MPHC3142
C	230V	32A	IEC 60309 32A 1P+N+G	18	6	1736.5	MPHC1143
C	230V	32 A	IEC 60309 32 A 1P+N+G	24		1736.5	MPHC1243
C	230V	32 A	Connection unit	18	6	1736.5	MPHC1160
C	230V	32 A	Connection unit	24		1736.5	MPHC1260
C	230/400V	3 x 16 A	IEC 60309 16 A 3P+N+G	18	6	1736.5	MPHC1144
C	230/400V	3 x 16 A	IEC 60309 16 A 3P+N+G	24		1736.5	MPHC1244
C	230/400V	3 x 16 A	Connection unit	18	6	1736.5	MPHC1161
C	230/400V	3 x 16 A	Connection unit	24		1736.5	MPHC1261
C	230/400V	3 x 32 A	IEC 60309 32 A 3P+N+G	18	6	1736.5	MPHC1145
C	230/400V	3 x 32 A	IEC 60309 32 A 3P+N+G	24		1736.5	MPHC1245
C	230/400V	3 x 32 A	IEC 60309 32 A 3P+N+G	6	12	1736.5	MPHC1345
C	230/400V	3 x 32 A	Connection unit	18	6	1736.5	MPHC1162
C	230/400V	3 x 32 A	Connection unit	24		1736.5	MPHC1262
C	230/400V	3 x 32 A	Connection unit	6	12	1736.5	MPHC1362
M	230V	16 A	C20 inlet	8		916.5	MPHM3341
M	230V	16 A	IEC 60309 16 A 1P+N+G	8		916.5	MPHM3342
M	230V	16 A	C20 inlet	16		1004	MPHM3141
M	230V	16 A	C20 inlet	18	6	1736.5	MPHM1141
M	230V	16 A	C20 inlet	24		1736.5	MPHM1241
M	230V	16 A	IEC 60309 16 A 1P+N+G	18	6	1736.5	MPHM1142
M	230V	16 A	IEC 60309 16 A 1P+N+G	24		1736.5	MPHM1242
M	230V	16 A	IEC 60309 16 A 1P+N+G	16		1004	MPHM3142
M	230V	32 A	IEC 60309 32 A 1P+N+G	18	6	1736.5	MPHM1143
M	230V	32 A	IEC 60309 32 A 1P+N+G	24		1736.5	MPHM1243
M	230V	32 A	Connection unit	18	6	1736.5	MPHM1160
M	230V	32 A	Connection unit	24		1736.5	MPHM1260
M	230/400V	3 x 16 A	IEC 60309 16 A 3P+N+G	18	6	1736.5	MPHM1144
M	230/400V	3 x 16 A	IEC 60309 16 A 3P+N+G	24		1736.5	MPHM1244
M	230/400V	3 x 16 A	Connection unit	18	6	1736.5	MPHM1161

Type	Input Values		Input Connector	Outputs		Length (mm)	Order Number
	Voltage	Current		C13	C19		
M	230/400V	3 x 16 A	Connection unit	24		1736.5	MPHM1261
M	230/400V	3 x 32 A	IEC 60309 32 A 3P+N+G	18	6	1736.5	MPHM1145
M	230/400V	3 x 32 A	IEC 60309 32 A 3P+N+G	24		1736.5	MPHM1245
M	230/400V	3 x 32 A	IEC 60309 32 A 3P+N+G	6	12	1736.5	MPHM1345
M	230/400V	3 x 32 A	Connection unit	18	6	1736.5	MPHM1162
M	230/400V	3 x 32 A	Connection unit	24		1736.5	MPHM1262
M	230/400V	3 x 32 A	Connection unit	6	12	1736.5	MPHM1362
R	230V	16 A	C20 inlet	8		916.5	MPHR3341
R	230V	16 A	IEC 60309 16 A 1P+N+G	8		916.5	MPHR3342
R	230V	16 A	C20 inlet	16		1004	MPHR3141
R	230V	16 A	C20 inlet	18	6	1736.5	MPHR1141
R	230V	16 A	C20 inlet	24		1736.5	MPHR1241
R	230V	16 A	IEC 60309 16 A 1P+N+G	18	6	1736.5	MPHR1142
R	230V	16 A	IEC 60309 16 A 1P+N+G	24		1736.5	MPHR1242
R	230V	16 A	IEC 60309 16 A 1P+N+G	16		1004	MPHR3142
R	230V	32 A	IEC 60309 32 A 1P+N+G	18	6	1736.5	MPHR1143
R	230V	32 A	IEC 60309 32 A 1P+N+G	24		1736.5	MPHR1243
R	230V	32 A	Connection unit	18	6	1736.5	MPHR1160
R	230V	32 A	Connection unit	24		1736.5	MPHR1260
R	230/400V	3 x 16 A	IEC 60309 16 A 3P+N+G	18	6	1736.5	MPHR1144
R	230/400V	3 x 16 A	IEC 60309 16 A 3P+N+G	24		1736.5	MPHR1244
R	230/400V	3 x 16 A	Connection unit	18	6	1736.5	MPHR1161
R	230/400V	3 x 16 A	Connection unit	24		1736.5	MPHR1261
R	230/400V	3 x 32 A	IEC 60309 32 A 3P+N+G	18	6	1736.5	MPHR1145
R	230/400V	3 x 32 A	IEC 60309 32 A 3P+N+G	24		1736.5	MPHR1245
R	230/400V	3 x 32 A	IEC 60309 32 A 3P+N+G	6	12	1736.5	MPHR1345
R	230/400V	3 x 32 A	Connection unit	18	6	1736.5	MPHR1162
R	230/400V	3 x 32 A	Connection unit	24		1736.5	MPHR1262
R	230/400V	3 x 32 A	Connection unit	6	12	1736.5	MPHR1362

Horizontal models

Type	Input Values		Input Connector	Outputs		Order Number
	Voltage	Current		C13	C19	
B	230V	16 A	C20 inlet	12		MPHB2141
B	230V	16 A	C20 inlet	8	2	MPHB2341
B	230V	32 A	IEC 60309 32A 1P+N+G	12		MPHB2143
B	230V	32 A	IEC 60309 32A 1P+N+G	8	2	MPHB2343
B	230/400V	3 x 16 A	IEC 60309 16A 3P+N+G	12		MPHB2144
B	230/400V	3 x 16 A	IEC 60309 16A 3P+N+G	2	6	MPHB2244
B	230/400V	3 x 32 A	IEC 60309 32A 3P+N+G	2	6	MPHB2245
M	230V	16 A	C20 inlet	9		MPHM2141
M	230V	16 A	C20 inlet	6	2	MPHM2441
M	230V	32 A	IEC 60309 32A 1P+N+G	9		MPHM2143
M	230V	32 A	IEC 60309 32A 1P+N+G	6	2	MPHM2443
M	230/400V	3 x 16 A	IEC 60309 16A 3P+N+G	9		MPHM2144
M	230/400V	3 x 16 A	IEC 60309 16A 3P+N+G	2	6	MPHM2344
M	230/400V	3 x 32 A	IEC 60309 32A 3P+N+G	2	6	MPHM2345
R	230V	16 A	C20 inlet	9		MPHR2141
R	230V	16 A	C20 inlet	6	2	MPHR2441
R	230V	32 A	IEC 60309 32A 1P+N+G	9		MPHR2143
R	230V	32 A	IEC 60309 32A 1P+N+G	6	2	MPHR2443
R	230/400V	3 x 16 A	IEC 60309 16A 3P+N+G	9		MPHR2144
R	230/400V	3 x 16 A	IEC 60309 16A 3P+N+G	2	6	MPHR2344
R	230/400V	3 x 32 A	IEC 60309 32A 3P+N+G	2	6	MPHR2345