


Disclosure and photocopying of this document, exploitation and communication of its contents are not permitted, unless permission is expressly granted. All rights are reserved.

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwendung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Alle Rechte vorbehalten.



CS8365C  
 (50 A, 3/PE, 200-240 V)

OUTPUT POWER

| BRANCH | PHASE | RECEPTACLE TYPE (QUANTITY) | VOLTAGE (V) | MAX. CONTINUOUS AMPS (A) |            |
|--------|-------|----------------------------|-------------|--------------------------|------------|
|        |       |                            |             | PER RECEPTACLE           | PER BRANCH |
| A      | L1-L2 | 4xC13                      | 200-240     | 12                       | 16         |
| B      | L2-L3 | 4xC13                      | 200-240     | 12                       | 16         |
| C      | L3-L1 | 4xC13                      | 200-240     | 12                       | 16         |
| D      | L1-L2 | 4xC13                      | 200-240     | 12                       | 16         |
| E      | L2-L3 | 4xC13                      | 200-240     | 12                       | 16         |
| F      | L3-L1 | 4xC13                      | 200-240     | 12                       | 16         |

AGENCY COMPLIANCE:  
 - UL certification: UL 60950-1 (2nd), CSA C22.2 No. 60950-1-07  
 - FCC certification  
 - CB certification: IEC 60950-1 (2nd)

ENVIRONMENTAL RATING:  
 OPERATING TEMPERATURE: 5 °C - 60 °C (41 °F - 140 °F) NON-CONDENSING, NON-CORROSIVE, 10 % - 90 % RH  
 STORAGE TEMPERATURE: -20 °C - 85 °C (-4 °F - 185 °F)  
 MAX. OPERATING ALTITUDE: 2000 m

- NOTES:  
 1. UNIT DIMENSIONS: 1826.5 mm (71.9") H x 50 mm (2.0") D x 56 mm (2.2") W  
 2. UNIT WEIGHT: 4 kg / 8.8 lbs  
 3. SHIPPING DIMENSIONS: 2017 mm (79.4") H x 297 mm (11.7") D x 176 mm (7.0") W  
 4. SHIPPING WEIGHT: 6.8 kg / 15 lbs  
 5. (2) MOUNTING BUTTONS AND (2) MOUNTING BRACKETS SUPPLIED WITH EACH UNIT. EITHER OPTION CAN BE USED TO MOUNT THE PDU.

INPUT POWER

| INPUT CORD  | INPUT PLUG | WIRE COUNT | FREQUENCY (Hz) | VOLTAGE (V) | RATED AMPS (A) | MAX. CONT. AMPS (A) |
|-------------|------------|------------|----------------|-------------|----------------|---------------------|
| 10 ft / 3 m | CS8365C    | 3/PE       | 50/60          | 200-240     | 50             | 40                  |

| METERING PARAMETER | MEASUREMENT ACCURACY                                                                     |
|--------------------|------------------------------------------------------------------------------------------|
| VOLTAGE            | ±1 % + 0.1 VAC                                                                           |
| CURRENT            | ±1.5 % + 0.01 A FROM 1 % TO 10 % OF UNIT RATING; ±1 % FROM >10 % TO 125 % OF UNIT RATING |

RoHS COMPLIANT

|                         |                                           |            |                      |                                                    |                      |  |                       |
|-------------------------|-------------------------------------------|------------|----------------------|----------------------------------------------------|----------------------|--|-----------------------|
| <p>Dimensions in mm</p> | Allgemeintoleranzen<br>General tolerances |            | Oberfläche<br>Finish |                                                    | Werkstoff / Material |  | Gewicht:<br>Weight: - |
|                         | -                                         |            | -                    |                                                    | -                    |  | -                     |
| Date                    |                                           | Name       |                      | Bezeichnung / Description                          |                      |  |                       |
| 10/12/15                |                                           | Blass      |                      | MPH2-NRV_CS8365C_24N                               |                      |  |                       |
| 10/12/15                |                                           | Votýpka    |                      | Input and Branch Metered + Outlet Metered/Switched |                      |  |                       |
| -                       |                                           | -          |                      | Zeichnungs-Nr. / Drawing no.                       |                      |  |                       |
| -                       |                                           | -          |                      | MPHR1224                                           |                      |  |                       |
| -                       |                                           | -          |                      | Verwendet in / Used in                             |                      |  |                       |
| -                       |                                           | -          |                      | -                                                  |                      |  |                       |
| Rev.                    | Change                                    | Date       | Name                 | Maßstab<br>Scale                                   |                      |  |                       |
| C                       | 18131                                     | 31.05.2017 | Petrú                | 1:5                                                |                      |  |                       |
|                         |                                           |            |                      | Blatt/Sheet                                        |                      |  |                       |
|                         |                                           |            |                      | 1/1                                                |                      |  |                       |