

## OVERVIEW

Upgradeable Switched Unit Level Monitored EC rPDUs provide reliable power distribution to critical IT equipment while delivering individual outlet level control and a comprehensive view of input power usage via remote network access. Includes environmental monitoring capabilities to obtain real-time environmental metrics. Upgrade the hot-swappable monitoring device on select units to leverage new technologies and accommodate changing business needs.

### Benefits

- Remotely reboot outlets to power cycle unresponsive IT equipment or increase runtime of critical equipment upon power failure with outlet-level control.
- Reliable power distribution with local and remote power monitoring options offer quick access to critical power usage information to evaluate energy usage trends and maximize uptime.
- Environmental monitoring capabilities with the addition of optional environmental sensors ensure users have critical infrastructure data at their fingertips to prevent climate-related equipment failure and system downtime.
- Fault-Tolerant Daisy Chaining with RSTP simplifies intelligent rPDU connectivity and ensures data is reported even when a break in the network chain occurs. Supports up to 40 rPDUs.
- Gather comprehensive power data at the palm of your hand with the use of



## Part #: VP8932

**Model Number:** MNS3EGB1-24S203-3TL5A0A10-S

**Category:** Switched

**Sub Category:** Unit Level Monitoring EC

**Power Configuration:** 30A, 120V, 2.8kW

**Physical Configuration:** 66in / 1683mm, Vertical

**Product Summary:** VP8932 - rPDU, Switched Unit Level Monitoring EC, 30A, 120V, 2.8kW, Vertical, (24) NEMA 5-20R, 10ft / 3m power cord with L5-30P, Black Powder Coat.

**Monitoring:** Input power monitoring with Outlet switching. Circuit/Breaker current monitoring. Environmental monitoring via optional remote sensors. Daisy chain Ethernet connectivity. Local high visibility LED display.

### Plug Form:



L5-30P

### Receptacle:



NEMA 5-20R  
(Quantity: 24)

### Chassis Color Options:



To discuss color options, contact your local sales representative.

## Product Specification and Options

### System Features

<b>Monitoring</b>	Input power monitoring with Outlet switching. Circuit/Breaker current monitoring. Environmental monitoring via optional remote sensors. Daisy chain Ethernet connectivity. Local high visibility LED display.
<b>Input Monitoring</b>	Phase (A) Monitoring (kWh, W, VA, PF, V, A)  Power Measurements Compliant with ANSI C12.1 and IEC 62053-21 at 1% Accuracy Class Requirements
<b>Circuit Monitoring</b>	Circuit / Breaker Monitoring (A)  Circuit/Breaker Current Measurements Independently Tested and Verified at 2% Accuracy
<b>Remote Power Management</b>	Individual Outlet Switching with Optional User Defined Time Delays and Sequential Power-up
<b>VLC Support</b>	Yes
<b>Quantity Of Inputs</b>	1
<b>Voltage</b>	100-120V
<b>Current</b>	30A
<b>VA per Input (Load Capacity)</b>	2.8kW (120V)
<b>Frequency</b>	50/60Hz
<b>Over Current Protection</b>	(2) 20A Single Pole Magnetic Breakers (5kAIC Rated)
<b>Switch</b>	Breaker/Switch Combination
<b>Scrolling / Rotatable Digital Display</b>	Yes
<b>Indicators - LED(s)</b>	24
<b>Power Cable Wire Gauge</b>	10/3
<b>Power Cable Length</b>	10ft / 3m
<b>Power Entry Location</b>	Bottom Front
<b>Plug Type</b>	NEMA L5-30P Twistlock
<b>Receptacle/Socket Type #1</b>	NEMA 5-20R
<b>- Quantity on Face</b>	24
<b>- Quantity per Breaker</b>	12
<b>- Style</b>	Individual
<b>- Voltage per Receptacle/Socket</b>	120V
<b>Network Connection</b>	Dual 10/100Mbps Ethernet
<b>Protocols Supported</b>	DHCP, HTTP, HTTPS, IPv4, IPv6, LDAP, NTP, RADIUS, RSTP, SSH, SMTP, SNMP (v1/v2c/v3), Syslog, TACACS+
<b>Data Access Formats</b>	CSV datalog, JSON API, JSON datalog
<b>USB Support</b>	Yes
<b>IP Reset Button</b>	Yes
<b>Hard Reboot Button</b>	Yes
<b>Serial Connection</b>	RS232 via RJ45
<b>Remote Sensor RJ Connection Jacks</b>	1 (Supports up to 16 Sensors)
<b>Maximum Operating Temperature</b>	60C / 140F
<b>Heavy Steel - Powder Coat Finish</b>	Black
<b>Configuration</b>	Zero U
<b>7938 Vertical Mounting Bracket Kit</b>	Yes

<b>Toolless Mounting Hardware - Center to Center Spacing</b>	61.25in and 64.75in / 1556mm and 1645mm
<b>Made in the USA</b>	Yes, TAA Compliant
<b>Product Warranty</b>	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
<b>Certification/Agency Approvals</b>	FCC Part 15 Class A Conformance
<b>Certification/Agency Approvals</b>	RoHS Compliant
<b>Certification/Agency Approvals</b>	UL & c-UL Listed 60950
<b>Chassis Dimensions (LxWxD)</b>	66.25in x 2in x 2.6in / 1683mm x 51mm x 66mm
<b>Shipped Weight</b>	20lbs (9.07kg)