

# VERTIV™ CXE LCX SERIES

Low Count Cross Connect Enclosures



## KEY FEATURES

- CAT5 rated with tight-twist cable for high speed transmission applications.
- 50-pair RLS self-strip terminal blocks are available for application flexibility.
- Includes two 32-inch mounting stakes for easy installation.
- Rugged metal housing made of mill-galvanized steel for durability and low cost maintenance.
- Our unique multi-stage paint process meets or exceeds EPA standards and provides a tough, corrosion resistant finish for longer life.

Vertiv™ CXE LCX Series from Vertiv provides traditional telephone service to rural areas with minimal capital expenditure.

## Description

The Vertiv CXE LCX Series offers an economical way to satisfy low pair count cross connect needs. This affordable, above-ground metal pedestal offers many of the same features as larger, more expensive cross-connect enclosures and includes two 32-inch mounting stakes plus a single pair tester. This series accommodates up to six RLS50 self-strip blocks to provide rapid pair-at-a-time, no-strip jumpering.

The Vertiv CXE LCX Series is accessed using a 216-type tool. If padlock protection is required, covers include a hasp for lock attachment.

## Application

Ideal for broadband networks that require high speed connections to support voice, data and video applications (such as xDSL and IPTV), the stake-mounted Vertiv CXE LCX Series of outdoor pedestals is designed for low pair count cross connection/ interface of 100, 200 or 300 pairs.



## Technical Specifications

### DIMENSIONS

H x W x D (inches)	44.22 x 10.93 x 16.37
--------------------	-----------------------

## Ordering Information

CATALOG NUMBER	PART NUMBER	DESCRIPTION
CCPLCRLS100G	F1010037	100-pair gray-green closure with RLS50 blocks, 50F 50D, raw harness
CCPLCRLS100DPMG	F1009781	100-pair gray-green closure with RLS50 blocks, 50F 50D, 4005DPM connectors
CCPLCRLS100CFG	F1010028	100-pair gray-green closure with RLS50 blocks, 50F 50D, 710 connectors
CCPLCRLS200G	F1009921	200-pair gray-green closure with RLS50 blocks, 100F 100D, raw harness
CCPLCRLS200DPMG	F1009645	200-pair gray-green closure with RLS50 blocks, 100F 100D, 4005DPM connectors
CCPLCRLS200CFG	F1010877	200-pair gray-green closure with RLS50 blocks, 100F 100D, 710 connectors
CCPLCRLS300CFG	F1010878	300-pair gray-green closure with RLS50 blocks, 150F 150D, 710 connectors
CCPLCRLS300DPMG	F1010494	300-pair gray-green closure with RLS50 blocks, 150F 150D, 4005DPM connectors
Accessories		
RLS50CAT5	F1010440	50 pair RLS block with raw harness
545890P	F1009767	50 pair RLS block with 710 connectors
RLS505DPM	F1010286	50 pair RLS block with 4005DPM connectors

## Diagram

