

VERTIV™ BBE TV SERIES

Access 360° Broadband Edge Enclosures



KEY FEATURES

- Lift-off cover provides 360° access to equipment for easy installation and maintenance.
- Square designs easily accommodate electronic equipment for efficient electronics installation.
- Flow-through louvers eliminate condensation and heat buildup for increased operating efficiency.
- A preassembled mounting stake and bracket reduce installation time.
- Multiple locking options are available.
- 8-in. pedestal base provides increased installation stability.
- Our unique multistage gray-green finishing process meets or exceeds EPA standards, and provides a tough corrosion-resistant finish for longer life.

Description

The Vertiv™ BBE TV Series line of metal CATV pedestals provides complete access to internally mounted distribution electronics for ease of installation and maintenance.

Available in four sizes to accommodate various distribution requirements, the Access 360° pedestals offer multiple locking options including Star Lock, Slam Lock, and Inner-Tite. They are equipped with preassembled stakes and brackets for a user friendly, ready-to-install system.

The 8x8, 10x10, and 12x12 Access 360° pedestals contain flow-through louvers for maximum heat dissipation. The 6x7 unit does not have louvers as it houses only non-heat generating passive equipment, such as taps. Pedestals are manufactured of heavy gauge mill-galvanized steel, treated with a unique finishing process for longer life.

Application

Access 360° pedestals are ideal for tap, coupler, splitter and line extender installations.



TV36088M




TV3601212M

Dimensions and Ordering Information

APPLICATION				DIMENSIONS						
Pedestal Size	Multi-Tap All Vendors	Tap/Splitter All Vendors	Tap/Splitter & Line Ext.	A	B	C	D	E	F	G
TV36067M	√			21-in.	8-in.	13-in.	6.5-in.	7.5-in.	17-in.	18-in.
TV36088M	√	√		25-in.	8-in.	17.5-in.	8-in.	8-in.	21-in.	26-in.
TV3601010M	√	√	√*	28-in.	8-in.	21-in.	10-in.	10-in.	24-in.	26-in.
TV3601212M	√	√	√*	32-in.	8-in.	24-in.	12-in.	12-in.	28-in.	26-in.

* This unit is designed to house two devices such as most line extenders with tap.

NOTE: All models are shipped complete and assembled with stakes, brackets, and provisions for padlock.



Ordering Matrix

CABINET	TV360 = Access 360° Metallic Pedestals
SIZE	67 = 6-in. x 7-in. 1010 = 10-in. x 10-in. 88 = 8-in. x 8-in. 1212 = 12-in. x 12-in.
MATERIAL	M = Metal
LOCK	N = No lock, 7/16-in. hex head bolt (can field install Star Lock or padlock)
BRACKET	I = I-bracket (6"x7" only) R = Mounting rod T = T-bracket O = Offset rod (10"x10" & 12"x12" only)
BASE	E = Extended (8"x8" & 10"x10" only) (8"x8" - A=38" B=21") (10"x10" - A=41" B=21") blank = Standard
DOME (CHECK FOR AVAILABILITY)	H = High (12"x12" only) (A=40" C=32") blank = Standard - all sizes (see Dimension table)



R-Mounting Rod
P63599



I-Bracket
P63588



O-Offset Rod
P76550



T-Bracket
P67259