


VERTIV™ VR RACK

Easy installation and integration of components and devices
Supports high-density weight loads





Rapid Deployments Everywhere You Operate

Standardize your deployments around the world and bring them online faster with the Vertiv™ VR rack. The Vertiv VR supports a wide variety of equipment, including: servers, storage, switches, routers, PDUs, UPSs, console port servers and KVM switches.

The Vertiv VR is delivered ready for high density environments to serve your mission critical needs — even as they evolve and change. This rack gives you the flexibility you need with easy installation.

The Vertiv VR Rack offers these advantages:

- Available in 8 standard sizes.
- Full depth adjustability of the 19" rails.
- Frame design allow for more than 25" more usable depth than similar sized racks.
- Doors that have 77% perforation and be hinged on either side.
- Tool-less removable top panel has four cable entry holes allowing for up to 2000 Cat6 cables, or 60A PDU plugs.
- Two dual purpose full height depth adjustable PDU / cable management brackets mounted in the zero U space with tool-less button mounting of rack PDUs, accessory mounting holes for tool-less cable management accessories and integrated cable tie off positions.
- 42U frame height that allows for the rack to pass through standard doors on casters.
- Simple external baying, allows for metric baying or on 24" centers.
- Split side panels with single locking slam latch allows for easy single person removal / installation.



High Density Cable Entry Top Panel

Removable openings for cable entry — ready for front / rear cabling. Can accommodate over 2000 Cat 6 cables.

Frame

More usable depth compared to similar sized rack



Split Locking Side Panels



For quick and easy installation and maintenance. Locks provide security.



Single and split 77% perforated doors providing maximum airflow. Lift off hinges for easy removal, and field reversibility.



Tool-less Cable Management

Requires just inserting and twisting the toolless accessories on 19" vertical mounting rail, or the PDU / cable management brackets.



Integrated 19" Rail Alignment

Ensures 19" rails are positioned correctly without measuring.



Leveling Feet

Accessible from the top of the frame for easy adjustment.



Vertiv™ VR Complete Rack

PART NUMBER	U	HEIGHT MM (INCHES)*	WIDTH MM (INCHES)*	DEPTH MM (INCHES)*
VR3100	42	2000 (78.6")	600 (23.6")	1100 (43.3")
VR3300	42	2000 (78.6")	600 (23.6")	1200 (47.8")
VR3150	42	2000 (78.6")	800 (31.5")	1100 (43.3")
VR3350	42	2000 (78.6")	800 (31.5")	1200 (47.8")
VR3107	48	2265 (89.2")	600 (23.6")	1100 (43.3")
VR3307	48	2265 (89.2")	600 (23.6")	1200 (47.8")
VR3157	48	2265 (89.2")	800 (31.5")	1100 (43.3")
VR3357	48	2265 (89.2")	800 (31.5")	1200 (47.8")

*Nominal dimensions, reference submittal drawings for exact dimensions VRXXXXSP ship with 2000 lb. rated shock packaging VRXXXXTAA are TAA Compliant

Features

FRAME

Frame capable of supporting up to 3000 lbs (1360kg) Static, 2250 lbs (1022kg) Dynamic, 2000 lbs (907kg) Transport (with Shock Package).

Simple external baying, allows for metric or on 24" centers and leveling feet incorporated into the frame for easy adjustment.

42U frame height that will allow access through standard doors on four swivel casters.

DOOR & SIDE PANELS

Single perforated front door and split rear doors with tool-less lift off hinges.

Locking handles.

Field reversible doors.

77% perforation exceeds IT manufacturers specifications.

Split side panels with single locking slam latch.

PDU / CABLE MANAGEMENT BRACKETS

Two dual purpose full height depth adjustable PDU / Cable Management brackets mounted in the zero U space.

Button mount keyholes throughout to accommodate tool-less button mounting of rack PDUs of various heights.

Accessory mounting holes allow for mounting of tool-less cable management accessories.

Integrated cable tie off positions.

Depth adjustable.

TOP PANEL

Tool-less removeable top panel.

Integrated hole pattern for easy installation of top panel accessories (cable management, modular busway support brackets, ladder / cable tray support brackets).

Four cable entry holes allowing for up to 2000 Cat6 cables, or 60A PDU plugs.

Top Panel load capacity of 150 lbs.

19" MOUNTING RAILS

(2) Pair of full height 19" EIA mounting rails, accepts cage nuts, U markings on front and rear of each rail.

Depth markings included on frame for easy alignment.

Accessory mounting holes along rails allow for mounting of cable management fingers and tool-less accessories

Rectangular cutouts for routing cables through 800mm (31.5") wide 19" EIA rails from front to rear or for airflow for side breathing equipment.

Full depth adjustability within the usable space.

COLOR

Frame, doors, side panels, top panel, rails and PDU brackets are powder coated RAL 7021 (Black).

CERTIFICATIONS

EIA 310E

UL2416

RoHS

REACH

Complete rack includes:

- Single 77% perforated locking front door.
- Split 77% perforated locking rear doors.
- 2 pair split locking side panels.
- High density cable entry top cover(2000 Cat 6 cables).
- 2 sets of 19" EIA Rails.
- 2 full height rack PDU
 Mounting / cable management brackets (one per side).
- Low profile casters and leveling feet.
- Baying brackets.
- Bolt down brackets.
- Hardware includes (50 each M6 cage nuts and screws),
 Cage nut installation tool, edge protection for top panel cable entry,
 T30 / Phillips L key, T30 extension driver.
- Keys.





Vertiv.com/en-in | E-mail: marketing.india@vertivco.com | Toll free: 1-800-2096070

Vertiv Energy Private Limited I Plot C-20, Rd No.19, Wagle Ind Estate, Thane (W), 400604. India