

VERTIV™ VR RACKS SHIP WITH PRE-INTEGRATED RACK PDUS



A worry-free time-saving solution for rapid deployment


Time is an invaluable resource when working to get an IT site up and running. Vertiv has answered the call by making its flagship line of premium server racks, Vertiv™ VR, "available pre-integrated with Vertiv Geist™ Rack PDUs" prior to shipment. Save time, money and resources on the integration process, while having peace of mind knowing that the parts you ordered will be set up correctly from the beginning.

Benefits:

- **No Hassle Installation** — We will install your PDUs for you, and make sure everything is set up correctly before shipment. Less waste and packaging to discard or deal with.
- **Worry-free Compatibility** — There is no question about compatibility with us integrating them before being sent to you.
- **Quick Shipment** — Adding this feature does not cause any delays. Your rack(s) with pre-integrated rPDUs will be shipped within days of Vertiv receiving the order.
- **5-Year Warranty** — Vertiv offers a 5-year warranty on the VR Rack and a 5-year warranty on the rPDU (with registration).



How it Works:



Select Your Rack

Choose from our standard 24 VR Rack SKUs designed to support high density weight loads.



Add Your Power Distribution Unit(s)

Select from a range of basic, monitored and switched PDUs. Choose your installation location(s) and cord placement location(s).



Deliver in a Single Shipment

We will install the PDU for you and ship the products as one pre-integrated assembly (versus separate parts).

How to Purchase:

Contact your local Vertiv office, or call us at 1.866.277.1924 to get started.

[Click Here](#)

Vertiv™ VR Rack

PART NUMBER	DESCRIPTION
VR3100	42U Server Rack 600mm x 1100mm w/sides Black
VR3100SP	42U Server Rack 600mm x 1100mm w/sides Black
VR3100TAA	42U Server Rack 600mm x 1100mm w/sides Black
VR3107	48U Server Rack 600mm x 1100mm w/Sides Black
VR3107SP	48U Server Rack 600mm x 1100mm w/Sides Black
VR3107TAA	48U Server Rack 600mm x 1100mm w/Sides Black
VR3150	42U Networking Rack 800mm x 1100mm w/Sides Black
VR3150SP	42U Networking Rack 800mm x 1100mm w/Sides Black
VR3150TAA	42U Networking Rack 800mm x 1100mm w/Sides Black
VR3157	48U Networking Rack 800mm x 1100mm w/Sides Black
VR3157SP	48U Networking Rack 800mm x 1100mm w/Sides Black
VR3157TAA	48U Networking Rack 800mm x 1100mm w/Sides Black

PART NUMBER	DESCRIPTION
VR3300	42U Server Rack 600mm x 1200mm w/sides Black
VR3300SP	42U Server Rack 600mm x 1200mm w/sides Black
VR3300TAA	42U Server Rack 600mm x 1200mm w/sides Black
VR3307	48U Server Rack 600mm x 1200mm w/Sides Black
VR3307SP	48U Server Rack 600mm x 1200mm w/Sides Black
VR3307TAA	48U Server Rack 600mm x 1200mm w/Sides Black
VR3350	42U Networking Rack 800mm x 1200mm w/Sides Black
VR3350SP	42U Networking Rack 800mm x 1200mm w/Sides Black
VR3350TAA	42U Networking Rack 800mm x 1200mm w/Sides Black
VR3357	48U Networking Rack 800mm x 1200mm w/Sides Black
VR3357SP	48U Networking Rack 800mm x 1200mm w/Sides Black
VR3357TAA	48U Networking Rack 800mm x 1200mm w/Sides Black

*Reference submittal drawings for exact dimensions VRXXXSP ship with 2000 lb. rated shock packaging VRXXXTAA are TAA Compliant.

Vertiv Geist™ Rack PDUs

MODEL	rPDU TYPE	rPDU SUB-TYPE	HORIZONTAL / VERTICAL	VOLTS	AMPS	MAX KW	PLUG TYPE	RECEPTACLE QTY/ TYPE	MAX OPERATING TEMP*	VI DIRECTOR
VP9562	Basic	Standard	H	120V	15A	1.4kW	5-15P	(10) 5-15R	45°C	N/A
VP9563	Basic	Standard	H	120V	20A	1.9kW	5-20P	(10) 5-20R	45°C	N/A
VP9571A	Basic	Standard	H	208V	30A	4.9kW	L6-30P	(12) C13	45°C	N/A
VP7541	Basic	Standard	V	208V	30A	4.9kW	L6-30P	(20) C13 / (4) C19	45°C	N/A
VP9567	Basic	Standard	V	120V	15A	1.4kW	5-15P	(14) 5-15R	45°C	N/A
VP8841	Monitored	Unit Level	V	208V	30A	4.9kW	L6-30P	(36) C13 / (6) C19	60°C	IMD Upgrade**
VP8832	Monitored	Unit Level	V	120V	30A	2.8kW	L5-30P	(24) 5-20R	60°C	IMD Upgrade**
VP8830	Monitored	Unit Level	V	120V	20A	1.9kW	L5-20P	(24) 5-20R	60°C	IMD Upgrade**
VP8865	Monitored	Unit Level	V	120/208V WYE	30A	8.6kW	L21-30P	(36) C13 / (6) C19 / (2) 5-20R	60°C	IMD Upgrade**
VP8866	Monitored	Unit Level	V	208V DELTA	60A	17.2kW	3P+E (IP44)	(12) C13 / (12) C19	60°C	IMD Upgrade**
VP8867	Monitored	Unit Level	V	208V DELTA	60A	17.2kW	3P+E (IP44)	(30) C13	60°C	IMD Upgrade**
VP7811B	Monitored	Unit Level	H	208V	30A	4.9kW	L6-30P	(12) C13 / (4) C19	60°C	IMD Upgrade**
VP8868	Monitored	Unit Level	V	208V DELTA	35A	10.0kW	3P+E CA	(36) C13 / (6) C19	60°C	IMD Upgrade**
VP4551V	Monitored	Outlet Level	V	208V DELTA	60A	17.2kW	3P+E (IP67)	(12) U-Lock C13 / (12) U-Lock C19	60°C	YES
VP8941	Switched	Unit Level Monitoring	V	208V	30A	4.9kW	L6-30P	(20) U-Lock C13 / (4) U-Lock C19	60°C	YES
VP8932	Switched	Unit Level Monitoring	V	120V	30A	2.8kW	L5-30P	(24) 5-20R	60°C	YES
VP8930	Switched	Unit Level Monitoring	V	120V	20A	1.9kW	L5-20P	(24) 5-20R	60°C	YES
VP8965	Switched	Unit Level Monitoring	V	120/208V WYE	30A	8.6kW	L21-30P	(18) U-Lock C13 / (6) U-Lock C19	60°C	YES
VP8959NA3	Switched	Unit Level Monitoring	V	208V	20A	3.3kW	L6-20P	(21) U-Lock C13 / (3) U-Lock C19	60°C	YES
VP8641	Switched	Outlet Level Monitoring	V	208V	30A	4.9kW	L6-30P	(20) U-Lock C13 / (4) U-Lock C19	60°C	YES
VP5870V	Switched	Outlet Level Monitoring	V	208V	30A	4.9kW	L6-30P	(30) U-Lock C13 / (6) U-Lock C19	60°C	YES
VP5665V	Switched	Outlet Level Monitoring	V	208V DELTA	30A	8.6kW	L15-30P	(30) U-Lock C13 / (6) U-Lock C19	60°C	YES

*Product chart shows limited spec information. For complete product details visit VertivCo.com.

VertivCo.com | Vertiv Headquarters, 1050 Dearborn Drive, Columbus, OH, 43085, USA

© 2019 Vertiv Co. All rights reserved. Vertiv, and the Vertiv logo trademarks or registered trademarks of Vertiv Co. All other names and logos referred to are trade names, trademarks or registered trademarks of their respective owners. While every precaution has been taken to ensure accuracy and completeness herein, Vertiv Co. assumes no responsibility, and disclaims all liability, for damages resulting from use of this information or for any errors or omissions. Specifications are subject to change without notice.