


VERTIV™ CXE UNX SERIES

RLS Accessories



Accessories

Accessories (not shown)

KEY	DESCRIPTION	PART NUMBER
1	Jumper wire spool, violet/white, 22 AWG, 300-ft	F525784
2	Jumper wire spool, violet/blue, 24 AWG, 500-ft, tight-twist	F1008214
3	Spool mtg hardware (incl shaft)	F529869
4	RLS/3M one-pair tester with leads	F019128
5	Dish for one-pair tester	F527097
6	50-pr RLS block, 5-ft, raw ended	F1010440
7	50-pr RLS block, 5-ft, w/ 710 conn	F1009767
8	50-pr RLS block, 5-ft, 3M 4005-DPM conn	F1010286
9	50-pr RLS block, 6-ft, 3M 4005-CBM conn	F016941
10	3-inch stainless steel hose clamp, #48	F508474
11	4-inch stainless steel hose clamp, #64	F518576
12	4-inch neoprene nozzle	F521860
13	Air vent	F525875
14	Pocket for accessories such as special service caps, spare activators, half-tap activators and loose documentation	*
14	Red RLS special service caps, 80 pack	F553828
15	RLS50 block diagram label	P53758S
16	Jumper routing diagram label	P808877
17	Cable assignment label	F016984

CATALOG NUMBER	DESCRIPTION
P29015	Wire spool shaft only
P29016	Wire spool retainer disk only
P29869	Spool mounting hardware including shaft
TU17	Touch-up paint (green)
TS50RLS1S	RLS 50-pair test shoe (female Cinch Jones)
RLSTEST1PKT	RLS/3M pocket tester, one pair
RLSACTGRAY10	RLS replacement activator, 10/pk standard
F1005390	RLS half-tap activator, feed-through
P35313	Handle, 3-pt. lock assembly
RLS Replacement Labels	
P53827	Green (feeder) label kit (600)
P53351	Green (feeder) label kit (1-1800)
P53308	Green (feeder) label kit, blank (2 blks.)
P68588	Green (feeder) label kit (1801-3600)
P68589	Green (feeder) label kit (3601-5400)
P64520	Blue (distribution) label kit (600)
P54203	Blue (distribution) label kit (1-1800)
P53350	Blue (distribution) label kit (1-3600)
P53271	Blue (distribution) label kit, blank (2 blks.)

* The pocket itself is not an orderable item.

VertivCo.com | Vertiv Headquarters, 1050 Dearborn Drive, Columbus, OH, 43085, USA

© 2018 Vertiv Co. All rights reserved. Vertiv and the Vertiv logo are trademarks or registered trademarks of Vertiv Co. All other names and logos referred to are trade names, trademarks or registered trademarks of their respective owners. While every precaution has been taken to ensure accuracy and completeness herein, Vertiv Co. assumes no responsibility, and disclaims all liability, for damages resulting from use of this information or for any errors or omissions. Specifications are subject to change without notice.