

VERTIV™ BBE OPFO SERIES

OPFOP Non-Metallic Broadband Edge Enclosures



KEY FEATURES

- Lift-off dome permits 360° access to all wirework and equipment
- Self-locking cover provides security
- Accommodates most splice closures for installation and flexibility
- Seamless non-metallic cover provides integral flood protection
- Accepts excess cable storage and grooming
- Multi-position ground bracket provides positive bonding of all equipment
- Meets or exceeds industry requirements


Vertiv™ BBE OPFO Series non-metallic enclosures accommodate optical nodes, fiber or copper splice enclosures, distribution equipment and cable slack.

Description

OPFOP14, OPFOP1420 & OFPOP1830 are direct buried above ground non-metallic pedestals with integral flood protection. Self-locking lift-off covers provide 360 access to internal equipment. Adjustable universal equipment/splice mounting brackets, cable storage guides, multi position bonding/grounding bar and mounting stakes are included.

Application

The OPFOP14, OPFOP1420 and OPFOP1830 are used for housing optical nodes, various distribution equipment, fiber or copper splice enclosures and cable slack storage. Fiber or copper splice capacity is limited by the size of splice enclosure used. The OPFOP pedestals provide cable slack storage, ease of equipment mounting and accessibility. Ideal for Telecom, Fiber, and Broadband applications.



OPFOP14 Open




OPFOP14 Closed




OPFOP1420 Open




OPFOP1420 Closed




OPFOP1830 Open



OPFOP1830 Closed



Bracket Accessory Kits



Dimension View
OPFOP1420 Closed

Dimensions

	A	B	C	D
OPFOP14	51"	36"	17.7"	17.7"
OPFOP1420	51"	36"	17.7"	23.6"
OPFOP1830	51"	36"	21.8"	33.8"

Ordering Information

CATALOG NUMBER	PART NUMBER	DESCRIPTION
OPFOP14	F1011026	OPFO Series, PRO14 pedestal
OPFOP1420	F1007747	OPFO Series, PRO1420 pedestal
OPFOP1830	F1007746	OPFO Series, PRO1830 pedestal

Accessories

CATALOG NUMBER	PART NUMBER	DESCRIPTION
MS1332	F602132	32" MOUNTING STAKE
MS1342	F604080	42" MOUNTING STAKE
MS1354	F604082	54" MOUNTING STAKE
MS1372	F604084	72" MOUNTING STAKE
OPFOP14BKTKIT	F1011027	Bracket kit to convert existing Pro14 to OPFO style enclosure
OPFOP1420BKTKIT	F1011028	Bracket kit to convert existing Pro1420 to OPFO style enclosure
OPFOP1830BKTKIT	F1011029	Bracket kit to convert existing Pro1830 to OPFO style enclosure