




Vertiv™ SmartCabinet™ Premium

Intelligent, Integrated Infrastructure
for the Data center



A CHANGING DIGITAL WORLD




Traditionally, data was generated at the Core and consumed at the Edge.

This model is now changing, with the large and growing number of smart devices and sensors generating a massive amount of information at the Edge.

Just a fraction of the content created at the Edge will be sent to the Core. Most of it will be processed and filtered at Edge sites.

What will enable this major shift?



Vertiv researched and analyzed the technology drivers and requirements of Edge use-cases across a wide range of business segments and verticals. The use-cases were each assigned to one of four archetypes that best characterize its intent and challenges:

- Data Intensive
- Human Latency
- M2M Latency
- Life Critical

Deploy a fully integrated 'Plug-n-Play' data center in just weeks.

No other solution offers the industry's leading power, precision cooling, and data center infrastructure management systems for such a wide array of applications and environments.


The Vertiv™ SmartCabinet™ Premium empowers Enterprise Class IT Infrastructure through the provision of integrated enclosure, power, cooling, and service. The biggest advantage is its Zero U space for non-core IT assets. Critically it also allows the most vital element - namely 360° visibility of all system components.

Customers can effectively manage and plan their IT Infrastructure with real time monitoring and insight into system performance.

Continuous availability depends on the power and cooling infrastructure that supports these systems and is comprised of the following:

- Power Quality
- Cooling
- Enclosure and Physical Infrastructure
- Monitoring and Management.

Capacity	: 6-20 kVA
Rack	: 1-4 Racks
Floor	: Primarily non raised
Certification	: CE Marking
Key Application	: Server room and small datacenters



Optimize your existing or new IT environments.



Technical Specifications

Specifications	SCP-1-7-U6 N	SCP-1-7 RC-U10 2N	SCP-2-7 RC-U10 2N	SCP-3-14 RC3-U20 2N	SCP-4-21 RC4-U20 2N
IT Capacity	6 kVA	7 kVA	7 kVA	14 kVA	20 kVA
No of Racks	1	1	2	3	4
Cooling Capacity	7 KW	2 X 7KW	2 X 7 KW	3 X 7 KW	4 X 7 KW
Cooling Redundacy	No	Yes	Yes	Yes	Yes
UPS Capacity	6 kVA	2 X 10 kVA	2 X 10 kVA	2 x 20 kVA	2 x 20 kVA
UPS Redundancy	No	Yes	Yes	Yes	Yes
Backup Time	Min 5 min and max 60 min				
Usable U Space*	42	30	84	120	162
Monitoring	Yes				
Rack PDU Type	All types (Basic, Metered, and Monitored)				
Fire Suppression and Access control	Optional				
Accessories	KVM, LCD Console, Camera with local surveillance, LTS, and DCIM				
CE Certification	Yes				

Dimensions

Width (mm)	932	932	1832	2732	3632
Depth (mm)	1200				
Height (mm)	2100 (42U)				

*U space available is subjected to change as per configuration and type of battery backup.

*Specifications are subjected to change without prior notice.

Additional SmartCabinet™ Premium Models being offered are SCP-1-7, SCP-1-7 RC, SCP-1-7-U10 N, SCP-1-7 RC-U10 2N, SCP-2-7, SCP-2-7 RC, SCP-2-7-U6 2N, SCP-2-7-U10 2N, SCP-2-7 RC-U6 2N, SCP-2-14, SCP-2-14 RC, SCP-2-14-U10 2N, SCP-2-14 RC-U10 2N, SCP-3-14 RC, SCP-3-14 RC-U10 2N, SCP-3-14 RC3, SCP-3-14 RC3-U10 2N, SCP-3-14 RC3-U20 2N, SCP-4-21 RC4, SCP-4-21 RC4-U10 2N, and SCP-4-21 RC4-U20 2N.

Local Expertise

Our network of local data center design experts have decades of experience building strong, infrastructures for IT environments of all sizes and types. These experts will work with you to identify and implement the exact solution for your needs. And they can thoroughly assess your IT environment to address your power, cooling and management challenges.

Industry-Leading Services

Our globally - renowned service and support organization is the largest in the industry. Vertiv Global Services can provide service capability for your entire facility infrastructure: from AC Power, DC power, Global Edge solutions, and Energy Storage solutions to Environmental Services, for all Vertiv brands and businesses.



Vertiv.com/en-in | E-mail : marketing.india@vertiv.com | Toll free : 1-800-2096070

Vertiv Energy Private Limited | Plot C-20, Rd No.19, Wagle Ind Estate, Thane (W), 400604. India

© 2023 Vertiv Co. All rights reserved. Vertiv, and the Vertiv logo trademarks or registered trademarks of Vertiv Co. All other names and logos referred to are trade names, trademarks or registered trademarks of their respective owners. While every precaution has been taken to ensure accuracy and completeness herein, Vertiv Co. assumes no responsibility, and disclaims all liability, for damages resulting from use of this information or for any errors or omissions. Specifications are subject to change without notice.