

Vertiv™ Rack Wall Mount



Space-saving solution for housing IT gear and networking equipment

Benefits

- Space efficiency: Wall Mounts can fit neatly into small spaces, no floorspace required.
- Flexibility for all applications: Different size options.
- Ventilation: Option for solid or mesh doors.
- Security Improved Accessibility: Lockable doors and panels.
- Equipment Organization: Cable Management Options.
- Noise and heat control by keeping it off their desks and away from direct interaction.

Vertiv™ Rack Wall Mount is designed to be mounted directly on walls, it organizes and secures devices like network switches, and servers, keeping them off the floor and neatly accessible.

Wall-mount racks come in various sizes and depths to accommodate different equipment types, with features such as lockable doors, and efficient cable management options for a streamlined setup; ideal for small deployments. Wall-mount racks are ideal for small office spaces, server rooms, and retail environments, offering reliable organization, security, and improved accessibility without taking up valuable floor space.

Wide offering scope

- Various depths to serve multiple channels:
 - Short depth for networking applications.
 - Medium depth for deeper networking/edge server.
 - Full depth for edge compute applications (will support full depth servers and more of our UPS's).
- Swings away from wall on hinge for easy back-door access with lock.
- Reversible mounting for left-hand or right-hand opening
- Complete rack stability and security –cabinet elevation/pallet brackets.
- Outer protection –Complete outer wrap & protective inserts.



Technical Specifications

SKU	U	Door	Height, inches (mm)	Width, inches (mm)	Depth, inches (mm)	Weight capacity, lbs
VR1000	12U	Plexi	24" (609.6)	21" (533.4)	24" (609.6)	150
VR1001	12U	Mesh	24" (609.6)	21" (533.4)	24" (609.6)	150
VR1002	12U	Solid	24" (609.6)	21" (533.4)	24" (609.6)	150
VR1003	12U	Plexi	24" (609.6)	24" (609.6)	31" (787.4)	200
VR1004	12U	Mesh	24" (609.6)	24" (609.6)	31" (787.4)	200
VR1005	12U	Solid	24" (609.6)	24" (609.6)	31" (787.4)	200
VR1006	19U	Plexi	36" (914.4)	21" (533.4)	24" (609.6)	250
VR1007	19U	Mesh	36" (914.4)	21" (533.4)	24" (609.6)	250
VR1008	19U	Solid	36" (914.4)	21" (533.4)	24" (609.6)	250
VR1009	19U	Plexi	36" (914.4)	24" (609.6)	31" (787.4)	250
VR1010	19U	Mesh	36" (914.4)	24" (609.6)	31" (787.4)	250
VR1011	19U	Solid	36" (914.4)	24" (609.6)	31" (787.4)	250
VR1012	25U	Plexi	48" (1219.2)	21" (533.4)	24" (609.6)	300
VR1013	25U	Mesh	48" (1219.2)	21" (533.4)	24" (609.6)	300
VR1014	25U	Solid	48" (1219.2)	21" (533.4)	24" (609.6)	300
VR1015	25U	Plexi	48" (1219.2)	24" (609.6)	31" (787.4)	300
VR1016	25U	Mesh	48" (1219.2)	24" (609.6)	31" (787.4)	300
VR1017	25U	Solid	48" (1219.2)	24" (609.6)	31" (787.4)	300
VR1021	6U	Mesh	12.65" (321)	22.62 (600)	17.12 (450)	132
VR1022	9U	Mesh	17.868 (321)	22.62 (600)	17.12 (450)	132

Accessories

SKU	Description
VM15	Double-Sided 19" Horizontal Cable Organizer
VM16	1 RMU 19" Horizontal Cable Organizer
VM17	2 RMU 19" Horizontal Cable Organizer
VRA1051	RFID Swing Handle, Multi-frequency, Wiegand Integration
VRA1052	RFID Swing Handle W/ PIN, Multi-frequency, Wiegand Integration
VRA1053	Electromechanical Swing Handle, RFID + PIN, black
VRA6300	19" Rackmount Copper Bus Bar
VRA2031	Double Wallmount Fan Kit (*)

(*) Only compatible with certain wall mount SKUs