

Vertiv™ Integrated Rack Solution

Reference Design #15

Premier Commercial and Office 42U Rack 6kVA Capacity

Solution Requirements

Physical Protection:

- Safeguard network gear from environmental threats and unauthorized access.
- Prevent dust, debris, and moisture from damaging equipment.

Power Protection:

- Prevent business interruption caused by power loss or power fluctuations with battery backup technology.

On-Site Management:

- Simplify deployment and support future growth with infrastructure designed for total compatibility and scalability.
- Streamline deployment and get critical applications up and running faster with on-site services and support.

Remote Management

- Maintain peace of mind one or more remote sites are up and running with real-time notifications.
- Save time by remotely accessing and rebooting unresponsive network equipment without an on-site visit.

Site-Maintenance

- Ensure continuity of business with remote access and management of critical systems.
- Maximize your investment with on-site equipment maintenance and extended warranty protection.

Thermal Management

- Cool critical IT gear in high density or high temperature environments.


Form Factor: Rack

Objective: Support network connectivity in commercial and office environments.

Recommended Environment

Climate-controlled unsecure environment with air conditioning in place for human comfort where temperature, humidity, and air quality control challenges could put IT equipment at risk of damage from uncontrolled heat, dust, or moisture.

- Converted Closet
- Retail Stock Room
- General Access Area



Integrated Solution Summary

| | |
|---------------------------|---|
| Capacity | 3000 VA / 2700 W |
| Rack(s) | 42U x 800mm x 1200mm (HxWxD) |
| Power Protection | Line Interactive UPS |
| Redundancy | N |
| Power Distribution | Switched Outlet Level Monitored 30A, 120V OU vertical. 24 NEMA 5-20R receptacles and a NEMA L5-30P input plug |
| Cooling | Included |
| Containment | Included |
| Monitoring | Included |
| Services | Included |
| Warranty | 3 years |
| Software | Included |

Explore all **Commercial and Office** form factors and power configurations available, **Endpoint, Rack, and Row** by visiting the **Solution Builder** on [Vertiv.com](https://www.vertiv.com) or by contacting a **Vertiv Sales Representative**.

Integrated Solution Includes:

| Qty: | Product Summary | SKU | Description: |
|------|------------------------------|---|--|
| 1 | Rack System | VRCS3350-120V | Vertiv™ VRC-S is a Self-Contained Rack Solution with integrated power distribution, and cooling. It includes the following: The Vertiv™ VR Rack VR3350 is a 42U server rack built with reliable engineering and is designed for simple and easy configuration. It has dimensions of 2000mm x 800mm x 1200mm (height, width, and depth), and has a deep frame that provides users around 2.5 inches more useable depth than similar sized racks. It has load capacities of 3,000 pounds static and 2,500 pounds dynamic. Vertiv™ Geist™ Switched Outlet Level Monitored Rack PDU NU30021 is a 30A, 120V 0U vertical with outlet level power monitoring and outlet level switching. It has 24 NEMA 5-20R receptacles and a NEMA L5-30P providing 2.8kW of power capacity. The Vertiv™ VRC rack cooling system is designed specifically for fast, easy installation in small server rooms, network closets, and edge computing spaces. This self-contained IT rack unit saves valuable floor space and provides up to 3,500 watts of cooling to critical equipment. Additionally, its variable speed components ensure high efficiency and scalable capacity. |
| 1 | Cable and Airflow Management | VR1000 VR1008 VR2000 | Vertiv™ VR Rack Accessories utilized to seamlessly integrate communications and power cables in to the cabinet while maintaining proper airflow separation of equipment intake and exhaust. |
| 1 | UPS | PSI5-3000RT120LI | The Liebert® PSI5 3000VA/2700W Lithium-ion line-interactive UPS is ideally suited to protect critical infrastructure in edge or distributed IT applications. The life expectancy of lithium-ion batteries is two to three times that of VRLA batteries – up to 10 years. That delivers up to 50% or more in TCO savings vs. VRLA batteries, chiefly because the PSI5 requires fewer battery replacements over its lifespan. |
| 1 | UPS COMM Card | IS-UNITY-SNMP | The interface card delivers SNMP, Telnet and web-management capability for enhanced communications and control of Liebert® UPS. The card manages a wide range of operating parameters, alarms and notifications, transmitting data over the network. Visit Vertiv.com for a free Vertiv™ Power Assist software download to gracefully shutdown an IT device when the UPS battery backup experiences a threatening condition. |
| 1 | IT Management | AV3216-001 ACS8016SAC-400 | Vertiv™ Avocent® AV3000 Rackmount KVM Over IP Switch CAC 8 Port KVM switches Local and Remote Access (AV3108-001). Vertiv™ Avocent ACS 8000 8-port Serial Console Server, Single AC Power (ACS8008SAC-400). |
| 1 | Warranty and Service | SVC-VRCS-INSU-M | Start-Up VRC-S with VRC Self-contained. |
| 1 | Warranty and Service | PEPPSI-30005Y | Power Emergency Package provides 5 years of coverage for electronic parts and batteries, advanced replacement. |
| 1 | Software | DSV4.5-BASE DSV4.5-100DEV 1YRSLV-100DEV | Avocent® DSView delivers secured web-browser enabled sessions of on-network infrastructure controls. As an IT integrated solution, Avocent DSView delivers secured web-browser enabled sessions to Virtual Machines. |

*Additional accessories and components are required and included in the integrated solution. Contact a Vertiv Partner for the complete bill of materials, to receive pricing, and to purchase.

Recommended Upgrades

| Qty: | Product Summary | Model #: | Description: |
|------|-----------------|---|---|
| 1 | IT Management | ACS8016-LN-DAC | The Vertiv™ Avocent® ACS8000 Serial Console System delivers secure in-band and out-of-band visibility and control to downstream equipment in enterprise data centers, as well as cloud and colocation facilities. This serial console system serves as a secure management gateway and single point of entry keeping you connected to critical IT equipment even in the event of partial or total data center outages. Includes the upgraded Cellular capability. |
| 1 | Software | ENVA-SERVER ENVA-DEV-100 ENVA-STUP-BSC ENVA-SERVER-SA ENVA-SA-100 | Vertiv™ Environet™ Alert provides industry companies with critical facility monitoring software that is affordable and easy to use. This solution delivers superior monitoring, alerting, trending and data organization capabilities for companies in such verticals as healthcare, financial services, government and more, helping them protect and grow their business. Customers get monitoring, alerting and trending at a price that's right for their business. |

Vertiv.com | Vertiv Headquarters, 1050 Dearborn Drive, Columbus, OH, 43085, USA

© 2021 Vertiv Group Corp. All rights reserved. Vertiv, and the Vertiv logo trademarks or registered trademarks of Vertiv Group Corp. All other names and logos referred to are trade names, trademarks or registered trademarks of their respective owners. While every precaution has been taken to ensure accuracy and completeness herein, Vertiv Group Corp. assumes no responsibility, and disclaims all liability, for damages resulting from use of this information or for any errors or omissions. Specifications are subject to change without notice.