

Vertiv™ BBE SE Series

UPC1000LOC, 1248LOC Broadband Edge Enclosures



Key Features

- Rugged metal housing made of mill-galvanized steel for durability and low maintenance costs.
- Our unique multi-stage paint process meets or exceeds EPA standards, and provides a tough corrosion resistant finish for longer life.
- Double-access hinged/lift-off doors offer easy access.
- Removable base cover provides simplified installation.
- Adjustable PVC-coated splice bars permit flexibility in dressing of conductors and splices.
- Close-cell neoprene door gasketing provides weatherproof protection for internal components.
- Positive action locking mechanism with padlock provisions ensures security from unauthorized entry.
- Pad- or stake-mount capability allows installation flexibility for multiple applications.

Description

UPC1000, UPC1248, UPC1252S, and UPC1278 are round-cornered rectangular-design telephone splice or equipment enclosures. Included in this series are adjustable PVC-coated splice bars, bonding and grounding bracket, and stakes (except in UPC1252S).

Application


The UPC1000, UPC1248, UPC1252S, and UPC1278 serve as above-ground housings for large PIC cable splices, load coils, and other loop treatment devices.



UPC1248

Dimensions

Catalog Number	A	B	C	D	W
UPC1000	48-in.	14-in.	33-1/8-in.	11-3/8-in.	16-1/2-in.
UPC1248	48-in.	14-in.	33-1/8-in.	11-3/8-in.	23-3/4-in.
UPC1252S	48-in.	14-in.	33-1/8-in.	11-3/8-in.	23-3/4-in.
UPC1278	60-in.	14-in.	45-in.	11-3/8-in.	23-3/4-in.



Ordering Information

Catalog Number	Part Number	Description	Splice
UPC1000	F604340	Gray-green splice enclosure	1800 pair
UPC1248	F604050	Gray-green splice enclosure	2400 pair
UPC1252S	F604590	Gray-green splice enclosure, stakes not included	2400 pair
UPC1278	F604410	Gray-green splice enclosure	2700 pair

NOTE: Total number of pairs spliced is dependent on the connector and local practices.

Accessories

Catalog Number	Part Number	Description
PADMT200300	F605650	Pad-mounting bracket for UPC1248, UPC1252S, and UPC1278

Vertiv.com | Vertiv Headquarters, 1050 Dearborn Drive, Columbus, OH, 43085, USA

© 2021 Vertiv Group Corp. All rights reserved. Vertiv™ and the Vertiv logo are trademarks or registered trademarks of Vertiv Group Corp. All other names and logos referred to are trade names, trademarks or registered trademarks of their respective owners. While every precaution has been taken to ensure accuracy and completeness here, Vertiv Group Corp. assumes no responsibility, and disclaims all liability, for damages resulting from use of this information or for any errors or omissions. Specifications, rebates and other promotional offers are subject to change at Vertiv's sole discretion upon notice.