


Disclosure and photocopying of this document, exploitation and communication of its contents are not permitted, unless permission is expressly granted. All rights are reserved.



CS8365C
 (50 A, 3/PE, 200-240 V)

OUTPUT POWER

BRANCH	PHASE	RECEPTACLE TYPE (QUANTITY)	VOLTAGE (V)	MAX. CONTINUOUS AMPS (A)	
				PER RECEPTACLE	PER BRANCH
A	L1-L2	3xC13, 1xC19	200-240	12/16	16
B	L2-L3	3xC13, 1xC19	200-240	12/16	16
C	L3-L1	3xC13, 1xC19	200-240	12/16	16
D	L1-L2	3xC13, 1xC19	200-240	12/16	16
E	L2-L3	3xC13, 1xC19	200-240	12/16	16
F	L3-L1	3xC13, 1xC19	200-240	12/16	16

AGENCY COMPLIANCE:

- UL certification: UL 60950-1 (2nd), CSA C22.2 No. 60950-1-07
- FCC certification
- CB certification: IEC 60950-1 (2nd)

ENVIRONMENTAL RATING:

OPERATING TEMPERATURE: 5 °C - 60 °C (41 °F - 140 °F) NON-CONDENSING, NON-CORROSIVE, 10 % - 90 % RH
 STORAGE TEMPERATURE: -20 °C - 85 °C (-4 °F - 185 °F)
 MAX. OPERATING ALTITUDE: 2000 m

NOTES:

- UNIT DIMENSIONS: 1826,5 mm (71,9") H x 50 mm (2,0") D x 56 mm (2,2") W
- UNIT WEIGHT: 4 kg / 8,8 lbs
- SHIPPING DIMENSIONS: 2017 mm (79,4") H x 297 mm (11,7") D x 176 mm (7,0") W
- SHIPPING WEIGHT: 6,8 kg / 15 lbs
- (2) MOUNTING BUTTONS AND (2) MOUNTING BRACKETS SUPPLIED WITH EACH UNIT. EITHER OPTION CAN BE USED TO MOUNT THE PDU.

INPUT POWER

INPUT CORD	INPUT PLUG	WIRE COUNT	FREQUENCY (Hz)	VOLTAGE (V)	RATED AMPS (A)	MAX. CONT. AMPS (A)
10 ft / 3 m	CS8365C	3/PE	50/60	200-240	50	40

METERING PARAMETER	MEASUREMENT ACCURACY
VOLTAGE	±1 % + 0.1 VAC
CURRENT	±1.5 % + 0.01 A FROM 1 % TO 10 % OF UNIT RATING; ±1 % FROM >10 % TO 125 % OF UNIT RATING

RoHS COMPLIANT

<p>Dimensions in mm</p>	Allgemeintoleranzen General tolerances		Oberfläche Finish		Werkstoff / Material		Gewicht / Weight: -
	-		-		-		-
Date		Name		Bezeichnung / Description			
10/12/15		Blass		MPH2-NRV_CS8365C_18N-60			
10/12/15		Votýpka		Input and Branch Metered + Outlet Metered/Switched			
-		-		Zeichnungs-Nr. / Drawing no.			
-		-		MPHR1124			
-		-		Verwendet in / Used in			
-		-		-			
Rev.	Change	Date	Name	Blatt/Sheet			
C	18131	31.05.2017	Petrú	1/1			
				Maßstab Scale			
				1:5			

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Alle Rechte vorbehalten.