

CFP 18.5 LCD CONSOLE

Flat Pack Local Rack Access



FEATURES

- Integrated LCD display, keyboard, mouse and switch
- 18.5 inch LED energy-saving display
- Scissors feet ultra-thin keyboard
- The machine adapts the topline type protective design and signal cable design to avoid losses caused by repeated pumping
- High quality dedicated slide rail
- Overall 1U height, suitable for standard cabinet installation
- No need for software installation, can be operated directly from the computer
- Built in 90-264V AC power supply; optional -48V telecom stage DC power supply; provides safety protection at the telecommunication level
- Automatic power protection design. When device is not in use automatically enters in protected mode
- Meets DDC/DDC2/DDC2B standards complies with VESA standards

The CFP185KMM is an LCD console tray from Vertiv that integrates the KVM Switch function of multiple ports in 1U. With space-saving and cost-efficient features, the CFP185KMM can manage multiple computers through a single set of console (LCD monitor, keyboard and mouse).

The CFP185KMM is easy to setup. Simply plug in the cables in their appropriate ports. No software required as the CFP185KMM8/16 works on any hardware platform and across all operating systems.



Technical Specifications

Model	CFP185KMM	
Display	Resolution	1366 x 768 ; DDC2B
	Display Size	18.5 Inch
	Backlight	LED
	LCD adjustment	4 x Button
	LCD on / off	1 x Button
Keyboard and Mouse	Keyboard	100 Key (83 Key keyboard +17 Key Independent digital keyboard)
	Mouse button	2 x Button
	Compatibility	Support Windows Microsoft system, support MAC system, support LINUX / UNIX/ Netware system
Built-in power supply module	AC power input	90V ~ 264V AC
	DC power input	-36 ~ 72V DC
Power	< 20 W	
Working Environment	Recommended working / Storage temperature	0-50°C / -20-60°C
	Humidity	0-80% RH, No condensation
Physical Features	Material	Metal & Plastic
	Net weight	10kg
	Equipment size (length x width x height)	594.5mm x 481mm x 42.5mm

Ordering Details

CFP185KMM - 101

CFP185KMM8 - 101

CFP185KMM16 - 101

CFP185KMM - 102

CFP185KMM8 - 102

CFP185KMM16 - 102

CFP185KMM - 202

CFP185KMM8 - 202

CFP185KMM16 - 202

VertivCo.com

© 2017 Vertiv Co. All rights reserved. Vertiv, the Vertiv logo are trademarks or registered trademarks of Vertiv Co. All other names and logos referred to are trade names, trademarks or registered trademarks of their respective owners. While every precaution has been taken to ensure accuracy and completeness herein, Vertiv Co. assumes no responsibility, and disclaims all liability, for damages resulting from use of this information or for any errors or omissions. Specifications are subject to change without notice.

Vertiv-CFP-18.5-LCD-Console-DS-EN-Asia-V1