



Geist™

Product Approval

Part Number: MGU5MGW1-36CF13-6PS6D2D10-S-A
Switched, Outlet Level Monitoring EC

Power Configuration: 63A, 230V, 14.4kW

Physical Configuration: 75in / 1905mm Vertical

Product Summary: rPDU, Switched Outlet Level Monitoring EC, 63A, 230V, 14.4kW, Vertical, (36) Combination C13/C19, 10ft / 3m power cord with 1P+N+E (IP67), Black Powder Coat.

Specifications and Options

Monitoring	Input and Outlet power monitoring with Outlet switching. Circuit/Breaker current monitoring. Environmental monitoring via optional remote sensors. Daisy chain Ethernet connectivity. Local high visibility display.
Input Monitoring	Phase (A) Monitoring (kWh, W, VA, PF, V, A) Power Measurements Compliant with ANSI C12.1 and IEC 62053-21 at 1% Accuracy Class Requirements
Circuit Monitoring	Circuit / Breaker Monitoring (A) Circuit/Breaker Current Measurements Independently Tested and Verified at 2% Accuracy
Outlet Monitoring	Outlet Monitoring (kWh, W, VA, PF, V, A) Power Measurements Compliant with ANSI C12.1 and IEC 62053-21 at 1% Accuracy Class Requirements.
Remote Power Management	Individual Outlet Switching with Optional User Defined Time Delays and Sequential Power-up
Quantity Of Inputs	1
Voltage	200-240V
Current	63A
VA per Input (Load Capacity)	14.4kW (230V)
Frequency	50/60Hz
Over Current Protection	(4) 16A Single Pole Magnetic Breakers (10kAIC Rated)
Switch	Breaker/Switch Combination
LCD Touchscreen Display / Auto Oriented	Yes
Indicators - LED(s)	36
Power Cable Wire Gauge	10mm ² H07RN-F
Power Cable Length	10ft / 3m
Power Entry Location	Top End
Plug Type	IEC60309 1P + N + E, 63A, 250V, Watertight IP67
Receptacle/Socket Type #1	Combination C13/C19

Specifications and Options Cont.

- Quantity on Face	36 (Outlet #1 Opposite Cord Entry)
- Quantity per Breaker	9
- Circuit Color ID	4 Circuit = Orange, Green, Light Orange, Light Green
- Style	Banks of 6
- Voltage per Receptacle/Socket	230V (L-N)
Network Connection	Dual 10/100Mbps Ethernet
Protocols Supported	DHCP, HTTP, HTTPS, IPv4, IPv6, LDAP, NTP, RADIUS, RSTP, SSH, SMTP, SNMP (v1/v2c/v3), Syslog, TACACS+
Data Access Formats	CSV datalog, JSON API, JSON datalog
USB Support	Yes
IP Reset Button	Yes
Hard Reboot Button	Yes
Serial Connection	RS232 via RJ45
Remote Sensor RJ Connection Jacks	1 (Supports up to 16 Sensors)
Maximum Operating Temperature	60C / 140F
Optional External Ground	Yes
Heavy Steel - Powder Coat Finish	Black
Configuration	Zero U
Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in / 1556mm and 1645mm
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	CE Marked
Certification/Agency Approvals	Complies with EN 55032 and EN 55024
Certification/Agency Approvals	Complies with IEC 62368-1 (DOC Available)
Chassis Dimensions (LxWxD)	75in x 2.2in x 3in / 1905mm x 56mm x 76mm

Americas

800.432.3219

Europe


+44 (0) 1823.275100

Asia

China
+86.755.86639505Hong Kong
+852.81764860

Confidential. Property of Vertiv.

NOTE: ALL DRAWINGS ARE SUBJECT
TO CONFIRMATION AT FINAL DESIGN
UNLESS OTHERWISE AGREED.



CIRCUIT	COLOR
1	ORANGE
2	GREEN
3	LT ORANGE
4	LT GREEN

MGU5MGW1-36CF13-6PS6D2D10-S-A

REVISION - 1


INFORMATION CONTAINED HEREON
IS PROPRIETARY AND MAY NOT
BE REPRODUCED WITHOUT WRITTEN
CONSENT OF VERTIV

DO NOT SCALE PRINT
BREAK ALL SHARP EDGES
A/R = AS REQUIRED

TOLERANCES	
Inches	
X.X	= +/-0.10
X.XX	= +/-0.03
X.XXX	= +/-0.010
ANGLES	= +/-2

VERTIV
1777 YOLANDE AVE.
LINCOLN, NE 68521
(402) 474-3400 (800) 432-3219

REFERENCE_ASM	
DWG. TITLE	
DATE	09/20/2024
SCALE	1:10
DESIGN	TBC
DRAWN	TBC
CHECKED	
APPROVED	
DWG. NO.	XXXXXXXXX
SHEET	1



INFORMATION CONTAINED HEREON IS PROPRIETARY AND MAY NOT BE REPRODUCED WITHOUT WRITTEN CONSENT OF GEIST MANUFACTURING

NOTE: ALL WIRING DIAGRAMS ARE SUBJECT TO CONFIRMATION AT FINAL DESIGN UNLESS OTHERWISE AGREED

VERTIV
1777 YOLANDE AVENUE
LINCOLN, NEBRASKA 68521
(402) 474-3400

TITLE:
MGU5MGW1-36CF13-6PS6D2D10-S-A

DRAWN:
AKG

REVIEWED:

REV:
10/03/2024

Revised: 10/8/2024

To ensure customer satisfaction with this unit, prior to acceptance of an order, Vertiv requires a signature of approval for the specification above and the terms below.

****PLEASE NOTE: THESE UNITS ARE ...NON-RETURNABLE...NON REFUNDABLE...NON-CANCELLABLE****

Specifications
Company: _____

Printed Name: _____ Title: _____

Authorized
Customer Signature: _____ Date: _____

Drawing
Company: _____

Printed Name: _____ Title: _____

Authorized
Customer Signature: _____ Date: _____

Wiring Diagram
Company: _____

Printed Name: _____ Title: _____

Authorized
Customer Signature: _____ Date: _____

Technical claims listed depend on a series of technical assumptions. Your experience with these products may differ if you operate the products in an environment which is different from the technical assumptions. Vertiv reserves the right to modify these specifications without prior notice. Vertiv makes no warranties, express or implied, on the information contained in this document.