



Vertiv™ Edge Lithium-Ion UPS

1500 – 3000VA 230V

High Performance
Line-Interactive Power
Protection for Servers and
Networking Equipment



Lithium-ion
Batteries


Vertiv™ Edge Lithium-Ion UPS

The Vertiv™ Edge Lithium-Ion line-interactive UPS provides a high level of power protection to your business-critical applications.

The Vertiv Edge Lithium-Ion line-interactive UPS provides both power conditioning and battery backup to critical IT equipment such as servers and network gear ensuring your business-critical applications are protected in the event of an unanticipated loss of power or an unprecedented power surge.

The Vertiv Edge Lithium-Ion UPS protects against a wide range of power fluctuations and automatically switches to battery backup when power loss is detected. With a 0.9 output power factor (PF) and less than 6 millisecond transfer time, you can ensure your most critical assets are protected.

Protects Against



High Performance Line-Interactive Power Protection


The rack-mount design of the Vertiv Edge Lithium-Ion UPS is ideal for server rooms, network closets, and other edge or distributed IT applications within small and medium businesses where floor space is at a premium. It is a true low-maintenance, set-it and forget-it solution ideal for remote locations with limited onsite technical resources.

Vertiv Edge Lithium-Ion Overview

- 1500VA, 2200VA, & 3000VA UPSs in a rack/tower convertible form factor
- Standard 5-year warranty provides peace of mind your investment is protected against potentially costly equipment failures
- Achieve the lowest total cost of ownership over the lifetime of the UPS with fewer battery replacements and up to 10 years of useable life
- Hot-swappable, user-replaceable batteries increase the useable life of the UPS by allowing you to easily replace the batteries without disrupting power to connected equipment
- Internal batteries offer industry-leading runtime (up to 10 minutes at full load) to protect critical equipment during an unexpected power loss
- Lithium-Ion battery technology degrades slower in high temperature environments, supports up to 10 times more discharge cycles, and delivers faster recharge times compared to VRLA batteries

Why should you choose Lithium-Ion Technology?


LONGER LIFE



LOWER TCO



SMALLER & LIGHTER




LONGER RUNTIME



ENVIRONMENTALLY FRIENDLY



FAST BATTERY RECHARGE



Lithium-Ion technology delivers up to 3 times the life expectancy of lead-acid batteries and lowers the total cost of ownership by nearly half


Lithium-Ion Outperforms VRLA when compared...

Battery Feature	VRLA Battery	Li-ion battery	Lithium-Ion Benefit
Standard battery life	3-5 years	8-10 years	Up to 3 times longer life
Typical cycle life	200-260	2000	Up to 10x more discharge/recharge cycles
Battery recharge time (@ 90%)	3-6 hours	<2 hours	Fast recovery time safeguards your critical IT equipment in the event of multiple outages
Battery weight	10.9 kg	5.9 kg	45% lighter making it ideal for small spaces and wall-mount racks
Warranty	2 or 3 years	5 years	Worry free operation so you can set-it and forget-it

Visit the TCO calculator at <https://www.vertiv.com/en-emea/support/tools-and-application/tco-calculator/>

Build Your Total Infrastructure Solution with Vertiv

Discover expert designed IT infrastructure solutions with proven success in diverse environments and countless applications.



Vertiv™ Geist™ rPDU
Reliable power distribution with outlet level remote monitoring and management providing the highest level of power visibility and control.

Cable and Air Flow Management
Included accessories ensure proper cable management and airflow to keep your equipment cool.

Software and IT Management
Monitor the entire system either locally or remotely to ensure you are alerted of out-of-range conditions that could result in costly downtime.

Vertiv™ Edge Lithium-Ion UPS
Protect mission critical equipment in the event of power loss or extreme power fluctuations.

Vertiv™ VR Rack
Self-contained 42U server rack designed to simplify equipment installation and provides an additional 6cm of useable depth.

Vertiv™ VRC
Keep critical IT equipment cool with a dedicated high-efficiency rack-mount cooling system with scalable capacity.

Visit [Vertiv.com](https://www.vertiv.com) or contact a Vertiv Sales Representative today to find out how Vertiv can help you configure an all-in-one infrastructure solution.

High Performance



0.9 Output Power Factor (PF): Provides more useable power enabling you to connect more equipment saving you money and space.



Increased Runtime: Internal batteries offer up to 10 minutes of runtime at full load.

Programmable Outlet Group: Extend run time when on battery power by power-cycling connected equipment and shedding less critical loads.



Battery Backed Outlets: Up to 7 battery backed outlets ensuring critical equipment is protected.

Advanced Warning Status: Receive early audible and visual alarms warning you of system status to alert you to an input voltage fluctuation (buck/boost) output overload, low battery, or battery replacement condition.

Wide Input Voltage Range: Prolong battery life by allowing the UPS to maximize the use of the utility power before transferring to battery.

Superior Battery Technology



Fewer Battery Replacements: Lithium-Ion batteries require fewer battery replacements and last on average up to 3 times as long as traditional VRLA batteries reducing maintenance, labor, and replacement costs (lower TCO).

More Discharge Cycles: Lithium-Ion batteries deliver up to 10 times more charge / discharge cycles than VRLA batteries.

Fast Recharge: Lithium-Ion batteries recharge twice as fast as traditional VRLA batteries getting you back to 90% in as little as 2 hours.

Hot-Swappable, User-Replaceable Batteries: Increase product life and reliability with batteries that can be easily replaced without disrupting power to connected equipment.

Environmentally Friendly: Significantly reduce battery disposal and recycling with lower replacement rates.

Enhanced Manageability



LCD Display: User-friendly full-color LCD interface with gravity sensing orientation simplified installation and configuration while also providing instant at-a-glance status and insights.

Free Power Management Software:

- Vertiv™ [Power Insight](#) – Add the Liebert® IntelliSlot Communications card for web/SNMP manageability
- Vertiv™ [Power Assist](#) – Monitor UPS conditions through a local USB connection
- Vertiv™ Intelligence Director – Together with Vertiv™ Geist™ rPDU one single IP Address to monitor and manage up to 50 devices

Remote Monitoring and Management: Add an optional Liebert® IntelliSlot communication card to enable remote monitoring / management (web based, SNMP, BACnet, MODBUS and relay contacts) and environmental monitoring via external sensors.

Remote Emergency Power Off: Remotely shutdown the UPS during an emergency.

Comprehensive Services for Critical Systems

Power Emergency Package

The Power Emergency Package provides emergency support with 100% parts coverage and is available for single-phase UPS products up to 3kVA. Adding Vertiv services to your Vertiv™ Edge Lithium-Ion UPS ensures you are protected during an emergency.

- Five years service coverage (10 with renewal)
- 24x7 professional Helpline
- Advanced replacement of the faulty unit
- Shipping costs covered by Vertiv
- Coverage for both electronic parts and battery failures
- The Power Emergency Premier version also provides remote diagnostic and preventive monitoring with Vertiv™ LIFE™ Services, enabled via the optional Liebert® Intellislot Communications Card




Installation and Start-up Services

Installation and Start-up Services provide on-site technical support for installation and start-up of your UPS or battery cabinet, ensuring you get up and running as quickly as possible:

- Installation includes mounting the new UPS and battery cabinets
- Start-up available in 2 scheduling options, in 8x5 or 24x7
- Services performed by a Vertiv factory trained technician

Service Part Number	Description	UPS applicable
RUPS-PE5-003	Power Emergency 5YR-8HR RESP8X5 Group 3	EDGELI-1500IRT2U EDGELI-2200IRT2U
RUPS-PE5-004	Power Emergency 5YR-8HR RESP8X5 Group 4	EDGELI-3000IRT2U
RUPS-PE5-005	Power Emergency 5YR-8HR Premier	EDGELI-3000IRT2U
PS-RUPS-INSTL247-005	Installation 1PH UPS 24X7 Group 5	EDGELI-3000IRT2U
PS-RUPS-ST85-005	Startup 1PH UPS 8X5 Group 5	EDGELI-3000IRT2U
PS-RUPS-ST247-005	Startup 1PH UPS 24X7 Group 5	EDGELI-3000IRT2U

Note: Service offerings are available only in select countries, please check with your Vertiv representative if yours is included. Timing may vary depending on local country public holidays and other considerations. Please refer to the appropriate Scope of Work for additional details.



- 1 Input circuit breaker
- 2 AC Input
- 3 USB communication port
- 4 IntelliSlot port (optional communications card)
- 5 Programmable output receptacles (1 group)
- 6 Non-programmable output receptacles
- 7 Emergency Power Off (EPO) connector
- 8 Output circuit breakers
- 9 Earth terminal

What's In The Box

- Vertiv™ Edge Lithium-Ion UPS
- USB type A to B cable
- 4-post rail kit
- Screws, ears and mounting hardware
- Tower feet
- 2 x IEC C13 to C14 output cables
- Input power cables (UK, AUS, Schuko)
- Vertiv™ Power Assist and Vertiv™ Power Insight management software ([free download](#))
- Quick Installation Guide
- Safety Instructions

Vertiv™ Edge Lithium-Ion UPS

Technical Specifications

	EDGELI-1500IRT2U	EDGELI-2200IRT2U	EDGELI-3000IRT2U
Power Rating (VA/W)	1500VA / 1350W	2200VA / 1980W	3000VA / 2700W
Form Factor	Rack / Tower (2U)	Rack / Tower (2U)	Rack / Tower (2U)
Dimensions, mm			
Unit (W x D x H)	438 x 410 x 86	438 x 510 x 86	438 x 630 x 86
Shipping (W x D x H)	550 x 620 x 240	565 x 700 x 240	600 x 800 x 240
Weight, kg			
Unit	12.8	17.5	24.3
Shipping	20.4	25.2	32.1
Input AC Parameters			
Voltage Range Without Battery Operation (230V default)	166 - 278V	166 - 278V	166 - 278V
Frequency Range	45 - 65Hz, autosensing	45 - 65Hz, autosensing	45 - 65Hz, autosensing
Input Power Connector	IEC60320 C14	IEC60320 C20	IEC60320 C20
Surge Protection	624J	624J	624J
Output AC Parameters			
Output Receptacles	3 + 3 IEC60320 C13	3 + 3 IEC60320 C13 + 1 IEC60320 C19	3 + 3 IEC60320 C13 + 1 IEC60320 C19
Output Receptacles - Controllable	Yes - 1 group (3 x IEC60320 C13)	Yes - 1 group (3 x IEC60320 C13)	Yes - 1 group (3 x IEC60320 C13)
Output Voltage	200/208/220/230 (default) /240	200/208/220/230 (default) /240	200/208/220/230 (default) /240
Waveform (Battery Operation)	Pure Sine Wave	Pure Sine Wave	Pure Sine Wave
Transfer Time	4 - 6 ms Typical	4 - 6 ms Typical	4 - 6 ms Typical
Output Overload (AC Mode)	111% - 120% @ 10 s > 121% - Shutdown	111% - 120% @ 10 s > 121% - Shutdown	111% - 120% @ 10 s > 121% - Shutdown
Efficiency (full load, interactive mode)	97.5%	98.5%	98.5%
Battery			
Type	Li-ion (LiFePo4)	Li-ion (LiFePo4)	Li-ion (LiFePo4)
Quantity & Voltage & Capacity	1 x 48V x 5Ahr	2 x 72V x 2.5Ahr	3 x 72V x 2.5Ahr
Recharge Time (90% / 100%, from full discharge)	1.7 hrs / 1.9 hrs	1.7 hrs / 1.9 hrs	2.4 hrs / 2.7 hrs
Full-Load Runtime	8.7min	9.3min	10.5min
Half-Load Runtime	18.5min	20.2min	22.6min
Environmental			
Operating Temperature	0 to 40°C	0 to 40°C	0 to 40°C
Storage Temperature	-10°C to +45°C	-10°C to +45°C	-10°C to +45°C
Relative Humidity (Operation)	8% to 90%, non-condensing	8% to 90%, non-condensing	8% to 90%, non-condensing
Operating Altitude (without derating)	3000m	3000m	3000m
Audible Noise (line mode)	<45dBA AVR mode, >70% load < 55dBA Battery mode	<45dBA AVR mode, >70% load < 55dBA Battery mode	<45dBA AVR mode, >70% load < 55dBA Battery mode
Agency			
Compliance*	CE, CB Report, EAC, RCM, UKCA	CE, CB Report, EAC, RCM, UKCA	CE, CB Report, EAC, RCM, UKCA
Safety	EN62040-1:2008+A1:2013 CB - IEC62619 li-ion battery	EN62040-1:2008+A1:2013 CB - IEC62619 li-ion battery	EN62040-1:2008+A1:2013 CB - IEC62619 li-ion battery
Environmental	RoHS2 / REACH / WEEE	RoHS2 / REACH / WEEE	RoHS2 / REACH / WEEE
Transportation	ISTA 2A UPS UN38.3 (Lithium-Ion)	ISTA 2A UPS UN38.3 (Lithium-Ion)	ISTA 2A UPS UN38.3 (Lithium-Ion)
Communications and Management			
Slot for optional cards	Yes	Yes	Yes
Communication port	USB	USB	USB
Emergency Power Off (EPO)	Yes	Yes	Yes
Warranty			
Warranty	5 years on UPS and Battery	5 years on UPS and Battery	5 years on UPS and Battery

*For a full list of compliance certificates please contact your local Vertiv representative.

Vertiv™ Edge Lithium-Ion UPS Runtimes

**Vertiv™ Edge Lithium-Ion 1500VA
EDGELI-1500IRT2U**

Load%	VA	Watts	Runtime (min)
100%	1500	1350	8.7
90%	1350	1215	9.7
80%	1200	1080	11.1
70%	1050	945	12.9
60%	900	810	15.3
50%	750	675	18.5
40%	600	540	23.5
30%	450	405	31.4
20%	300	270	43.7
10%	150	135	84.9

**Vertiv™ Edge Lithium-Ion 2200VA
EDGELI-2200IRT2U**

Load%	VA	Watts	Runtime (min)
100%	2200	1980	9.3
90%	1980	1782	10.5
80%	1760	1584	12.0
70%	1540	1386	13.9
60%	1320	1188	16.6
50%	1100	990	20.2
40%	880	792	25.5
30%	660	594	34.3
20%	440	396	47.1
10%	220	198	90.7

**Vertiv™ Edge Lithium-Ion 3000VA
EDGELI-3000IRT2U**

Load%	VA	Watts	Runtime (min)
100%	3000	2700	10.5
90%	2700	2430	11.8
80%	2400	2160	13.5
70%	2100	1890	15.6
60%	1800	1620	18.6
50%	1500	1350	22.6
40%	1200	1080	28.6
30%	900	810	38.5
20%	600	540	52.4
10%	300	270	102.6

Vertiv™ Edge Lithium-Ion Accessories


MicroPOD – Maintenance Bypass and Output Distribution

UPS Model Number	MicroPOD Model Number	Input Connection	Output Connection
EDGELI-1500IRT2U	MP2-210K	IEC60320-C14	4+4 IEC60320-C13
EDGELI-2200IRT2U	MP2-220L	IEC60320-C20	2+2+2 IEC60320-C13 & 1 IEC60320-C19
EDGELI-3000IRT2U	MP2-220L	IEC60320-C20	2+2+2 IEC60320-C13 & 1 IEC60320-C19



Internal Battery Replacement Kits

Model Number	Applicable To	Description
PSI5-1500LIBATKIT	EDGELI-1500IRT2U	48V x 5Ahr (LiFe-485000 x 1)
PSI5-2200LIBATKIT	EDGELI-2200IRT2U	72V x 2.5Ahr (LiFe-722500 x 2 parallel)
PSI5-3000LIBATKIT	EDGELI-3000IRT2U	72V x 2.5Ahr (LiFe-722500 x 3 parallel)



Vertiv™ Edge Lithium-Ion UPS

Network Communication Cards and Environmental Sensors

Optional Intellislot cards are compatible with all Vertiv™ Liebert® Edge UPS systems



**IS-UNITY-DP and
IS-UNITY-SNMP
Network Cards are in
Phase Out**

Network Communications	RDU120	Network Communication Card with 10/100/1000 Mbps Ethernet, web interface, SNMP, BACnet IP/MSTP, Modbus TCP/RTU and environmental sensor support. UL-2900-1 certified. Includes a configuration cable.
	IS-UNITY-SNMP*	10/100 Mbit Ethernet SNMP, Device Web Page, with MIB and configuration cable
	IS-UNITY-DP*	Same as IS-UNITY-SNMP plus SN series environmental sensor support
	IS-RELAY	Intellislot Interface Kit for Relay Contacts
UNITY Card Environmental Sensors	SN-Z01	Integrated cable with single temperature sensor
	SN-Z02	Integrated cable with three temperature sensors
	SN-Z03	Integrated cable with three temperature and one humidity sensors
	SN-T	Modular with single temperature sensor
	SN-TH	Modular with single temperature and single humidity sensor
	SN-2D	Modular with two door contact inputs
	SN-3C	Modular with three dry contact inputs
	SN-L20	Modular leak zone sensor with 20 foot cable (Liebert RDU-S only)
RDU120 Card Environmental Sensors	A2D-10	Analog to digital converter provides the ability to connect a dry contact, 0-10V, or 4-20mA sensor to a Plug-n-Play sensor port. Includes a 10ft / 3m cable.
	A2D-50	Analog to digital converter provides the ability to connect a dry contact, 0-10V, or 4-20mA sensor to a Plug-n-Play sensor port. Includes a 10ft / 3m cable.
	GT3HD	Temperature, humidity, and dew point sensor with dual inputs for included 3ft / .9m and 6ft / 1.8m temperature sensors for monitoring top, middle, and bottom of a rack or cabinet. Includes a supplementary input for daisy-chaining additional sensors. Includes 10ft / 3m cable.
	GT3HD-50	Temperature, humidity, and dew point sensor with dual inputs for included 3ft / .9m and 6ft / 1.8m temperature sensors for monitoring top, middle, and bottom of a rack or cabinet. Includes a supplementary input for daisy-chaining additional sensors. Includes 50ft / 15.2m cable.
	GTHD	Temperature, humidity, and dew point sensor. Includes a supplementary input for daisy-chaining additional sensors. Includes 10ft / 3m cable.
	GTHD-50	Temperature, humidity, and dew point sensor. Includes a supplementary input for daisy-chaining additional sensors. Includes 50ft / 15.2m cable.
	SRT-12	Temperature sensor used to monitor temperature in critical environments. Includes a 12ft / 3.6m cable.
	SRT-20	Temperature sensor used to monitor temperature in critical environments. Includes a 20ft / 6.1m cable.
	SRT-50	Temperature sensor used to monitor temperature in critical environments. Includes a 50ft / 15.2m cable.
	SRT-100	Temperature sensor used to monitor temperature in critical environments. Includes a 100ft / 30.4m cable.
	RTAFHD3-12	Temperature, airflow, humidity, and dew point sensor. Includes 12ft / 3.6m cable.
	RTAFHD3-20	Temperature, airflow, humidity, and dew point sensor. Includes 20ft / 6.1m cable.
	RTAFHD3-50	Temperature, airflow, humidity, and dew point sensor. Includes 50ft / 15.2m cable.
	RTAFHD3-100	Temperature, airflow, humidity, and dew point sensor. Includes 100ft / 30.4m cable.
	FS-15	0-5VDC conductivity based flood sensor used to detect the presence of water. Includes a 15ft / 4.5m cable.
	FS-100	0-5VDC conductivity based flood sensor used to detect the presence of water. Includes a 100ft / 30.4m cable.
	RDPS	Magnetic normally-closed dry-contact sensor used to monitor remote door position. Includes 30ft / 9.1m cable.
	RDPS-50	Magnetic normally-closed dry-contact sensor used to monitor remote door position. Includes 50ft / 15.2m cable.
	RDPS-100	Magnetic normally-closed dry-contact sensor used to monitor remote door position. Includes 100ft / 30.4m cable.
	PFS-100 US	0-5V power failure sensor to monitor the presence of utility power. Includes a 100ft / 30.4m cable and US NEMA power supply

*IS-UNITY-DP and IS-UNITY-SNMP Network Communications Card are being phased out and will remain available for purchase only until Dec 2025.

Vertiv™ UPS Software Benefits Ladder

Feature	Power Assist	Power Insight	Environet™ Alert	DSView Solutions	Environet™ Connect
Management					
Mass Firmware Upgrade (Network Card only)				•	•
Hypervisor Plugin		vCenter, vXRail, Nutanix			
Automated Server Shutdown	•	•			
Reporting					
Analytics and Reporting			•		•
Historical Data		•	•		•
Thresholds and Alerts		•	•	•	•
Alarm Management	•	•	•	•	•
Monitoring					
IT Device Monitoring				•	
Thermal Monitoring			•		•
Power Monitoring	UPS Only	UPS and Rack PDU	•	UPS, Rack PDU, Servers	•
Specifications					
Protocol Support	USB/SNMP	SNMP	SNMP, Modbus TCP, BACnet IP	SNMP, IPMI, Redfish	SNMP
Equipment Support	Vertiv Only	Vertiv Only	Multi-Vendor	Multi-Vendor	Multi-Vendor
Max. Devices Support	2	100	Scalable	Scalable	Scalable
Software Architecture	On-prem	On-prem	On-Prem	On-Perm	Multi-Tenant Cloud based
Licensing	Free	Free	Perpetual	Subscription	Subscription

