






- | | |
|--|---|
| ① LIEBERT INTELLISLOT PORT | ⑨ OUTPUT RECEPTACLE AND CABLE L6-20R |
| ② TERMINAL BLOCK COMMUNICATION | ⑩ OUTPUT RECEPTACLE AND CABLE L6-20R |
| ③ USB PORT | ⑪ OUTPUT CIRCUIT BREAKER FOR L6-20R (NOTE 10) |
| ④ RS-485 PORT | ⑫ OUTPUT RECEPTACLE AND CABLE L6-30R |
| ⑤ RS-232 PORT | ⑬ OUTPUT CIRCUIT BREAKER FOR L6-30R |
| ⑥ REPO CONNECTOR | ⑭ MAINTENANCE BYPASS BREAKER |
| ⑦ EXTERNAL BATTERY CONNECTOR | ⑮ INPUT CIRCUIT BREAKER FOR L6-30P |
| ⑧ OUTPUT CIRCUIT BREAKER FOR L6-20R (NOTE 9) | ⑯ INPUT PLUG AND CABLE L6-30P |

NOTES:

- UNIT DIMENSIONS (WxDxH): 430mm x 631mm x 217mm (5U)
(16.9") x (24.9") x (8.5")
- UNIT WEIGHT: 68kg (149.9lbs)
- SHIPPING DIMENSIONS (WxDxH): 646mm x 816mm x 520mm
(25.4") x (32.1") x (20.5")
- SHIPPING WEIGHT: 92kg (202.8lbs)
- MINIMUM AIRFLOW CLEARANCE IS 100mm (4.0") FRONT AND REAR.

DRAWN BY B. LAY	SHEET NO. 1 OF 1
CHK BY M. MCCLINCY	ECN NO.
REF. DWG.	ORDER NO.

OUTLINE DRAWING
LIEBERT GXT5 6kVA
208VAC RACK/TOWER UPS

DWG. NO.
GXT5-6K630HV_OD

DATE
6/17/19

REV. #
0

1050 DEARBORN DRIVE
P.O. BOX 29186
COLUMBUS, OHIO 43229

