

Vertiv™ PowerGo

-  Simplified Power Distribution
-  Enhanced Reliability
-  Ease of Use
-  Essential Features Built In
-  Right-Sized for Your Environment
-  Consistent Performance



Affordable, reliable, and easy to deploy

- Designed for quick and easy deployment in network closets, data centers and industrial applications.
- Suitable for budget-friendly power distribution and power management.
- Designed for fast-moving, price-sensitive IT deployments - without compromising on Vertiv reliability. The perfect balance of value and performance.

 Type	 Receptacles	 Monitoring - IMD-3x:	 Certifications	 Magnetic Breakers Protection
- Basic - Monitored Unit Level - Switched Unit Level	- Manual lock C13 - Manual lock C19 - German Schuko	- LED display and remote monitoring - Input power monitoring with 1% accuracy - Dual 10/100 Mbps Ethernet - Remote outlet control* - Daisy-chain and fault-tolerant connectivity *Available on switched unit level models.	- CE Marked - FCC Marked - IEC 62368-1 - EN 55032 - EN 55035 - RoHS	From 32A PDU's

For combination outlets, environmental monitoring upgradability and customization, explore PowerIT rPDU product line.

KEY HIGHLIGHTS



Basic distribution and monitoring needs



Price assessable to all



Good performance



2 years warranty

Discover All Models

