

OVERVIEW

Upgradeable Metered rPDUs provide reliable power distribution to critical IT equipment within a rack or cabinet while delivering a view of real-time view of power usage from a local LED display.

Benefits

- With the Geist Upgradeable hot-swap technology, users may easily transform metered rPDUs to monitored rPDUs with the addition of the appropriate Interchangeable Monitoring Device (IMD).
- Avoid accidental overloads when deploying or moving critical server equipment with instant access to power consumption metrics on the local digital display.
- Gather comprehensive power data at the palm of your hand with the use of the Vertiv VLC mobile app.
- Every unit is 100% tested for reliability and functionality.
- Simple and convenient configuration options for cord lengths and chassis colors.



Part #: G110097

Model Number: MG01D4B0-36CF13-2PS6B2A10-S

Category: Metered

Sub Category: Upgradeable

Power Configuration: 16A, 230V, 3.6kW

Physical Configuration: 66in / 1683mm, Vertical

Product Summary:

rPDU, Metered Upgradeable, 16A, 230V, 3.6kW, Vertical, (36) Combination C13/C19, 10ft power cord with 1P+N+E (IP44), Black Powder Coat.

Monitoring:

Input current monitoring. Local high visibility LED display. Input power monitoring available via VLC feature using the Vertiv rPDU Scanner app.

Plug Form:



1P+N+E (IP44)

Receptacle:



Combination C13/C19
(Quantity: 36)

Chassis Color Options:



To discuss color options, contact your local sales representative.

Product Specification and Options

System Features

Monitoring

Input current monitoring. Local high visibility LED display. Input power monitoring available via VLC feature using the Vertiv rPDU Scanner app.

Monitoring Level 1	Phase (A) Monitoring (kWh, W, VA, PF, V, A)
	Power Measurements Compliant with ANSI C12.1 and IEC 62053-21 at 1% Accuracy Class Requirements
VLC Support	Yes
Quantity Of Inputs	1
Voltage	200-240V
Current	16A
VA per Input (Load Capacity)	3.6kW (230V)
Frequency	50/60Hz
Over Current Protection	None
Switch	No
Scrolling / Rotatable Digital Display	Yes
Power Cable Wire Gauge	2.5mm² H07RN-F
Power Cable Length	10ft / 3m
Power Entry Location	Bottom Front
Plug Type	IEC60309 1P + N + E, 16A, 250V, Splashproof IP44
Receptacle/Socket Type #1	Combination C13/C19
- Quantity on Face	36
- Circuit Color ID	1 Circuit = Orange
- Style	Banks of 6
- Voltage per Receptacle/Socket	230V
Internal RMS Voltage Sensor	Yes
Internal RMS Current Sensor	Yes
Maximum Operating Temperature	60C / 140F
Heavy Steel - Powder Coat Finish	Black
Configuration	Zero U
7938 Vertical Mounting Bracket Kit	Yes
Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in / 1556mm and 1645mm
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	CE Marked
Certification/Agency Approvals	Complies with EN 55032 and EN 55024
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	RCM Mark (EMC Only)
Certification/Agency Approvals	Complies with IEC 62368-1 (DOC Available)
Certification/Agency Approvals	China RoHS
Chassis Dimensions (LxWxD)	66.25in x 2in x 2in / 1683mm x 51mm x 51mm
Shipped Weight	15lbs (6.8kg)