Liebert® PSI5 Lithium-Ion TAA UPS



Superior Power Protection for Edge Applications, Telecom, and Distributed IT Equipment

Overview

Lithium-Ion Battery Technology

Lithium-ion is a game-changing technology when it comes to UPS batteries. When compared to traditional valve-regulated-lead-acid (VRLA) batteries, Lithium-ion batteries have greater power density, last up to 3 times longer, recharge much more quickly, and can endure up to 10x more discharge cycles. With a 5 year standard warranty, more than double the useful life, and significantly more runtime, the Liebert* PSI5 Lithium-lon UPS is at the top of its class.

Liebert PSI5 Lithium-Ion Key Benefits vs VRLA

- Up to 3x battery life
- Lowest TCO
- 5 year standard warranty on UPS and Batteries
- Longer Runtime
- Quicker recharge times
- Smaller and lighter:
 - Greater power density
 - Reduced unit depth
- Up to 10x more discharge cycles
- Greater battery performance in higher temperature environments

















Lower Total Cost of Ownership (TCO)

The Liebert PSI5 Lithium-Ion line-interactive UPSs are ideally suited to protect critical infrastructure in edge or distributed IT applications. The life expectancy of Lithium-Ion batteries is up to three times that of VRLA batteries up to 10 years. That delivers 50% or more in TCO savings vs. VRLA batteries, chiefly because the Liebert PSI5 Lithium-Ion requires fewer battery replacements over its lifespan. You save not only on the cost of batteries but on the labor required to replace them - an especially significant issue at remote locations with few or no IT personnel on site. In short, the Liebert PSI5 Lithium-Ion UPS is a true low-maintenance, set-it-and-forget-it solution.


Lower TCO



Smaller & Lighter



Longer Life



Longer Runtime



What's In The Box

- UPS Unit
- USB Type A to USB Type B cable
 1.8 meter (6ft) in length
- Printed quick start guide with safety instructions
- 4 Post Rack Mounting Kit
- Support base for tower configuration
- Free download <u>Power Assist</u>, <u>Power Insight software</u>



Technical Specifications

Standard Models*	PSI5-1500RT120LITAA	PSI5-2200RT120LITAA	PSI5-3000RT120LITAA
Form Factor	2U Rack/Tower	2U Rack/Tower	2U Rack/Tower
Power Rating	1500VA / 1350W	1920VA / 1920W	3000VA / 2700W
Dimensions, W X D X H, IN (MM)			
Unit	17.2 x 16.2 x 3.4 (438 x 411 x 86)	17.2 x 20.1 x 3.4 (438 x 510 x 86)	17.2 x 24.8 x 3.4 (438 x 630 x 86)
Rackmount Depth	15" (380mm)	18.9" (480mm)	23.62" (600mm)
Shipping	10.2 x 22.9 x 22.4 (258 x 582 x 570)	10.2 x 26.5 x 22.4 (258 x 672 x 570)	10.2 x 30.8 x 21.7 (258 x 782 x 550)
Weight, LB (KG)	(236 x 362 x 370)	(236 X 0/2 X 3/0)	(238 x 762 x 330)
Unit	28.3 (12.9)	39.5 (18.0)	53.5 (24.3)
Shipping	42.1 (19.1)	53.8 (24.4)	67.9 (30.8)
Input/Output AC Parameters			
Input Plug	NEMA 5-15P	NEMA L5-20P	NEMA L5-30P
Input Cord	8ft (3m)	8ft (3m) L5-20, 5-20P adapter	8ft (3m)
Non-Programmable Receptacles	(3) NEMA 5-15R	(1) NEMA L5-20R,	(1) NEMA L5-30R,
Programmable Receptacles	(3) NEMA 5-15R	(3) NEMA 5-20R	(3) NEMA 5-20R (3) NEMA 5-20R
Nominal Voltage Setting		(3) NEMA 5-20R IVAC Default; 100/110/115/125VAC User Select	
Voltage Range Without Battery Operation	75 - 146VAC		
Frequency Range	55 to 65Hz (57-63Hz Battery to Normal Comeback)		
Surge Protection	ANSI C62.41, Category A, Level 3		
Transfer Time	4 - 6ms Typical		
Battery Waveform	Pure Sine Wave		
Efficiency		Tule one wave	
Normal (Line) Mode	98.6%	98.5%	98.4%
Battery Parameters			
Туре		Lithium-Ion (LiFePO4)	
Recharge Time (from full discharge)	2hrs to 90%	2hrs to 90%	2hrs to 90%
Full-Load Runtime	7.5 min	8.6min	8.9min
Half-Load Runtime	17.7 min	19.0min	20.0 min
Environmental			
Operating Temperature,°F (°C)	32° to 104° (0° to 40°)		
Storage Temperature °F (°C)	5° to 120° (-15° to 50°)		
Relative Humidity	20% – 90%, non-condensing		
Operating Altitude, ft (m)	0 to 9,942 (0 to 3,000) without derating.		
Audible Noise	< 45 dB @ line mode, < 55 dB @ battery mode		
Certifications			
Safety	UL 1642 (LiFe cells), UL 1973 (LiFe pack), UL 1778, CSA 22.2 no. 107.3		
Agency	UL 1778, c-UL, NOM, FCC Part 15, Class B, Energy Star		
Environmental	RoHS2 / REACH / WEEE		
Network Surge	ANSI C62.41, Category A, Level 3		
	ISTA Procedure 2A UN 38.3 (Lithium-ion)		
Transportation		UN 38.3 (Lithium-ion)	
Transportation Warranty		UN 38.3 (Lithium-ion) 5 years on UPS and Battery	

^{*} Liebert* PSI5 UPS + IS-UNITY-SNMP card bundles available - Add an "N" to the end of the model number. Available through select distributors."

Vertiv.com | Vertiv Headquarters, 1050 Dearborn Drive, Columbus, OH, 43085, USA

© 2022 Vertiv Group Corp. All rights reserved. Vertiv[™] and the Vertiv logo are trademarks or registered trademarks of Vertiv Group Corp. All other names and logos referred to are trade names, trademarks or registered trademarks of their respective owners. While every precaution has been taken to ensure accuracy and completeness here, Vertiv Group Corp. assumes no responsibility, and disclaims all liability, for damages resulting from use of this information or for any errors or omissions. Specifications, rebates and other promotional offers are subject to change at Vertiv's sole discretion upon notice.