

OVERVIEW

Upgradeable Switched Unit Level Monitored rPDUs provide reliable power distribution to critical IT equipment while delivering individual outlet level control and a comprehensive view of input power usage via remote network access. Includes environmental monitoring capabilities to obtain real-time environmental metrics. Upgrade the hot-swappable monitoring device on select units to leverage new technologies and accommodate changing business needs.

Benefits

- Remotely reboot outlets to power cycle unresponsive IT equipment or increase runtime of critical equipment upon power failure with outlet-level control.
- Reliable power distribution with local and remote power monitoring options offer quick access to critical power usage information to evaluate energy usage trends and maximize uptime.
- Environmental monitoring capabilities with the addition of optional environmental sensors ensure users have critical infrastructure data at their fingertips to prevent climate-related equipment failure and system downtime.
- Fault-Tolerant Daisy Chaining with RSTP simplifies intelligent rPDU connectivity and ensures data is reported even when a break in the network chain occurs. Supports up to 40 rPDUs.
- Daisy-chain up to 50 devices on a single IP address and reduce



Part #: VP5N11A0

Model Number: MNS5M1R5-06S153-1ST5A0H10-S

Category: Switched

Sub Category: Unit Level Monitoring

Power Configuration: 15A, 120V, 1.4kW

Physical Configuration: 19in / 483mm, Horizontal

Product Summary:

rPDU, Switched Unit Level Monitoring EC, 15A, 120V, 1.4kW, Horizontal, (6) NEMA 5-15R, 10ft / 3m power cord with 5-15P, Black Powder Coat.

Monitoring:

Input power monitoring with Outlet switching. Environmental monitoring via optional remote sensors. Daisy chain Ethernet connectivity. Local high visibility display.

Plug Form:



5-15P

Receptacle:



NEMA 5-15R
(Quantity: 6)

Chassis Color Options:



deployment time with self-configuration of downstream devices.

To discuss color options, contact your local sales representative.

Product Specification and Options

System Features

Monitoring	Input power monitoring with Outlet switching. Environmental monitoring via optional remote sensors. Daisy chain Ethernet connectivity. Local high visibility display.
Input Monitoring	Phase (A) Monitoring (kWh, W, VA, PF, V, A)
	Power Measurements Compliant with ANSI C12.1 and IEC 62053-21 at 1% Accuracy Class Requirements
Remote Power Management	Individual Outlet Switching with Optional User Defined Time Delays and Sequential Power-up
Quantity Of Inputs	1
Voltage	100-120V
Current	15A
VA per Input (Load Capacity)	1.4kW (120V)
Frequency	50/60Hz
Over Current Protection	None
Switch	No
LCD Touchscreen Display / Auto Oriented	Yes
Indicators - LED(s)	6
Power Cable Wire Gauge	14/3
Power Cable Length	10ft / 3m
Power Entry Location	Rear
Plug Type	NEMA 5-15P
Receptacle/Socket Type #1	NEMA 5-15R
- Quantity on Rear	6
- Style	Individual
- Voltage per Receptacle/Socket	120V
Network Connection	Dual 10/100/1000Mbps Ethernet
Protocols Supported	DHCP, HTTP, HTTPS, IPv4, IPv6, LDAP, NTP, RADIUS, RSTP, SSH, SMTP, SNMP (v1/v2c/v3), Syslog, TACACS+, Modbus TCP
Data Access Formats	CSV datalog, JSON API, JSON datalog
USB Support	Yes
IP Reset Button	Yes
Hard Reboot Button	Yes
Serial Connection	RS232 via RJ45
Remote Sensor RJ Connection Jacks	1 (Supports up to 16 Sensors)
Maximum Operating Temperature	60C / 140F
Heavy Steel - Powder Coat Finish	Black
Configuration	19in / 483mm Horizontal Rackmount
Adjustable Mount Brackets	Yes
Country of Origin	USA, TAA Compliant and Buy American Act COTS Compliant
Product Warranty	5-year limited warranty

Certification/Agency Approvals	UL & c-UL Listed 62368-1
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	FCC Part 15 Class A Conformance
Chassis Dimensions (HxWxD)	1.72in x 17in x 12in / 44mm x 432mm x 305mm
Shipped Weight	10lbs (4.54kg)