

OVERVIEW

Upgradeable Switched Unit Level Monitored rPDUs provide reliable power distribution to critical IT equipment while delivering individual outlet level control and a comprehensive view of input power usage via remote network access. Includes environmental monitoring capabilities to obtain real-time environmental metrics. Upgrade the hot-swappable monitoring device on select units to leverage new technologies and accommodate changing business needs.

Benefits

- Remotely reboot outlets to power cycle unresponsive IT equipment or increase runtime of critical equipment upon power failure with outlet-level control.
- Reliable power distribution with local and remote power monitoring options offer quick access to critical power usage information to evaluate energy usage trends and maximize uptime.
- Environmental monitoring capabilities with the addition of optional environmental sensors ensure users have critical infrastructure data at their fingertips to prevent climate-related equipment failure and system downtime.
- Fault-Tolerant Daisy Chaining with RSTP simplifies intelligent rPDU connectivity and ensures data is reported even when a break in the network chain occurs. Supports up to 40 rPDUs.
- Daisy-chain up to 50 devices on a single IP address and reduce



Part #: VP5U60A0

Model Number: MUS5MHW1-36CF17-6PS6B4A10-S

Category: Switched

Sub Category: Unit Level Monitoring

Power Configuration: 60/63A, 200-240V, 14.4kW

Physical Configuration: 70in / 1778mm, Vertical

Product Summary:

rPDU, Switched Unit Level Monitoring, 60A/63A, 200-240V, 14.4kW, Vertical, (36) Combination C13/C19, 10ft / 3m power cord with 1P+N+E (IP44), Black Powder Coat.

Monitoring:

Input power monitoring with Outlet switching. Circuit/Breaker current monitoring. Environmental monitoring via optional remote sensors. Daisy chain Ethernet connectivity. Local high visibility display.


deployment time with self-configuration of downstream devices.

Plug Form:



1P+N+E (IP44)

Receptacle:



Combination C13/C19
(Quantity: 36)

Chassis Color Options:



To discuss color options, contact your local sales representative.

Product Specification and Options

System Features

Monitoring	Input power monitoring with Outlet switching. Circuit/Breaker current monitoring. Environmental monitoring via optional remote sensors. Daisy chain Ethernet connectivity. Local high visibility display.
Input Monitoring	Total Unit Monitoring (kWh, W, VA, PF) Phase (A, B, C) Monitoring (kWh, W, VA, PF, V, A) Power Measurements Compliant with ANSI C12.1 and IEC 62053-21 at 1% Accuracy Class Requirements
Circuit Monitoring	Circuit / Breaker Monitoring (A) Circuit/Breaker Current Measurements Independently Tested and Verified at 1% Accuracy
Remote Power Management	Individual Outlet Switching with Optional User Defined Time Delays and Sequential Power-up
Quantity Of Inputs	1
Voltage	200-240V
Current	60/63A
VA per Input (Load Capacity) 48A Derated UL	11.5kW (240V)
VA per Input (Load Capacity) 63A CE	14.4kW (230V)
Frequency	50/60Hz
Over Current Protection	(4) 16A Double Pole Magnetic Breakers
Switch	Breaker/Switch Combination
LCD Touchscreen Display / Auto Oriented	Yes
Indicators - LED(s)	36
Power Cable Wire Gauge	16mm ² H07RN-F
Power Cable Length	10ft / 3m
Power Entry Location	Bottom Front
Plug Type	IEC60309 2P + E, 60/63A, 250V, Splashproof IP44
Receptacle/Socket Type #1	Combination C13/C19
- Quantity on Face	36
- Quantity per Breaker	9
- Circuit Color ID	4 Circuit = Orange, Light Orange, Green, Light Green

- Style	Banks of 6
- Voltage per Receptacle/Socket	230V
Network Connection	Dual 10/100/1000Mbps Ethernet
Protocols Supported	DHCP, HTTP, HTTPS, IPv4, IPv6, LDAP, NTP, RADIUS, RSTP, SSH, SMTP, SNMP (v1/v2c/v3), Syslog, TACACS+, Modbus TCP
Data Access Formats	CSV datalog, JSON API, JSON datalog
USB Support	Yes
IP Reset Button	Yes
Hard Reboot Button	Yes
Serial Connection	RS232 via RJ45
Remote Sensor RJ Connection Jacks	1 (Supports up to 16 Sensors)
Maximum Operating Temperature	60C / 140F
Heavy Steel - Powder Coat Finish	Black
Configuration	Zero U
7938 Vertical Mounting Bracket Kit	Yes
Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in / 1556mm and 1645mm
Product Warranty	5-year limited warranty
Certification/Agency Approvals	CE Marked
Certification/Agency Approvals	UL & c-UL Listed 62368-1
Certification/Agency Approvals	UKCA Marked
Certification/Agency Approvals	Complies with IEC 62368-1 (DOC Available)
Certification/Agency Approvals	Complies with EN 55032 and EN 55035
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	RCM Mark (EMC Only)
Certification/Agency Approvals	FCC Part 15 Class A Conformance
Certification/Agency Approvals	China RoHS
Chassis Dimensions (LxWxD)	70in x 3.5in x 2.6in / 1778mm x 89mm x 66mm
Shipping Weight	20 lbs (9.1 kg)