

OVERVIEW

Upgradeable Switched Outlet Level Monitored rPDUs provide reliable power distribution to critical IT equipment while delivering individual outlet level control and a comprehensive view of outlet level power usage via remote network access. Includes environmental monitoring capabilities to obtain real-time environmental metrics. With the PowerIT Upgradeable hot-swap technology, users may easily update the rPDU technology with the addition of the appropriate Interchangeable Monitoring Device (IMD) as business needs change.

Benefits

- Remotely reboot outlets to power cycle unresponsive IT equipment or increase runtime of critical equipment upon power failure with outlet-level control.
- Reliable power distribution with local and remote outlet-level power monitoring options offer quick access to critical power usage information down to the device level to evaluate energy usage trends and maximize uptime.
- Environmental monitoring capabilities with the addition of optional environmental sensors ensure users have critical infrastructure data at their fingertips to prevent climate-related equipment failure and system downtime.
- Fault-Tolerant Daisy Chaining with RSTP simplifies intelligent rPDU connectivity and ensures data is reported even when a break in the network chain occurs. Supports up to 40 rPDUs.



Part #: VP7UA0A0

Model Number: JMUU5MIZ1-36CF13-8HW56A9BXX-S

Category: Switched

Sub Category: Outlet Level Monitoring

Power Configuration: 80A, 240/415V WYE, 57.6kW

Physical Configuration: 66in / 1683mm, Vertical

Product Summary:

rPDU, Switched Outlet Level Monitoring, 80A, 200-240/346-415V WYE, 57.6kW, Vertical, (36) Combination C13/C19, Hardwired, Black Powder Coat.

Monitoring:

Input and Outlet power monitoring with Outlet switching. Circuit/Breaker current monitoring. Environmental monitoring via optional remote sensors. Daisy chain Ethernet connectivity. Local high visibility display.

- Daisy-chain up to 50 devices on a single IP address and reduce deployment time with self-configuration of downstream devices.

Plug Form:

NO
IMAGE
AVAILABLE

Hardwired

Receptacle:



Combination C13/C19
(Quantity: 36)

Chassis Color Options:



To discuss color options, contact your local sales representative.

Product Specification and Options

System Features

| | |
|--|--|
| Monitoring | Input and Outlet power monitoring with Outlet switching. Circuit/Breaker current monitoring. Environmental monitoring via optional remote sensors. Daisy chain Ethernet connectivity. Local high visibility display. |
| Input Monitoring | Total Unit Monitoring (kWh, W, VA, PF) Phase (A, B, C) Monitoring (kWh, W, VA, PF, V, A) Power Measurements Compliant with ANSI C12.1 and IEC 62053-21 at 1% Accuracy Class Requirements |
| Circuit Monitoring | Circuit / Breaker Monitoring (A) Circuit/Breaker Current Measurements Independently Tested and Verified at 1% Accuracy |
| Outlet Monitoring | Outlet Monitoring (kWh, W, VA, PF, V, A) Power Measurements Compliant with ANSI C12.1 and IEC 62053-21 at 1% Accuracy Class Requirements. |
| Remote Power Management | Individual Outlet Switching with Optional User Defined Time Delays and Sequential Power-up |
| Quantity Of Inputs | 1 |
| Voltage | 200-240/346-415V WYE |
| Current | 80A x 3 Phase WYE |
| VA per Input (Load Capacity) | 57.6kW |
| Frequency | 50/60Hz |
| Over Current Protection | (18) 20A Single Pole Magnetic Breakers (10kAIC Rated) |
| Switch | Breaker/Switch Combination |
| LCD Touchscreen Display / Auto Oriented | Yes |
| Indicators - LED(s) | 36 |
| Power Entry Location | Bottom End |
| Hardwired | Removable Panel - Conduit Connection Access for Input & Output |
| Receptacle/Socket Type #1 | Combination C13/C19 |
| - Quantity on Face | 36 |
| - Quantity per Breaker | 2 |

| | |
|---|---|
| - Quantity per Phase | 12 |
| - Circuit Color ID | 18 Circuit = Orange, Green, Blue, Light Orange, Light Green, Light Blue, Orange, Green, Blue, Light Orange, Light Green, Light Blue, Orange, Green, Blue, Light Orange, Light Green, Light Blue |
| - Style | Banks of 6 |
| - Voltage per Receptacle/Socket | 240V (L-N) |
| Network Connection | Dual 10/100/1000Mbps Ethernet |
| Protocols Supported | DHCP, HTTP, HTTPS, IPv4, IPv6, LDAP, NTP, RADIUS, RSTP, SSH, SMTP, SNMP (v1/v2c/v3), Syslog, TACACS+, Modbus TCP |
| Data Access Formats | CSV datalog, JSON API, JSON datalog |
| USB Support | Yes |
| IP Reset Button | Yes |
| Hard Reboot Button | Yes |
| Serial Connection | RS232 via RJ45 |
| Remote Sensor RJ Connection Jacks | 1 (Supports up to 16 Sensors) |
| Maximum Operating Temperature | 60C / 140F |
| Heavy Steel - Powder Coat Finish | Black |
| Configuration | Zero U |
| 7938 Vertical Mounting Bracket Kit | Yes |
| Toolless Mounting Hardware - Center to Center Spacing | 61.25in and 64.75in / 1556mm and 1645mm |
| Product Warranty | 5-year limited warranty |
| Certification/Agency Approvals | CE Marked |
| Certification/Agency Approvals | UL & c-UL Listed 62368-1 |
| Certification/Agency Approvals | UKCA Marked |
| Certification/Agency Approvals | Complies with IEC 62368-1 (DOC Available) |
| Certification/Agency Approvals | Complies with EN 55032 and EN 55035 |
| Certification/Agency Approvals | RoHS Compliant |
| Certification/Agency Approvals | RCM Mark (EMC Only) |
| Certification/Agency Approvals | China RoHS |
| Certification/Agency Approvals | FCC Part 15 Class B Conformance |
| Chassis Dimensions (LxWxD) | 66.25in x 3.8in x 3.0in / 1683mm x 97mm x 76mm |
| Shipping Weight | 22 lbs (9.98 kg) |