

OVERVIEW

Rack Transfer Switch (RTS) delivers redundant power to single corded devices. The RTS automatically detects the loss of power and switches the power load (no phase-synchronization required) to the alternative power source in less than 4-8 milliseconds without the need for human intervention.

Benefits

- Reliable power distribution with local and remote power monitoring options offer quick access to critical power usage information to evaluate energy usage trends and maximize uptime.
- Environmental monitoring capabilities with the addition of optional environmental sensors ensure users have critical infrastructure data at their fingertips to prevent climate-related equipment failure and system downtime.
- Gather comprehensive power data at the palm of your hand with the use of the Vertiv VLC mobile app.
- Fault-Tolerant Daisy Chaining with RSTP simplifies intelligent rPDU connectivity and ensures data is reported even when a break in the network chain occurs. Supports up to 40 rPDUs.
- Every unit is 100% tested for reliability and functionality.



Part #: VA4G9100

Model Number: AG03E1R1-12CF13-3PS6PS6B211-D

Category: Rack Transfer Switch

Sub Category: Monitored Unit Level

Power Configuration: 32A, 230V, 7.3kW

Physical Configuration: 19in / 483mm, Horizontal

Product Summary:

rPDU, Rack Transfer Switch Monitored Unit Level, 32A, 230V, 7.3kW, Horizontal, (12) Combination C13/C19, 10ft / 3m power cords with 1P+N+E (IP44), Black Powder Coat.

Monitoring:

Input power monitoring with breaker level current monitoring. Environmental monitoring via optional remote sensors. Daisy chain Ethernet connectivity. Local high visibility LED display.

Plug Form:



1P+N+E (IP44)

Receptacle:



Combination C13/C19
(Quantity: 12)

Chassis Color Options:



To discuss color options, contact your local sales representative.

Product Specification and Options

System Features

Monitoring	Input power monitoring with breaker level current monitoring. Environmental monitoring via optional remote sensors. Daisy chain Ethernet connectivity. Local high visibility LED display.
Monitoring Level 1	Phase (A) Monitoring (kWh, W, VA, PF, V, A)
Monitoring Level 2	Circuit/Breaker Monitoring (A) Circuit/Breaker Current Measurements Independently Tested and Verified at 2% Accuracy
Power Switching	Auto Switching - In Event of Power Failure
Transfer Time	<4-8ms
Out of Phase Transfers	Yes
Front Panel HMI LED Overlay	Yes
Quantity Of Inputs	2 (Dual Input)
Voltage	200-240V
Current	32A
VA per Input (Load Capacity)	7.3kW (230V)
Frequency	50/60Hz
Over Current Protection	(2) 16A Single Pole Magnetic Breakers (10kAIC Rated)
Switch	Breaker/Switch Combination
Scrolling / Rotatable Digital Display	Yes
Power Cable Wire Gauge	4mm ² H07RN-F
Power Cable Length	10ft / 3m
Power Entry Location	Left Rear
Plug Type	(2) IEC60309 1P + N + E, 32A, 250V Connector, Splashproof IP44
Receptacle/Socket Type #1	Combination C13/C19
- Quantity on Rear	12
- Quantity per Breaker	6
- Circuit Color ID	2 Circuit = Orange, Green
- Style	Banks of 6
- Voltage per Receptacle/Socket	230V
Network Connection	Dual 10/100/1000Mbps Ethernet
Protocols Supported	DHCP, HTTP, HTTPS, IPv4, IPv6, LDAP, NTP, RADIUS, RSTP, SSH, SMTP, SNMP (v1/v2c/v3), Syslog, TACACS+
Data Access Formats	CSV datalog, JSON API, JSON datalog
USB Support	Yes
IP Reset Button	Yes
Hard Reboot Button	Yes
Serial Connection	RS232 via RJ45

Remote Sensor RJ Connection Jacks	1 (Supports up to 16 Sensors)
Maximum Operating Temperature	60C / 140F
Heavy Steel - Powder Coat Finish	Black
Configuration	19in / 483mm Horizontal Rackmount
Adjustable 4 Post Mounting (Range)	Yes (24" - 37")
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	CE Marked
Certification/Agency Approvals	Complies with EN 55032 and EN 55035
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	RCM Mark (EMC Only)
Certification/Agency Approvals	Complies with IEC 62368-1 (DOC Available)
Certification/Agency Approvals	C _p Mark
Chassis Dimensions (HxWxD)	1.72in x 17in x 18in / 44mm x 432mm x 457mm
Shipped Weight	19lbs (8.62kg)