



- | | |
|--------------------------------|---|
| ① INTELLISLOT PORT | ⑥ EXTERNAL BATTERY CONNECTOR |
| ② USB PORT | ⑦ 12A INPUT CIRCUIT BREAKER |
| ③ RS485 PORT | ⑧ INPUT POWER PLUG (5-15P, 10 FEET/3M) |
| ④ RS232 PORT | ⑨ NON-PROGRAMMABLE OUTPUT RECEPTACLES (5-15R) |
| ⑤ TERMINAL BLOCK COMMUNICATION | ⑩ PROGRAMMABLE OUTPUT RECEPTACLES (5-15R) |

NOTES:

1. UNIT DIMENSIONS (WxDxH): 16.9" x 15.8" x 3.3" (2U)
(430mm) x (401mm) x (85mm)
2. UNIT WEIGHT: 37lbs (16.8kg)
3. SHIPPING DIMENSIONS (WxDxH): 22.4" x 24.3" x 10.3"
(570mm) x (617mm) x (262mm)
4. SHIPPING WEIGHT: 50lbs (22.7kg)
5. MINIMUM AIRFLOW CLEARANCE IS 4.0" (100mm)
FRONT AND REAR.

DRAWN BY B. LAY CHK BY L. JOHNSON REF. DWG.	SHEET NO. 1 OF 1	OUTLINE DRAWING LIEBERT GXT5 500-1000VA 100/120VAC RACK/TOWER UPS	<div> </div>			
	ECN NO.					
	ORDER NO.					
		DWG. NO. GXT5-500_1KLVD	DATE 10/29/19	REV. # 2	1050 DEARBORN DRIVE P.O. BOX 29186 COLUMBUS, OHIO 43229	

FILE NAME: I:\dpgeng\GXT5\Submittals\A\Outline Dwg\GXT5-500_1KLVD