# Vertiv<sup>™</sup> EnergyCore Battery System



# Overview

Lithium-ion batteries have changed how we power the world—from mobile devices to electric vehicles. Now, that same proven technology is reshaping data centers handling AI compute loads.

The Vertiv<sup>™</sup> EnergyCore Battery System brings efficient, space-saving, and longlasting energy storage to UPS and critical infrastructure applications. With a focus on reliability and modernization, it helps organizations meet today's performance and sustainability goals.

#### **Ideally Suited For**

- New and retrofit data centers
- Cloud, colocation, and enterprise IT
- UPS energy storage systems
- Lead-acid battery replacements

#### Compliant

- UL 1973 Battery Safety
- UL 9540A Thermal propagation tested
- UL 9540

Qualified for most current and legacy three-phase Vertiv™ UPS systems.

<b>≡</b> \$787.05 55	(TVP	$\odot$	Normal	Operation	SERVICE	
ENEROYCORE BA SSOV Coldnet 1 SSOV Coldnet 3 SSOV Coldnet 7 SSOV	- <b>A</b>	- W 	42 04 42 05557 44 0557 48 0557	SYSTEM SHO	99.9 % State of Charge 555.7 V Time Remaining	
I a canad						

### **EnergyCore Battery Cabinet**

The Vertiv EnergyCore is the first lithium-ion battery cabinet engineered specifically for data center use. Its compact design, proven safety features, and factory-tested reliability make it a smarter choice for modern IT environments.

The cabinet has successfully passed UL 9540A thermal runaway testing. According to NFPA 855's ESS installation standards, when successfully completing a UL9540A test, the three feet (92cm) spacing requirement between racks can be waived by the Authorities having Jurisdiction (AHJ) and free up valuable white space in a data center.



#### **Benefits:**

- Purpose-built design optimized for 5-min and 7-min End of Life runtimes
- Accurate real-time State of Charge provides assurance with Al compute loads
- Predictive maintenance planning is enabled by State of Health tracking
- Reduced hits on battery from Al compute load steps exceeding 100%
- Integrated operation between batteries and power converter helps smooth input source current for AI compute load
- Built-in reverse polarity protection
- Visual monitoring of system and cabinet level status available with Touchscreen GHMI of primary cabinet

Vertiv™ EnergyCore Battery Cabinet

# Health management with Al compute loads

Vertiv EnergyCore battery systems use advanced algorithms to accurately calculate SoC and SoH.

#### State of Charge (SoC)

The Vertiv EnergyCore BMS provides accurate, real-time SoC using blended sensors to maintain precision across dynamic loads

- Real-time charge tracking
- Improves runtime predictability
- Reduces risk of over/undercharging

#### State of Health (SoH)

Vertiv EnergyCore tracks battery health across all levels, enabling smarter maintenance and longer battery life.

- Predictive maintenance insights
- Real-time performance alerts
- Fewer replacements, stronger ROI

#### A New Standard in Energy

The Vertiv<sup>™</sup> EnergyCore Battery System delivers powerful, space-efficient energy storage designed for modern data centers. With high-density lithium-ion battery modules and an integrated battery management system (BMS), Vertiv EnergyCore provides safe, reliable runtime while simplifying installation, service, and monitoring. The built-in GHMI display gives operators full visibility into battery performance and protection across all connected cabinets—delivering confidence from day one.



#### Why Choose Vertiv EnergyCore Over VRLA

Legacy VRLA batteries have long been used in critical backup systems, but they fall short in today's demanding IT environments. EnergyCore lithium-ion batteries deliver longer life, greater reliability, and smarter performance.

#### **Benefits of Lithium-ion Batteries**





Fewer Facility Disruptions Lower Total Cost of Ownership



# **Vertiv Brings All the Pieces Together**

Vertiv integrates UPS, batteries, monitoring, and services into one seamless energy storage solution. Built on decades of critical infrastructure experience, the Vertiv<sup>™</sup> EnergyCore Battery System connects directly into your power chain. You get one trusted partner for everything from deployment to long-term support.

Our systems are designed to work together, simplifying installation, improving visibility, and delivering the performance and reliability your operations require.





Vertiv<sup>™</sup> Liebert<sup>®</sup> EXL S1 with Vertiv<sup>™</sup> EnergyCore Batteries

# **Management and Control**

The Vertiv<sup>™</sup> Battery Management System (BMS) provides secure, real-time visibility at every level including cell, module, cabinet, and facility. Whether you are monitoring on-site or remotely, you gain proactive insights into battery health, safety, and performance.

Compatible with:

- Vertiv™ Albér™ Battery Xplorer Enterprise
- Vertiv™ Liebert® Sitescan™
- Third-party systems via open protocols

# **Protect Your Assets Wherever They Are Located**

Uptime depends on expert support. Vertiv offers both on-site and remote service from trained engineers who can monitor systems in real time or via shared files. Our team supports your infrastructure before, during, and after installation.

Scalable service plans help keep your critical infrastructure protected and performing at its best.

# **Vertiv: Your Energy Storage Expert**

Vertiv delivers more than just batteries. We provide a complete energy storage solution with proven technology and expert support. Whether you are upgrading old systems or building new, we can supply and support your next Vertiv EnergyCore deployment.

From maintenance to replacements, you can count on Vertiv to keep your energy storage working for you.

Addition
Addition

Provide
Constrained

Provide
Provide

Prov

Vertiv™ Albér™ Battery Xplorer Enterprise



Support Services for Critical Facilities

# Vertiv<sup>™</sup> EnergyCore Li5 Specifications

Vertiv™ Battery Module for 5 min EOL Runtime



Parameter	5 min EOL runtime						
	10 Module	16 Module	18 Module				
Nominal Energy	17.3kWh	27.6kWh	31.1kWh				
Nominal Voltage	288VDC	461VDC	518VDC				
Nominal Capacity		60Ah					
Dimensions		600mm x 750mm x 2000mm					
Weight	400kg	543kg	590kg				
Cell Type		Lithium-Iron Phosphate LFP Cylindrical Cell					
Battery Module		9S3P					
Battery Module Quantity	10	16	18				
Recommended End of Discharge Voltage	250VDC	401VDC	451VDC				
Float Charge Voltage	306VDC	495VDC	557VDC				
Maximum Discharge Power	146kWb	234kWb	263kWb				
Recommended Charge Current		20A					
Max Battery Cell Temperature		0°06					
Min Operating Battery Cell Temperature		10°C					
Maintenance Disconnect		1					
Fusing		500A/700VDC					
Charge Inhibit Circuit		Included					
DC Connections		Lugs to Terminals					
Network Interfaces		100MB Ethernet supports Modbus TCP or SNMP RS-485 supports Modbus RTU					
Service Interfaces		RS-232 Serial, USB 2.0					
Signaling		Isolated Discretes					
Front Panel		GHMI Touch Screen					
Recommended Operating Temperature		20°C to 30°C					
Storage Temperature Long Period		-20°C to 30°C					
Storage Temperature Less Than 2 Weeks		-20°C to 45°C					
Storage Temperature Less Than 1 Week		-30°C to 60°C					
Cooling		Convective					
Control Power		Internal					
Service Power		24VDC					
Compliance		CSA mark (UL 1973 3rd edition), CE mark (IEC 62619:2022), ISO 13849:2015 Cat. 2 PLa, ISTA 3B, UNDOT 38.3, FCC 47 CFR 15B					
Testing		UL9540A 4th Edition					
Altitude		Up to 3,000m					
Operating Humidity Range		5 to 95% Relative Humidity (Non-Condensing)					



# Vertiv<sup>™</sup> EnergyCore Li7 Specifications

Vertiv™ Battery Module (7 min EOL Runtime)



Parameter	7 min EOL runtime						
	10 Module	16 Module	17 Module				
Nominal Energy	20.4kWh	32.6kWh	34.6kWh				
Nominal Voltage	304.5VDC	486.4VDC	516.8VDC				
Nominal Capacity		67Ah					
Dimensions		600mm x 750mm x 2000mm					
Weight	443kg	564kg	582kg				
Cell Type		Lithium-Ion NMC/LMO Hybrid					
Battery Module		8S1P					
Battery Module Quantity	10	16	17				
Recommended End of Discharge Voltage	256VDC	409.6VDC	435.2VDC				
Float Charge Voltage	335.2VDC	536.3VDC	569.8VDC				
Maximum Discharge Power	130.7kWb	208.3kWb	222.2kWb				
Recommended Charge Current		22.3A					
Max Battery Cell Temperature		69°C					
Min Operating Battery Cell Temperature		18°C					
Maintenance Disconnect		1					
Fusing		500A/700VDC					
Charge Inhibit Circuit		Included					
DC Connections		Lugs to Terminals					
Network Interfaces		100MB Ethernet supports Modbus TCP or SNMP. RS-485 supports Modbus RTU					
Service Interfaces		RS-232 Serial, USB 2.0					
Signaling		Isolated Discretes					
Front Panel		GHMI Touch Screen					
Pushbuttons		18°C to 28°C					
Interlocks		-20°C to 30°C					
Recommended Operating Temperature		-20°C to 45°C					
Storage Temperature Long Period		-30°C to 60°C					
Storage Temperature Less Than 2 Weeks		Convective					
Storage Temperature Less Than 1 Week		Internal					
Cooling		24VDC					
Control Power		Internal					
Service Power		24VDC					
Compliance		CSA mark (UL 1973 3rd edition), CE mark (IEC 62619:2022), ISO 13849:2015 Cat. 2 PLc, ISTA 3B, UNDOT 38.3, FCC 47 CFR 15B					
Testing		UL9540A 4th Edition					
Altitude		Up to 2,000m					
Operating Humidity Range		5 to 95% Relative Humidity (Non-Condensing)					

Vertiv.com | Vertiv Headquarters, 505 N Cleveland Ave, Westerville, OH 43082, USA

© 2025 Vertiv Group Corp. All rights reserved. Vertiv<sup>™</sup> and the Vertiv logo are trademarks or registered trademarks of Vertiv Group Corp. All other names and logos referred to are trade names, trademarks or registered trademarks of their respective owners. While every precaution has been taken to ensure accuracy and completeness here, Vertiv Group Corp. assumes no responsibility, and disclaims all liability, for damages resulting from use of this information or for any errors or omissions. Specifications, rebates and other promotional offers are subject to change at Vertiv's sole discretion upon notice.