

TAA Compliant Solutions



Overview

Vertiv offers a comprehensive list of trade compliant products to ensure a smooth selection, procurement and deployment process for contractors and partners serving the federal, state and local governments.



*Trade Agreement Act (TAA)
per Federal Acquisition
Regulation 52.225-5*

*Buy American Act (BAA) per 41 USC
§§10a-10d and FAR Part 25, FAR §
52.225-1 and DFARS § 252.225-7001*

*If required Vertiv has a suite of
products that comply with The Buy
America Act per 49 U.S.C. § 5323(j)
and 49 C.F.R. § 661.5(a)
(FTA requirements).*

Today, critical technologies can be located anywhere; in an office, IT network closet, lab and data center. Government services depend on the continuity of these vital systems that offer power, cooling, control and management capabilities.



Vertiv has a comprehensive portfolio of solutions, ready to be procured and deployed to help you meet your agency's Data Center Optimization Initiative (DCOI) and modernization needs.

If you are looking for specific data center equipment that must be TAA-Compliant, or you have a TAA quota to meet, Vertiv can support you with our TAA-compliant critical infrastructure solutions.

Vertiv™ rack systems and integrated solutions can provide complete protection for your equipment while streamlining deployment. They are designed to meet flexibility, ease installation and delivery requirements. We have different rack systems to serve your mission critical needs even high-density environments.

Product

TAA BAA Additional Certifications

Single Phase UPS

Vertiv™ Liebert® PSI5 UPS 1500-3000VA VRLA UPS	✓		UL 1778, c-UL, ANSI C62.42, Energy Star, FCC, RoHS2, REACH
Vertiv™ Liebert® PSI5 Lithium UPS 1500-300VA	✓		UL 1778, UL1642, UL 1973, UN38.3, c-UL, ANSI C62.41, Energy Star, FCC, RoHS2, REACH
Vertiv™ Liebert® GXT5 TAA 1000-3000 VA VRLA UPS	✓		UL 1778, CSA, ANSI C62.41, Energy Star, FCC, RoHS2, REACH

Power Distribution

Vertiv™ Geist™ Rack Transfer Switch	✓	✓	UL & c-UL Listed 62368-1, RoHS Compliant, FCC Part 15 Class A Conformance (Monitored, Switched, Switched & Outlet Monitored Models Only), UL 2900 (IMD-5M Models Only)
Vertiv™ Geist™ Switched Rack PDU	✓	✓	
Vertiv™ Geist™ Monitored Rack PDU	✓	✓	
Vertiv™ Geist™ Basic Rack PDU	✓	✓	
Vertiv™ Geist™ Universal PDU (UPDU)	✓	✓	

Busway and Busduct

Vertiv™ Powerbar iMPB	✓	✓	
-----------------------	---	---	--

Racks

Vertiv™ VR Rack System	✓		EIA 310E, UL2416, RoHS, REACH
Vertiv™ DCE Rack System	✓	✓	EIA 310E, UL2416, IBC2012
Vertiv™ Wallmount, 2-Post, 4-Post Racks	✓		UL2416

Integrated Solutions

Vertiv™ SmartMod™	✓	✓	
Vertiv™ SmartMod™ Max CW	✓	✓	
Vertiv™ SmartMod™ Max DX	✓	✓	
Vertiv™ MegaMod™	✓	✓	
Vertiv™ SmartMod™ Combo	✓	✓	
Vertiv™ SmartMod™ Combo	✓	✓	
Vertiv™ SmartMod™ Combo	✓	✓	

Thermal

Vertiv™ Liebert® CRV Row Based Data center cooling 10-40kW	✓	✓	BAA available through ETO request, AHRI
Vertiv™ Liebert® PDX Cooling System	✓	✓	
Vertiv™ CoolLoop RDHx	✓	✓	
Vertiv™ CoolLoop Thermal Wall	✓	✓	BAA available through ETO request
Vertiv™ Liebert® DSE Free-Cooling Economization System, 50-265kW	✓	✓	
Vertiv™ Liebert® CW Chilled Water Cooling System, 38-181 kW	✓	✓	AHRI
Vertiv™ Liebert® CW Chilled Water-cooling System, 305-440kW	✓		
Vertiv™ Liebert® Mini-Mate, Ceiling-Mounted Variable Capacity Coolin, 10.5, 14 & 17.5kW	✓	✓	BAA available through ETO request
Vertiv™ Liebert® Mini-Mate, ceiling mounted precision cooling system 3.5-28kw	✓	✓	BAA through ETO
Vertiv™ Liebert® AFC inverter screw free cooling chiller range with low-GWP refrigerant from 900 to 1800 kW	✓		
Vertiv™ Liebert® PCW Compact Chilled Water Cooling System, 11-29kW	✓	✓	BAA available through ETO request, AHRI
Vertiv™ Liebert® AFC Chillers	✓		

Product

TAA BAA Additional Certifications

Three Phase UPS

Vertiv™ Liebert® EXM UPS, 10-250kVA	✓	✓	
Vertiv™ Liebert® EXL S1 UPS	✓	✓	
Vertiv™ Liebert® NXL	✓	✓	
Vertiv™ Liebert® Trinegy™ Cube UPS	✓	✓	

IT Systems (Avocent)

Vertiv™ Avocent® HMX 5000/6000/8000 High Performance KVMs	✓		CE, FCC, UL, RCM, BiS
Vertiv™ Avocent® Longview™ 5500/5520 Extenders	✓		CE, FCC approvals
Vertiv™ Avocent® HMX 6500R High Performance KVM Receiver	✓		
Vertiv™ Avocent® MergePoint Unity™ KVM over IP Switch	✓		FIPS 140-2
Vertiv™ Avocent® LCD Local Rack Access (LRA) Console	✓		UL, CE, CCC, BSMI, RCM, cUL, IC, EAC, VCCL, KCC FCC Class A
Vertiv™ Avocent® Cybex™ SC800 and SC900 Secure Desktop KVM Switches	✓		NIAP PP4.0; EAL4+; FCC class A; CE; UKCA; TUV – US; TUV – Canada; RCM; VCCI
Vertiv™ Avocent® Cybex™ Secure MultiViewer KVM Switch	✓		NIAP PP4.0; EAL4+; FCC class A; CE; UKCA; TUV – US; TUV – Canada; RCM; VCCI
Vertiv™ Avocent® Cybex™ SCM 100 Series Secure Desktop Matrix	✓		
Vertiv™ Avocent® Cybex™ SCKM 100 Secure Desktop KM Switches	✓		
Vertiv™ Avocent® ACS8000	✓		
Vertiv™ Avocent® IPIQ IPUHD	✓		UL, FCC Part 15, cUL, ICES-003, CE, RoHS, REACH, EAC, VCCI, KCC, RCM, BSMI, NOM, and FIPS140-2
Vertiv™ Avocent® IPSL MP1000 Appliance	✓		EMI: EN55032 Class A EN55024 EN55035 EN61000-3-2 EN61000-3-3 FCC Part 15, Subpart B Class A VCCI Class A CCC BSMI 13438 Safety CB UL CCC BSMI 14336-1 RoHS-2.0 Compliant
Vertiv™ Avocent® RM1048P	✓		UL, FCC Part 15, cUL, ICES-003, CE, RoHS, REACH, EAC, VCCI, KCC, RCM, SMI, CCC, NOM, FIPS140-2

Vertiv™ Secure KVM Products offer a variety of TAA-compliant accessories.